



ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	5/15/2024	KDANG	AGANWANI



FLANGE DETAIL
(FDP22)FLANGE DETAIL
(FDM22)

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
X = ±.2 [5] FRACTIONS
XX = ±.02 [0.5] ± 1/32
XXX = ±.005 [0.13] ANGLES ± 1°

CABLE LENGTH TOLERANCES:
≤12 [305] = +1 [25] / -0
≥12 [305] ≤ 60 [1524] = +2 [51] / -0
≥60 [1524] ≤ 120 [3048] = +4 [102] / -0
≥120 [3048] ≤ 300 [7620] = +6 [152] / -0
≥300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND
COLORS MAY VARY

WR-430
FDM22 GROOVED FLANGE

INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE SHEET
NONE 1 OF 1

 Fairview Microwave®
an INFINIT® brand

Website: www.FairviewMicrowave.com
Phone: 1.800.715.4396 | 1.972.649.6678

DESCRIPTION
WR-430 90 DEGREE WAVEGUIDE RIGHT HAND TWIST WITH A
UG COVER AND GROOVED FLANGES OPERATING FROM 1.72
GHZ TO 2.61 GHZ

SIZE CAGE CODE DRAWN BY ITEM NO. REV
A 3FKR5 KDANG FMW430TW001 A

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.