





REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	04/16/2026	AKRESOWSKI	DWANG

CENTER CONDUCTOR	Ø .262 [6.66]	TUBULAR BARE COPPER
DIELECTRIC	Ø .680 [17.27]	GAS INJECTED FOAM POLYETHYLENE
SHIELD	Ø .686 [17.42]	BONDED ALUMINUM-POLYESTER-ALUMINUM TAPE
OUTER BRAID	Ø .732 [18.59]	30 GA TINNED COPPER BRAID (90%k)
JACKET	Ø .870 [22.10]	BLACK, LOW SMOKE LOW TOXICITY FR POLYETHYLENE

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS	
TOLERANCES:	
X = ±.2 [5]	FRACTIONS ± 1/32
.XX = ±.02 [0.5]	ANGLES ± 1°
.XXX = ±.005 [0.13]	
CABLE LENGTH TOLERANCES:	
≤12 [305] = +1 [25] / -0	
>12 [305] ≤ 60 [1524] = +2 [51] / -0	
>60 [1524] ≤ 120 [3048] = +4 [102] / -0	
>120 [3048] ≤ 300 [7620] = +6 [152] / -0	
>300 [7620] = +5% / -0	
CABLE LENGTH TOL IAW IPC A-620	
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE UN-DIMENSIONED/NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION COLORS MAY VARY	

 Fairview Microwave® an INFINIT@ company			
Website: www.FairviewMicrowave.com Phone: 1.800.715.4396 1.866.730.6243		SCALE NONE	SHEET 1 OF 1
DESCRIPTION LOW LOSS FLEXIBLE LMR-900-FR RISER RATED COAX CABLE WITH BLACK PE JACKET			
SIZE A	CAGE CODE 3FKR5	DRAWN BY AKRESOWSKI	ITEM NO. LMR-900-FR
			REV A