

78 Ohm TRS Subminiature Plug 1553 Connector Clamp/Solder Attachment for M17/176-00002

78 Ohm TRS Subminiature Plug 1553 Connector Clamp/Solder Attachment for M17/176-00002 Cable, part number FMCN10-10030-206, from Fairview Microwave is in-stock and ships same day. This TRS Subminiature plug connector operates up to a maximum frequency of 500 MHz. TRS Subminiature Plug connector has a bayonet coupling design with a center contact and an intermediate cylindrical contact. TRS connectors are preferred in applications that require weight reduction, high packing density, and noise-free guarded circuits. TRS connectors can increase packing density to more than 240% compared to TRB standard connectors. The reduced size limits the maximum outer cable diameter to 0.250 inches.

Fairview's 78 ohm TRS Subminiature plug connector FMCN10-10030-206 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		500	MHz
Insertion Loss		0.1		dB

Mechanical Specifications

Size	
Length	0.76 in [19.3 mm]
Width/Dia.	0.45 in [11.43 mm]
Height	0.45 in [11.43 mm]
Weight	0.01 lbs [4.54 g]

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold 30 micro inches ASTM-B-488
Insulation	Teflon	
Outer Conductor	Phosphor Bronze	ASTM-B-488
Body	Brass	Nickel ASTM-B-733
Gasket	Rubber	
Crimp Sleeve	Brass	Nickel



Configuration:

- TRS Subminiature Plug Connector
- MIL-STD-1553
- 78 Ohms
- Straight Body Geometry
- M17/176-00002 Interface Type
- Clamp/Solder Attachment
- 1553 Design

Features:

- Operating Frequency of 500 MHz Max.
- Gold 30 micro inches Plated Beryllium Copper Contact
- Contact plating according to ASTM-B-488
- Twinax Connectivity
- Subminiature

Applications:

- General Purpose Test
- Custom Cable Assemblies
- Robust Design
- Ease of Use
- Use in High Shock and Vibration Environment

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Environmental Specifications

Temperature

Operating Range -55 to +200 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data


Notes:

78 Ohm TRS Subminiature Plug 1553 Connector Clamp/Solder Attachment for M17/176-00002 from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [78 Ohm TRS Subminiature Plug 1553 Connector Clamp/Solder Attachment for M17/176-00002 FMCN10-10030-206](#)

URL: <https://www.fairviewmicrowave.com/trs-subminiature-plug-m17-176-00002-connector-fmcn10-10030-206-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



78 Ohm TRS Subminiature Plug 1553 Connector Clamp/Solder Attachment for M17/176-00002

78 Ohm TRS Subminiature Plug 1553 Connector Clamp/Solder Attachment for M17/176-00002 Cable, part number FMCN10-10030-206, from Fairview Microwave is in-stock and ships same day. This TRS Subminiature plug connector operates up to a maximum frequency of 500 MHz. TRS Subminiature Plug connector has a bayonet coupling design with a center contact and an intermediate cylindrical contact. TRS connectors are preferred in applications that require weight reduction, high packing density, and noise-free guarded circuits. TRS connectors can increase packing density to more than 240% compared to TRB standard connectors. The reduced size limits the maximum outer cable diameter to 0.250 inches.

Fairview's 78 ohm TRS Subminiature plug connector FMCN10-10030-206 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		500	MHz
Insertion Loss		0.1		dB

Mechanical Specifications

Size	
Length	0.76 in [19.3 mm]
Width/Dia.	0.45 in [11.43 mm]
Height	0.45 in [11.43 mm]
Weight	0.01 lbs [4.54 g]

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold 30 micro inches ASTM-B-488
Insulation	Teflon	
Outer Conductor	Phosphor Bronze	ASTM-B-488
Body	Brass	Nickel ASTM-B-733
Gasket	Rubber	
Crimp Sleeve	Brass	Nickel



Configuration:

- TRS Subminiature Plug Connector
- MIL-STD-1553
- 78 Ohms
- Straight Body Geometry
- M17/176-00002 Interface Type
- Clamp/Solder Attachment
- 1553 Design

Features:

- Operating Frequency of 500 MHz Max.
- Gold 30 micro inches Plated Beryllium Copper Contact
- Contact plating according to ASTM-B-488
- Twinax Connectivity
- Subminiature

Applications:

- General Purpose Test
- Custom Cable Assemblies
- Robust Design
- Ease of Use
- Use in High Shock and Vibration Environment

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Environmental Specifications**Temperature**

Operating Range -55 to +200 deg C

Compliance Certifications (see [product page](#) for current document)**Plotted and Other Data**

Notes:

78 Ohm TRS Subminiature Plug 1553 Connector Clamp/Solder Attachment for M17/176-00002 from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [78 Ohm TRS Subminiature Plug 1553 Connector Clamp/Solder Attachment for M17/176-00002 FMCN10-10030-206](#)

URL: <https://www.fairviewmicrowave.com/trs-subminiature-plug-m17-176-00002-connector-fmcn10-10030-206-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

