

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	1	INITIAL RELEASE	04/25/2024	DZINN	AGANWANI

NOTES:


1. CENTER PIN CRIMP SIZE .19[4.8] X .11[2.7]. CONTACT PIN RETENTION FORCE ≥ 10 LB.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS	
TOLERANCES:	
X = $\pm .2$ [5]	FRACTIONS $\pm 1/32$
XX = $\pm .02$ [0.5]	ANGLES $\pm 1^\circ$
XXX = $\pm .005$ [0.13]	
CABLE LENGTH TOLERANCES:	
≤ 12 [305] = $+1$ [25] / -0	
>12 [305] ≤ 60 [1524] = $+2$ [51] / -0	
>60 [1524] ≤ 120 [3048] = $+4$ [102] / -0	
>120 [3048] ≤ 300 [7620] = $+6$ [152] / -0	
>300 [7620] = $+5\%$ / -0	
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE UN-DIMENSIONED/NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION COLORS MAY VARY	



Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE
NONE

SHEET
1 OF 1

DESCRIPTION
TCOM CONNECTOR FOR TCOM-600, 4.3-10 MALE (PLUG), FIELD
INSTALL, CRIMP PIN

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	53919	DZINN	TCP-600-4310MC-LP	1