

UHF Male Connector Crimp/Non-Solder Contact Attachment for LMR-600, LMR-600-DB Cable

Times Microwave Systems Connector Specification

UHF Male Standard Connector Crimp/Non-Solder Contact Attachment for LMR-600, LMR-600-DB and PE-C600 Cable, part number EZ-600-UM-X, from Times Microwave offered by Fairview Microwave is in-stock and ships same day. This UHF male connector operates up to a maximum frequency of 3 GHz.

Times Microwave's UHF male connector EZ-600-UM-X datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		3	GHz
Insertion Loss			0.17	dB
DWV (AC)			2,000	Vrms
Insulation Resistance	10,000			MOhms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Freq. Range	DC to 2.45					GHz
VSWR, Max	1.3:1					

Mechanical Specifications

Size

Length	2.54 in [64.52 mm]
Width/Dia.	0.689 in [17.50 mm]
Height	0.689 in [17.5 mm]
Weight	0.01188 lbs [5.39 g]

Material Specifications

Description	Material	Plating
Contact	Phosphor Bronze	Silver 200µin
Insulation	PTFE	
Body	Brass	Tin/Nickel 100µin
Coupling Nut	Brass	Tin/Nickel 100µin



Configuration:

- UHF Male Connector
- 50 Ohms
- Straight Body Geometry
- LMR-600, LMR-600-DB, PE-C600 Interface Type
- Crimp/Non-Solder Contact Attachment

Features:

- Operating Frequency of 3 GHz Max.
- Silver Plated Phosphor Bronze Contact
- 200µin contact plating

Applications:

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

 Crimp Sleeve

Copper

 Tin/Nickel
 100µin

Environmental Specifications

Temperature

Operating Range

-40 to +125 deg C

Shock

MIL-STD-202, Meth. 213, Cond. G

Vibration

MIL-STD-202, Meth. 204, Cond. B

Thermal Shock

MIL-STD-202, Meth. 107, Cond. B

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data


Notes:

UHF Male Connector Crimp/Non-Solder Contact Attachment for LMR-600, LMR-600-DB Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [UHF Male Connector Crimp/Non-Solder Contact Attachment for LMR-600, LMR-600-DB Cable EZ-600-UM-X](#)

URL: <https://www.fairviewmicrowave.com/uhf-male-lmr-600-connector-ez-600-um-x-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



UHF Male Connector Crimp/Non-Solder Contact Attachment for LMR-600, LMR-600-DB Cable

Times Microwave Systems Connector Specification

UHF Male Standard Connector Crimp/Non-Solder Contact Attachment for LMR-600, LMR-600-DB and PE-C600 Cable, part number EZ-600-UM-X, from Times Microwave offered by Fairview Microwave is in-stock and ships same day. This UHF male connector operates up to a maximum frequency of 3 GHz.

Times Microwave's UHF male connector EZ-600-UM-X datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		3	GHz
Insertion Loss			0.17	dB
DWV (AC)			2,000	Vrms
Insulation Resistance	10,000			MOhms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Freq. Range	DC to 2.45					GHz
VSWR, Max	1.3:1					

Mechanical Specifications

Size

Length	2.54 in [64.52 mm]
Width/Dia.	0.689 in [17.50 mm]
Height	0.689 in [17.5 mm]
Weight	0.01188 lbs [5.39 g]

Material Specifications

Description	Material	Plating
Contact	Phosphor Bronze	Silver 200µin
Insulation	PTFE	
Body	Brass	Tin/Nickel 100µin
Coupling Nut	Brass	Tin/Nickel 100µin



Configuration:

- UHF Male Connector
- 50 Ohms
- Straight Body Geometry
- LMR-600, LMR-600-DB, PE-C600 Interface Type
- Crimp/Non-Solder Contact Attachment

Features:

- Operating Frequency of 3 GHz Max.
- Silver Plated Phosphor Bronze Contact
- 200µin contact plating

Applications:

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Crimp Sleeve	Copper	Tin/Nickel 100µin
--------------	--------	----------------------

Environmental Specifications

Temperature

Operating Range	-40 to +125 deg C
Shock	MIL-STD-202, Meth. 213, Cond. G
Vibration	MIL-STD-202, Meth. 204, Cond. B
Thermal Shock	MIL-STD-202, Meth. 107, Cond. B

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data


Notes:

UHF Male Connector Crimp/Non-Solder Contact Attachment for LMR-600, LMR-600-DB Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: [UHF Male Connector Crimp/Non-Solder Contact Attachment for LMR-600, LMR-600-DB Cable EZ-600-UM-X](#)

URL: <https://www.fairviewmicrowave.com/uhf-male-lmr-600-connector-ez-600-um-x-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



TCOM-600-FR Low PIM Flexible Coax Cable Black FRPE Jacket Fire Rated



TCOM-600-FR

Configuration

- Low PIM, Fire Rated Flexible Cable
- 3 Shield(s)

Features

- Lightweight and Extremely Flexible
- PIM < -155 dBc
- RF Shielding >100 dB
- Low Loss Dielectric 87% VoP
- Fire Rated Jacket
- Non-Halogen (Non-Toxic)

Applications

- Wireless Base Station Interconnect
- Distributed Antenna Systems (DAS)
- Antenna Jumpers
- UL/NEC & CSA rating of 'CMR' and 'FT4'
- Low Smoke Requirements
- Small Cell
- Indoor-Riser CMR

Description

TCOM-600 low PIM coax cable from Fairview Microwave is only one of many radio frequency coaxial cable types specifically stocked to be ready for same business day shipment. Fairview Microwave's TCOM-600-FR coax cable is manufactured in a flexible design and has a 50 Ohm impedance. This flexible 50 Ohm coax cable is constructed with a polyethylene jacket of 0.590 inch diameter. The maximum passive intermodulation of this low PIM cable is -155 dBc.

Fairview Microwave's TCOM-600-FR flexible coax cable with a polyethylene jacket is rated for a 10 GHz maximum operating frequency. This 50 Ohm flexible coax cable is built with a shield count of 3. Our low PIM RF coaxial cable has a solid conductor made of copper. The black-colored coax RF cable has a typical insertion loss/attenuation of 0.45, 1.1, 1.9, 2.8, 4.5, 7.6 and 11.0 dB/100ft at frequencies of 30 MHz, 150 MHz, 450 MHz, 900 MHz, 2000 MHz, 5800 MHz and 10000 MHz respectively.


The TCOM-600 coax cable with foam polyethylene dielectric can operate at temperatures ranging from -40 to +85 deg C. Additional specifications for this TCOM-600-FR RF coaxial cable are on our downloadable PDF datasheet above. Our low PIM coaxial cable has a dielectric withstanding voltage of 4000 Vdc. This low PIM RF cable has a one time minimum bend radius of 1.5 inches and a repeat minimum bend radius of 6.0 inches. Our flexible 50 Ohm coax cable has a peak power rating of 40000 watts.

TCOM-600 low PIM RF cable is part of more than one million RF, microwave, and millimeter wave parts in stock at Fairview Microwave. This TCOM-600 coax cable is ready to buy and can be shipped worldwide. Fairview Microwave also maintains a wide selection of other radio frequency and coaxial cable types that ship the same business day from our warehouse in the United States, as with the rest of our other RF/microwave and millimeter wave components.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		10	GHz
Impedance		50		Ohms
Velocity of Propagation		87		%
Time Delay		1.17 [3.84]		ns/ft [ns/m]
Shielding Effectiveness	100			dB

TCOM-600-FR Low PIM Flexible Coax Cable Black FRPE Jacket Fire Rated



TCOM-600-FR

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Passive Intermodulation			-155	dBc
Dielectric Withstanding Voltage (DC)			4,000	Vdc
Jacket Spark			8,000	Vrms
Inner Conductor DC Resistance			0.53	Ohms/1000ft
Outer Conductor DC Resistance			1.52	Ohms/1000ft
Nominal Capacitance		23.4 [76.77]		pF/ft [pF/m]
Nominal Inductance		0.058 [0.19]		uH/ft [uH/m]
Input Power (Peak)			40	kWatts

Performance by Frequency Band

Description	F1	F2	F3	F4	F5	Units
Frequency	0.03	0.15	0.45	0.9	2	GHz
Attenuation, Typ	0.45	1.1	1.9	2.8	4.5	dB/100ft
	1.48	3.61	6.23	9.19	14.76	dB/100m

Description	F6	F7	F8	F9	F10	Units
Frequency	5.8	10				GHz
Attenuation, Typ	7.6	11				dB/100ft
	24.93	36.09				dB/100m


Mechanical Specifications

Diameter	0.59 in [14.99 mm]
Weight	0.154 lbs/ft [0.23 kg/m]
Min. Bend Radius (Installation)	1.5 in [38.1 mm]
Min. Bend Radius (Repeated)	6 in [152.4 mm]
Bending Moment	2.75 lbs-ft [3.73 N-m]
Tensile Strength	350 lbs [158.76 kg]
Flat Plate Crush	60 lbs/in [1.07 kg/mm]

Construction Specifications

Description	Material and Plating	Diameter
Inner Conductor	Copper Clad Aluminum, 1 Strand	0.176 in [4.47 mm]
Conductor Type	Solid	
Dielectric	PE (F)	0.455 in [11.56 mm]
First Shield	Silver Plated Copper Braid	0.465 in [11.81 mm]
Second Shield	Tinned Copper Braid	0.5 in [12.7 mm]

TCOM-600-FR Low PIM Flexible Coax Cable Black FRPE Jacket Fire Rated



TCOM-600-FR

Construction Specifications

Description	Material and Plating	Diameter
Jacket	FRPE, Black	0.59 in [14.99 mm]

Environmental Specifications

Temperature

Operating Range	-40 to +85 deg C
Installation Range	-40 to +85 deg C
Storage Range	-70 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

TCOM-600-FR Low PIM Flexible Coax Cable Black FRPE Jacket Fire Rated from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [TCOM-600-FR Low PIM Flexible Coax Cable Black FRPE Jacket Fire Rated TCOM-600-FR](#)

URL: <https://www.fairviewmicrowave.com/tcom600fr-low-pim-flexible-coax-cable-frpe-jacket-tcom-600-fr-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

TCOM-600-FR CAD Drawing

TCOM-600-FR Low PIM Flexible Coax Cable Black FRPE Jacket Fire Rated

