

RA BNC Male Connector Crimp/Non-Solder Contact Attachment for LMR-240, LMR-240-DB, LMR-240-UF, LMR-240-FR, RG8X Cable

Times Microwave Systems Connector Specification

EZ-240-BM-RA-X BNC male right angle coaxial connector has an interface type of BNC male which is compatible with LMR-240, LMR-240-DB, LMR-240-UF, LMR-240-FR, and RG8X cables and a 50 Ohms impedance. Fairview Microwave's BNC male connector uses crimp/non-solder contact as an attachment method. Our male BNC right angle coaxial connector operates at a maximum frequency of 6 GHz.

The Fairview Microwave right angle BNC male coaxial connector has a teflon dielectric type and a VSWR of 1.35. Fairview Microwave's BNC coaxial connector has a brass body with tri-metal plating. Our EZ-240-BM-RA-X BNC right angle connector uses brass contact. This bayonet RF connector can operate at temperatures ranging from -55 to 155 degrees C. Additional RF connector specs and dimensions for this component can be found on its PDF specification datasheet and CAD drawings above.

The radio frequency connector is made from brass along with a contact life of 500 cycles or more. Our high-quality EZ-240-BM-RA-X connector features an 80 μ m minimum body plating specification. This right angle BNC connector has a gold over nickel inner contact plating. Fairview Microwave's BNC male connector has a maximum operating voltage of 500 Vrms.

This Fairview Microwave right angle male BNC connector will ship the same business day as purchased. Our BNC right angle male connector is part of over 40,000 RF, microwave, and millimeter wave components in stock for worldwide shipment. For further information on similar products, our expert technical support and trained sales team can get you the ideal RF connector as per your requirements.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		6	GHz
VSWR			1.35:1	
Operating Voltage (AC)			500	Vrms
DWV (DC)			750	Vdc
Insulation Resistance	5,000			MOhms

Mechanical Specifications

Size	
Length	1.32 in [33.53 mm]
Width/Dia.	0.571 in [14.50 mm]
Height	1.185 in [30.1 mm]
Weight	0.1 lbs [45.36 g]
Mating Cycles	500 Cycles
Cable Retention Force	60 lbs [27.22 kg]

Material Specifications

Description	Material	Plating
Contact	Brass	Gold over nickel 50 μ m minimum



Configuration:

- BNC Male Connector
- 50 Ohms
- Right Angle Body Geometry
- LMR-240, LMR-240-DB, LMR-240-UF, LMR-240-FR, RG8X Interface Type
- Crimp/Non-Solder Contact Attachment

Features:

- Operating Frequency of 6 GHz Max.
- Good VSWR of 1.35:1
- Gold over nickel Plated Brass Contact
- 50 μ m minimum contact plating

Applications:

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Insulation	Teflon	
Body	Brass	Tri-Metal 80 μ in minimum
Crimp Sleeve	Brass	Tri-Metal 80 μ in minimum

Environmental Specifications

Temperature

Operating Range

-55 to +155 deg C

Shock

US MIL-STD 202, Meth.213, Cond.I

Vibration

US MIL-STD 202, Meth.204, Cond.B

Thermal Shock

US MIL-STD 202, Meth.107, Cond.B

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

RA BNC Male Connector Crimp/Non-Solder Contact Attachment for LMR-240, LMR-240-DB, LMR-240-UF, LMR-240-FR, RG8X Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [RA BNC Male Connector Crimp/Non-Solder Contact Attachment for LMR-240, LMR-240-DB, LMR-240-UF, LMR-240-FR, RG8X Cable EZ-240-BM-RA-X](#)

URL: <https://www.fairviewmicrowave.com/bnc-male-lmr-240-lmr-240-db-lmr-240-uf-lmr-240-fr-rg8x-connector-ez-240-bm-ra-x-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

