

1553 TRB 3-Slot Plug to TRB 3-Slot Plug Cable
78 Ohm FMBC-30-02003 Coax in 12 Inch with Bend Relief

The 78 ohm TRB 3-Slot plug to 78 ohm TRB 3-Slot plug 12 inch cable using 78 ohm FMBC-30-02003 twinax, part number FM3MP2164-12, from Fairview Microwave is in-stock and ships same day. This Fairview TRB 3-Slot to TRB 3-Slot cable assembly has a plug to plug gender configuration with 78 ohm flexible FMBC-30-02003 twinax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FM3MP2164-12 TRB 3-Slot plug to TRB 3-Slot plug cable assembly operates to 500 MHz. The FM3MP2164 cable assembly consists of a 3-slot solder/clamp TRB plug with Bend Relief to 3-slot solder/clamp TRB plug with Bend Relief for FMBC-30-02003, that is a standard lab-rated PVC cable for MIL-STD-1553 applications, with an O.D. 0.150". These cable assemblies come with a 1.700" steel spring-style bend relief that helps to minimize cable damage when exceeding the cables minimum bend radius. These assemblies are built to withstand severe shocks and vibrations.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		500	MHz
Capacitance		20.3 [66.6]		pF/ft [pF/m]
Operating Voltage (AC)			300	Vrms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	10	50	100	200	500	MHz
Insertion Loss (Typ.)	0.253	0.319	0.368	0.437	0.575	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications
Cable Assembly

Length* 12 in [304.8 mm]
 Weight 0.3 lbs [136.08 g]

Cable

Cable Type FMBC-30-02003
 Impedance 78 Ohms
 Inner Conductor Type Stranded
 Inner Conductor Material and Plating Copper, Silver
 Dielectric Type PE
 Shield Layer 1 Silver Plated Copper


Configuration:

- TRB 3-Slot Plug
- TRB 3-Slot Plug
- FMBC-30-02003

Features:

- Max Frequency 500 MHz
- PVC Jacket
- MIL-STD-1553
- -20°C to +75°C
- 78 ohms
- Lab rated
- Bend Relief

Applications:

- General Purpose
- Laboratory Use
- MIL-STD-1553
- Data
- Lab applications

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Jacket Material PVC, Blue
One Time Minimum Bend Radius 1.5 in [38.1 mm]

Connectors

Description	Connector 1	Connector 2
Type	TRB 3-Slot Plug Bayonet	TRB 3-Slot Plug Bayonet
Option	Bend Relief Spring	Bend Relief Spring
Impedance	78 Ohms	78 Ohms
Contact Material & Plating	Bronze, Gold 30 micro inches	Bronze, Gold 30 micro inches
Contact Plating Spec.	ASTM-B-488	ASTM-B-488
Dielectric Type	Teflon	Teflon
Outer Cond Material & Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Outer Cond Plating Spec.	30 micro inches	30 micro inches
Body Material & Plating	Brass, Nickel	Brass, Nickel
Body Plating Spec.	ASTM-B-733	ASTM-B-733

Environmental Specifications

Temperature
Operating Range -20 to +75 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FM3MP2164 - xx uu

cm = Centimeters
<blank> = Inches
Length

Example: FM3MP2164-12 = 12 inches long cable
FM3MP2164-100cm = 100 cm long cable


1553 TRB 3-Slot Plug to TRB 3-Slot Plug Cable 78 Ohm FMBC-30-02003 Coax in 12 Inch with Bend Relief from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [1553 TRB 3-Slot Plug to TRB 3-Slot Plug Cable 78 Ohm FMBC-30-02003 Coax in 12 Inch with Bend Relief FM3MP2164-12](https://www.fairviewmicrowave.com/1553-trb-3-slot-plug-to-trb-3-slot-plug-cable-78-ohm-fmbc-30-02003-coax-in-12-inch-with-bend-relief-fm3mp2164-12)

URL: <https://www.fairviewmicrowave.com/1553-trb-3-slot-plug-to-trb-3-slot-plug-cable-78-ohm-fmbc-30-02003-coax-in-12-inch-with-bend-relief-fm3mp2164-12-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





REVISION		DATE	CHANGED BY	APPROVED
ZONE	REV			
	A	08/01/2023	LNAGARAJ	EKIM
DESCRIPTION				
INITIAL RELEASE				

<p>Fairview Microwave[®] an INFINIT[®] brand</p> <p>Website: www.FairviewMicrowave.com Phone: 1.800.715.4396 1.972.649.6678</p>		<p>INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 SCALE NONE SHEET 1 OF 1</p>														
<p>UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE IN INCHES, DIMENSIONS IN [] ARE MILLIMETERS</p> <p>TOLERANCES:</p> <table border="0"> <tr> <td>X = ± 2 [6]</td> <td>FRACTIONS ± 1/32</td> </tr> <tr> <td>.XX = ± 0.01 [0.5]</td> <td>ANGLES ± 1°</td> </tr> <tr> <td>XXX = ± 0.05 [1.3]</td> <td></td> </tr> </table> <p>CABLE LENGTH TOLERANCES:</p> <table border="0"> <tr> <td>> 12 [305] ≤ 60 [1524] = ± 2 [51] / -0</td> <td>512 [305] = +1 [25] / -0</td> </tr> <tr> <td>> 60 [1524] ≤ 90 [2286] = ± 3 [76] / -0</td> <td>90 [2286] = +2 [51] / -0</td> </tr> <tr> <td>> 90 [2286] ≤ 120 [3048] = ± 4 [102] / -0</td> <td>120 [3048] = +6 [152] / -0</td> </tr> <tr> <td>> 120 [3048] ≤ 300 [7620] = ± 6 [152] / -0</td> <td>300 [7620] = +5% / -0</td> </tr> </table>			X = ± 2 [6]	FRACTIONS ± 1/32	.XX = ± 0.01 [0.5]	ANGLES ± 1°	XXX = ± 0.05 [1.3]		> 12 [305] ≤ 60 [1524] = ± 2 [51] / -0	512 [305] = +1 [25] / -0	> 60 [1524] ≤ 90 [2286] = ± 3 [76] / -0	90 [2286] = +2 [51] / -0	> 90 [2286] ≤ 120 [3048] = ± 4 [102] / -0	120 [3048] = +6 [152] / -0	> 120 [3048] ≤ 300 [7620] = ± 6 [152] / -0	300 [7620] = +5% / -0
X = ± 2 [6]	FRACTIONS ± 1/32															
.XX = ± 0.01 [0.5]	ANGLES ± 1°															
XXX = ± 0.05 [1.3]																
> 12 [305] ≤ 60 [1524] = ± 2 [51] / -0	512 [305] = +1 [25] / -0															
> 60 [1524] ≤ 90 [2286] = ± 3 [76] / -0	90 [2286] = +2 [51] / -0															
> 90 [2286] ≤ 120 [3048] = ± 4 [102] / -0	120 [3048] = +6 [152] / -0															
> 120 [3048] ≤ 300 [7620] = ± 6 [152] / -0	300 [7620] = +5% / -0															
<p>ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE. UN-DIMENSIONED CRITICAL FEATURES MAY VARY. DIMENSIONAL TOLERANCES MAY VARY. COLORS MAY VARY.</p>																
SIZE	CAGE CODE	ITEM NO.														
A	3FKR5	FM3MP2164-XX														

- NOTES:
- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
 - CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY LENGTH DETERMINED BY PN AS ILLUSTRATED: FM3MP2164-XX (XX = OAL IN METERS).

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN WHOLE OR IN PART FOR ANY PURPOSES WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITY TECHNOLOGY OR SOFTWARE WHEN EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.