

## TRS Subminiature Plug to TRB Jack 1553 Cable 24 Inch Length Using 78 Ohm M17/176-00002 Coax

The 78 ohm TRS Subminiature plug to 78 ohm TRB 3-Lug jack 24 inch cable using 78 ohm M17/176-00002 twinax, part number FM3MP3006-24, from Fairview Microwave is in-stock and ships same day. This Fairview TRS Subminiature to TRB 3-Lug cable assembly has a plug to jack gender configuration with 78 ohm flexible M17/176-00002 twinax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FM3MP3006-24 TRS Subminiature plug to TRB 3-Lug jack cable assembly operates to 10 MHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

| Description            | Min | Typ        | Max     | Units        |
|------------------------|-----|------------|---------|--------------|
| Frequency Range        | DC  |            | 10      | MHz          |
| Capacitance            |     | 24 [78.74] |         | pF/ft [pF/m] |
| Operating Voltage (AC) |     |            | 750,000 | Vrms         |

### Performance by Frequency

| Description           | F1    | F2    | F3    | F4   | F5   | Units |
|-----------------------|-------|-------|-------|------|------|-------|
| Frequency             | 1     | 3     | 5     | 7    | 10   | MHz   |
| Insertion Loss (Typ.) | 0.228 | 0.242 | 0.256 | 0.27 | 0.29 | dB    |

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

### Mechanical Specifications

#### Cable Assembly

|         |                     |
|---------|---------------------|
| Length* | 24 in [609.6 mm]    |
| Weight  | 0.117 lbs [53.07 g] |

#### Cable

|                                      |                      |
|--------------------------------------|----------------------|
| Cable Type                           | M17/176-00002        |
| Impedance                            | 78 Ohms              |
| Inner Conductor Type                 | Stranded             |
| Inner Conductor Material and Plating | Copper, Silver       |
| Dielectric Type                      | PTFE                 |
| Shield Layer 1                       | Silver Plated Copper |
| Jacket Material                      | PFA, Blue            |

|                              |                  |
|------------------------------|------------------|
| One Time Minimum Bend Radius | 1.5 in [38.1 mm] |
|------------------------------|------------------|



### Configuration:

- TRS SUBMINIATURE Plug
- TRB 3-Lug Jack
- M17/176-00002

### Features:

- Max Frequency 10 MHz
- PFA Jacket
- MIL-STD-1553
- -55°C to +200°C
- 78 ohms

### Applications:

- General Purpose
- Laboratory Use
- Vehicle High Temperature
- Data
- MIL-STD-1553

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

## Connectors

| Description                   | Connector 1                   | Connector 2                  |
|-------------------------------|-------------------------------|------------------------------|
| Type                          | TRS SUBMINIATURE Plug Bayonet | TRB 3-Lug Jack Bayonet       |
| Impedance                     | 78 Ohms                       | 78 Ohms                      |
| Contact Material & Plating    | Bronze, Gold 30 micro inches  | Bronze, Gold 30 micro inches |
| Contact Plating Spec.         | ASTM-B-488                    | ASTM-B-488                   |
| Dielectric Type               | Teflon                        | Teflon                       |
| Outer Cond Material & Plating | Phosphor Bronze, Gold         | Phosphor Bronze, Gold        |
| Outer Cond Plating Spec.      | 30 micro inches               | 30 micro inches              |
| Body Material & Plating       | Brass, Nickel                 | Brass, Nickel                |
| Body Plating Spec.            | ASTM-B-733                    | ASTM-B-733                   |

## Environmental Specifications

### Temperature

Operating Range -55 to +200 deg C

## Compliance Certifications (see [product page](#) for current document)

## Plotted and Other Data

Notes:

## How to Order

Part Number Configuration:

**FM3MP3006 - xx uu**

cm = Centimeters  
 <blank> = Inches

Length

Example: FM3MP3006-12 = 12 inches long cable  
 FM3MP3006-100cm = 100 cm long cable

TRS Subminiature Plug to TRB Jack 1553 Cable 24 Inch Length Using 78 Ohm M17/176-00002 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [TRS Subminiature Plug to TRB Jack 1553 Cable 24 Inch Length Using 78 Ohm M17/176-00002 Coax FM3MP3006-24](#)

URL: <https://www.fairviewmicrowave.com/1553-trs-subminiature-plug-to-trb-3-lug-jack-cable-78-ohm-m17-176-00002-coax-in-24-inch-fm3mp3006-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

