

## Halogen Free 1553 TRB 3-Lug Jack to Blunt Cut Genderless Cable 78 Ohm TWCH-78-2 Coax

The 78 ohm TRB 3-Lug jack to Blunt cut genderless cable using 78 ohm TWCH-78-2 twinax, part number FM3MSA00400, from Fairview Microwave is in-stock and ships same day. This Fairview TRB 3-Lug to Blunt Cut cable assembly has a jack to genderless gender configuration with 78 ohm flexible TWCH-78-2 twinax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FM3MSA00400 TRB 3-Lug jack to Blunt cut genderless cable assembly operates to 500 MHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		500	MHz
Capacitance		21.2 [69.55]		pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

### Mechanical Specifications

#### Cable Assembly

Length\* 0 in [0 mm]  
 Weight 0.054 lbs [24.49 g]

#### Cable

Cable Type TWCH-78-2  
 Impedance 78 Ohms  
 Inner Conductor Type Stranded  
 Inner Conductor Material and Plating Copper, Silver  
 Dielectric Type PE  
 Shield Layer 1 Silver Plated Copper  
 Jacket Material HF POF, Blue

One Time Minimum Bend Radius 1.25 in [31.75 mm]



### Configuration:

- TRB 3-Lug Jack
- Blunt Cut Genderless
- TWCH-78-2

### Features:

- Max Frequency 500 MHz
- HF POF Jacket
- MIL-STD-1553
- -30°C to +80°C
- 78 ohms
- Halogen Free
- Non-Toxic

### Applications:

- General Purpose
- Laboratory Use
- Military Contractors
- MIL-STD-1553
- Data
- Safer Environments
- Ventilation critical areas

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Connectors**

Description	Connector 1	Connector 2
Type	TRB 3-Lug Jack Bayonet	Blunt Cut Genderless Other
Impedance	78 Ohms	
Contact Material & Plating	Bronze, Gold 30 micro inches	
Contact Plating Spec.	ASTM-B-488	
Dielectric Type	Teflon	
Outer Cond Material & Plating	Phosphor Bronze, Gold	
Outer Cond Plating Spec.	30 micro inches	
Body Material & Plating	Brass, Nickel	
Body Plating Spec.	ASTM-B-733	

**Environmental Specifications**  
**Temperature**

Operating Range -30 to +80 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

**How to Order**

Part Number Configuration: **FM3MSA00400 - xx uu**

cm = Centimeters  
<blank> = Inches

Length

Example: FM3MSA00400-12 = 12 inches long cable  
FM3MSA00400-100cm = 100 cm long cable

Halogen Free 1553 TRB 3-Lug Jack to Blunt Cut Genderless Cable 78 Ohm TWCH-78-2 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [Halogen Free 1553 TRB 3-Lug Jack to Blunt Cut Genderless Cable 78 Ohm TWCH-78-2 Coax FM3MSA00400](#)

URL: <https://www.fairviewmicrowave.com/halogen-free-1553-trb-3-lug-jack-to-blunt-cut-genderless-cable-78-ohm-twch-78-2-coax-fm3msa00400-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

