

WR-90 Waveguide Standard Gain Horn Antenna Operating from 8.2 GHz to 12.4 GHz with a Nominal 25 dB Gain SMA Female Input



FM9856B/SF-25

Features

- WR-90 Rectangular Waveguide Interface
- 8.2 GHz to 12.4 GHz
- 25 dBi Nominal Gain
- Type SMA Female Connector

Applications

- Antenna Measurements
- Wireless Communication
- Laboratory Use
- Microwave Radio Systems

Description

The Fairview Microwave FM9856B/SF-25 Proline series standard gain horn antenna (also known as waveguide horn) is part of our huge selection of waveguide antennas. This Fairview Microwave standard gain horn antenna is manufactured with a WR-90 input and a Type SMA waveguide to coaxial transition adapter. Our standard gain horn antenna, WR-90 has a 25 dBi nominal gain. This WR-90 standard gain horn from Fairview Microwave has a female Type SMA waveguide to coax transition adapter.

The 25 dBi Fairview Microwave WR-90 horn antenna operates from 8.2GHz to 12.4 GHz. Fairview Microwave's Type SMAfemale WR-90The 25 dBi Fairview Microwave WR-90 horn antenna operates from 8.2 GHz to 12.4 GHz. Fairview Microwave's Type SMA female WR-90 standard gain horns are available in 10, 15 and 20 dBi models with pyramidal shape and rectangular input. It is part of over 40,000 RF, microwave and millimeter wave components available at Fairview Microwave.

Waveguide standard gain horn antennas, such as the FM9856B/SF-25, are used in a wide variety of applications due to their high power handling capability, low loss, high directivity, and near constant electrical performance. The WR-90 FM9856B/SF-25 waveguide horn is US made and TAA compliant. Our WR-90 standard gain horn Proline antennas with Type SMA female interface can ship same day to anywhere in the world.

Configuration

Design	WR-90
Pattern	Directional
Coaxial Interface	SMA Female

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	8.2		12.4	GHz
Gain		25		
Horizontal Half Power Beam Width		8		Degrees
Vertical Half Power Beam Width		8		
Waveguide to Coaxial Adapter				
VSWR			1.4:1	

Mechanical Specifications

Size	
Length	24.5 in [622.3 mm]
Width	9.83 in [249.68 mm]
Height	7.29 in [185.17 mm]
Weight	0.58 lbs [263.08 g]

WR-90 Waveguide Standard Gain Horn Antenna Operating from 8.2 GHz to 12.4 GHz with a Nominal 25 dB Gain SMA Female Input



FM9856B/SF-25

RF Connector

Type	SMA Female
Contact Material Plating	Stainless Steel

Waveguide Interface

Waveguide Size	WR-90
Flange Type	Square Cover
Flange Designation	UG-135/U
Body Material and Plating	Aluminum

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data

WR-90 Waveguide Standard Gain Horn Antenna Operating from 8.2 GHz to 12.4 GHz with a Nominal 25 dB Gain SMA Female Input from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [WR-90 Waveguide Standard Gain Horn Antenna Operating from 8.2 GHz to 12.4 GHz with a Nominal 25 dB Gain SMA Female Input FM9856B/SF-25](#)

URL: <https://www.fairviewmicrowave.com/wr-90-standard-gain-horn-25-db-sma-fm9856b-sf-25-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FM9856B/SF-25 CAD Drawing

WR-90 Waveguide Standard Gain Horn Antenna Operating from 8.2 GHz to 12.4 GHz with a Nominal 25 dB Gain SMA Female Input

