

## N Male (Plug) to RP TNC Female (Jack) Adapter, Commercial Grade



### FMAD10049

#### Configuration

- N Male Connector 1
- TNC Female Reverse Polarity Connector 2
- 50 Ohms Impedance
- Straight Body Geometry

#### Features

- Gold Plated Brass Contact

#### Applications

- Enables Between Series Connections
- General Purpose Test

#### Description

Type N male to RP TNC female adapter part number FMAD10049 from Fairview Microwave is in-stock and ships same day. This Fairview type N to reverse polarity TNC adapter has a male to female gender configuration. FMAD10049 type N male to reverse polarity TNC female adapter operates to 11 GHz.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		11	GHz
Impedance		50		Ohms
Insertion Loss			0.15	dB
Operating Voltage (DC)			500	Vdc
Dielectric Withstanding Voltage (AC)			1,000	Vrms

#### Mechanical Specifications

##### Size

Length	1.31 in [33.30 mm]
Width	0.79 in [19.99 mm]
Height	0.79 in [19.99 mm]
Weight	0.08 lbs [36.29 g]

Description	Connector 1	Connector 2
Polarity	Standard	Reverse Polarity
Mating Torque	15 in-lbs 1.70 Nm max	15 in-lbs 1.70 Nm max

## N Male (Plug) to RP TNC Female (Jack) Adapter, Commercial Grade



**FMAD10049**

### Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	N Male		TNC Female Reverse Polarity	
Contact	Brass	Gold	Brass	Gold
Insulation	PTFE		PTFE	
Outer Conductor	Brass	Nickel	Brass	Nickel
Body	Brass	Nickel	Brass	Nickel
Gasket	Silicone Rubber			

### Environmental Specifications

#### Temperature

Operating Range

-55 to +85 °C

Humidity

MIL-Std-202, Method 106, Condition B

Vibration

MIL-Std-202, Method 204, Condition B

Altitude

MIL-Std-202, Method 105, Condition C

Temperature Cycling

MIL-Std-202, Method 102, Condition C

Salt Spray

MIL-Std-202, Method 101, Condition C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

N Male (Plug) to RP TNC Female (Jack) Adapter, Commercial Grade from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [N Male \(Plug\) to RP TNC Female \(Jack\) Adapter, Commercial Grade FMAD10049](#)

URL: <https://www.fairviewmicrowave.com/product/rf-adapters/n-male-to-rp-tnc-female-adapter-mil-std-202-method-106-condition-b-fmad10049.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMAD10049 CAD Drawing
N Male (Plug) to RP TNC Female (Jack) Adapter, Commercial Grade

