

## N Female (Jack) to SHV Male (Plug) Adapter MIL-STD-202, Method 206



### FMAD10128

#### Configuration

- N Female Connector 1
- SHV Male Connector 2
- 50 Ohms Impedance
- Straight Body Geometry

#### Features

- VSWR of 1.2:1 max up to 300 MHz
- Gold over Nickel over Copper Plated Beryllium Copper Contact

#### Applications

- Enables Between Series Connections
- General Purpose Test

#### Description

Type N female to SHV male adapter part number FMAD10128 from Fairview Microwave is in-stock and ships same day. This Fairview type N to SHV adapter has a female to male gender configuration. FMAD10128 type N female to SHV male adapter operates to 300 MHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.2:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		300	MHz
Impedance		50		Ohms
VSWR			1.2:1	
Operating Voltage (AC)			1,000	Vrms
Dielectric Withstanding Voltage (AC)			2,500	Vrms

#### Electrical Specification Notes:

Dielectric Withstanding Voltage (at sea level)

Working Voltage (at sea level)

#### Mechanical Specifications

##### Size

Length	1.91 in [48.59 mm]
Width	0.75 in [19.00 mm]
Height	0.75 in [19.00 mm]
Weight	0.10 lbs [45.36 g]

Description	Connector 1	Connector 2
Polarity	Standard	Standard

## N Female (Jack) to SHV Male (Plug) Adapter MIL-STD-202, Method 206



### FMAD10128

Description	Connector 1	Connector 2
Mating Cycles, Min	500	500
Mating Torque	6 to 10 in-lbs 0.68 to 1.13 Nm	0.6 to 2.5 in-lbs 0.07 to 0.28 Nm
Contact Captivation Axial Force, Min	6.3 lbs [2.86 kg]	6.1 lbs [2.77 kg]
Coupling Retention, Min		101.2 lbs [45.9 kg]

### Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	N Female		SHV Male	
Contact	Beryllium Copper	Gold over Nickel over Copper	Beryllium Copper	Gold over Nickel over Copper
Insulation	PTFE		PTFE	
Body	Brass	Copper-Tin-Zinc Alloy	Brass	Copper-Tin-Zinc Alloy
Gasket	Silicone		Silicone	
Washer	Brass		Brass	

### Environmental Specifications

#### Temperature

Operating Range

-65 to +165 °C

Humidity

MIL-STD-202, Method 206

Thermal Shock

MIL-STD-202, Method 107, Condition B

Salt Spray

MIL-STD-202, Method 101, Condition B

### Compliance Certifications (see [product page](#) for current document)

### Plotted and Other Data

N Female (Jack) to SHV Male (Plug) Adapter MIL-STD-202, Method 206 from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [N Female \(Jack\) to SHV Male \(Plug\) Adapter MIL-STD-202, Method 206 FMAD10128](#)

URL: <https://www.fairviewmicrowave.com/product/rf-adapters/n-female-to-shv-male-adapter-mil-std-202-method-206-fmad10128.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMAD10128 CAD Drawing
N Female (Jack) to SHV Male (Plug) Adapter MIL-STD-202, Method 206

