

High Temperature Adapter Bulkhead 2.92mm Female to 2.92mm Female, 40GHz VSWR1.25, MIL-STD 348B with Stainless Steel Body

Bulkhead 2.92mm female to 2.92mm female adapter part number FMAD1667 from Fairview Microwave is in-stock and ships same day. This Fairview 2.92mm to 2.92mm adapter has a female to female gender configuration and is built of stainless steel in a high temperature adapter design. FMAD1667 2.92mm female to 2.92mm female adapter operates to 40 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.25:1 maximum. The 2.92mm connector mates mechanically with commercially available SMA and 3.5mm connectors. Our RF 2.92mm bulkhead to 2.92mm adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

| Description | Min | Typ | Max | Units |
|------------------------|-------|-----|--------|-------|
| Frequency Range | DC | | 40 | GHz |
| VSWR | | | 1.25:1 | |
| Insertion Loss | | | 0.26 | dB |
| Operating Voltage (AC) | | | 250 | Vrms |
| DWV (AC) | | | 750 | Vrms |
| Insulation Resistance | 5,000 | | | MOhms |
| RF Leakage | | | 100 | dB |

Mechanical Specifications

| | |
|-------------|--------------------|
| Size | |
| Length | 0.87 in [22.10 mm] |
| Width | 0.37 in [9.40 mm] |
| Height | 0.37 in [9.40 mm] |
| Weight | 0.01 lbs [4.54 g] |

| Description | Connector 1 | Connector 2 |
|--------------------------------------|-----------------------------------|-----------------------------------|
| Type | 2.92mm Female | 2.92mm Female |
| Polarity | Standard | Standard |
| Mating Cycles, Min | 500 | 500 |
| Mating Torque | 11.47 in-lbs min [1.30 Nm] min | 11.47 in-lbs min [1.30 Nm] min |
| Contact Captivation Axial Force, Min | 4.9 lbs [2.22 kg] | 4.9 lbs [2.22 kg] |
| Coupling Proof Torque | 15 in-lbs [1.7 Nm] | 15 in-lbs [1.7 Nm] |



Configuration:

- 2.92mm Female Connector 1
- 2.92mm Female Connector 2
- 50 Ohm
- High Temperature Adapter Design
- Straight Body Geometry
- Bulkhead Mount Method

Features:

- VSWR of 1.25:1 max up to 40 GHz
- Gold over Nickel Plated Beryllium Copper Contact

Applications:

- General Purpose Test
- Rack Mounted Equipment

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Material Specifications

| Description | Connector 1 | Connector 2 |
|---------------------|------------------|------------------|
| Type | 2.92mm Female | 2.92mm Female |
| Contact Material | Beryllium Copper | Beryllium Copper |
| Contact Plating | Gold over Nickel | Gold over Nickel |
| Insulation Material | PEI | PEI |
| Body Material | Stainless Steel | Stainless Steel |
| Body Plating | Passivated | Passivated |

Environmental Specifications

Temperature

Operating Range

Humidity

Thermal Shock

Salt Spray

-50 to +170 deg C

MIL-STD-202, Method 206

MIL-STD-202, Method 107, Condition B

MIL-STD-202, Method 101, Condition B

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

High Temperature Adapter Bulkhead 2.92mm Female to 2.92mm Female, 40GHz VSWR1.25, MIL-STD 348B with Stainless Steel Body from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [High Temperature Adapter Bulkhead 2.92mm Female to 2.92mm Female, 40GHz VSWR1.25, MIL-STD 348B with Stainless Steel Body FMAD1667](#)

URL: <https://www.fairviewmicrowave.com/high-temperature-adapter-bulkhead-2.92mm-female-to-2.92mm-female-adapter-mil-std-202-method-206-40ghz-vswr1.25-mil-std-348b-with-stainless-steel-body-fmad1667-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

