

2.5 dB NF, 2 GHz to 8 GHz, Low Noise Broadband Amplifier with 13 dBm, 14 dB Gain and SMA

FMAM3290 is a broadband coaxial low noise amplifier, operating in the 2 to 8 GHz frequency range. The amplifier offers 13 dBm of P1dB min and 14 dB small signal gain min, with the gain flatness of ± 2.0 dB max and a Noise Figure of 2.5 dB. This low noise amplifier requires only a single positive DC supply, in unconditionally stable, operates over the temperature range of -20°C to 85°C , and is Hermetically sealed.

Electrical Specifications (TA= 25°C, VDC1 = 12 Vdc)

Description	Min	Typ	Max	Unit
Frequency Range	2		8	GHz
Gain	14			dB
P1dB	+13			dBm
Noise Figure		2.5		dB
Input VSWR			2:1	
Output VSWR			2:1	
Operating DC Voltage 1	11	12	13	Volts
Operating DC Current		120		mA
Operating Temperature Range (OTR)	-40		+80	$^{\circ}\text{C}$

Mechanical Specifications

Size	
Length	1.083 in [27.51 mm]
Width	1.093 in [27.76 mm]
Height	0.382 in [9.7 mm]
Weight	0.069 lbs [31.3 g]
Input Connector	SMA Female
Output Connector	SMA Female

Environmental Specifications

Temperature	
Operating Range	-40 to $+80$ deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

- Values at 25 $^{\circ}\text{C}$, sea level
- ESD Sensitive Material, Transport material in Approved ESD bags. Handle only in ESD Workstation.



Features:


- 2 to 8 GHz Frequency Range
- P1dB: 13 dBm min
- Small Signal Gain: 14 dB min
- Gain Flatness: ± 2.0 dB max
- Noise Figure: 2.5 dB max
- 50 Ohm Input and Output Matched
- -20 to $+85^{\circ}\text{C}$ Operating Temperature
- Unconditionally Stable
- Single DC Positive Supply
- Built-in DC Voltage Regulator


Applications:

- Laboratory Applications
- R&D Labs
- Test Instrumentation
- Military & Space
- Communication Systems
- Satellite Communications
- Wireless Communications
- Unmanned Systems
- Microwave Radio Systems
- Low Noise Amplifier
- General Purpose Amplification
- RF Front Ends

Fairview Microwave
1130 Junction Dr. #100
Allen, TX 75013
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Typical Performance Data






2.5 dB NF, 2 GHz to 8 GHz, Low Noise Broadband Amplifier with 13 dBm, 14 dB Gain and SMA from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [2.5 dB NF, 2 GHz to 8 GHz, Low Noise Broadband Amplifier with 13 dBm, 14 dB Gain and SMA FMAM3290](https://www.fairviewmicrowave.com/2-8-ghz-low-noise-broadband-amplifier-fmam3290-p.aspx)

URL: <https://www.fairviewmicrowave.com/2-8-ghz-low-noise-broadband-amplifier-fmam3290-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



STANDARD TOLERANCES

.X ±0.2
.XX ±0.1
.XXX ±0.05

*STANDARD TOLERANCES APPLY
ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

TITLE

2.5 dB NF, 2 GHz to 8 GHz, Low Noise Broadband
Amplifier with 13 dBm, 14 dB Gain and SMA

DWG NO

FMAM3290

CAGE CODE

3FKR5

CAD FILE

111016

SHEET

SCALE

N/A

SIZE

A

2233