

862 to 928 MHz Rubber Duck Antenna 3 dBi SMA Male Tilt Swivel

FMANRBD1057



Features

- 862 MHz to 928 MHz
- 3 dBi Gain
- SMA Male connector
- Tilt/Swivel
- VSWR 2.5:1
- Linear polarization

Applications

- LPWAN
- ISM
- LoRaWAN
- Sigfox
- Weightless-P
- WiFi HaLow
- Fixed and Mobile Devices

Description

The FMANRBD1057 is a high-quality dual-band rubber duck antenna with 3 dBi nominal gain and has a frequency range of 862 MHz to 928 MHz. Fairview Microwave's omnidirectional tilt/swivel rubber duck antenna is 5.34 inches tall and 0.79 inches wide.

The FMANRBD1057 rubber duck antenna from Fairview Microwave features a SMA Male connector with an input VSWR (voltage standing wave ratio) of 2.5:1.

Fairview Microwave's linearly polarized antenna can operate at temperatures ranging from -40 °C to 60 °C. This dual-band rubber duck antenna is offered with expert technical support, PDF datasheets, and CAD drawings with dimensions and specifications.

Configuration

Design	Rubber Duck
Band Type	Dual
Radiation Pattern	Omni Directional
Polarization	Linear
Connector Type	SMA Male
Number of Ports	1

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	862		928	MHz
Input VSWR			2.5:1	
Impedance		50		Ohms
Gain		3		dBi

Specifications by Band

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Frequency	0.862 to 0.87	0.902 to 0.928				GHz

Mechanical Specifications

Radome Material	ABS
Size	
Length	6 in [152.4 mm]

862 to 928 MHz Rubber Duck Antenna 3 dBi SMA Male Tilt Swivel

FMANRBD1057



Width	0.5 in [12.7 mm]
Height	0.5 in [12.7 mm]
Weight	0.035 lbs [15.88 g]

Connectors

Description	Connector 1	Connector 2	Connector 3
Body Material and Plating	Brass		

Environmental Specifications

Temperature	
Operating Range	-20 to +65 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Radiation Pattern

Appendix

Electrical Downtilt: Angle in the antenna's elevation pattern in which the maximum gain occurs.

Gain: Antenna's average gain.

Front to Back Ratio @ 180°±30°: Average difference between the antenna's maximum gain and the maximum gain in the antenna's back lobe over ±30° angles.

Cross-polarization Ratio (dB): Typical difference between the co-polarization and cross-polarization gain across the sector's 3 dB Beam Width.

862 to 928 MHz Rubber Duck Antenna 3 dBi SMA Male Tilt Swivel from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [862 to 928 MHz Rubber Duck Antenna 3 dBi SMA Male Tilt Swivel FMANRBD1057](#)

URL: <https://www.fairviewmicrowave.com/product/antennas/862-928-mhz-rubber-duck-antenna-3-dbi-sma-male-tilt-swivel-fmanrbd1057.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMANRBD1057 CAD Drawing
862 to 928 MHz Rubber Duck Antenna 3 dBi SMA Male Tilt Swivel

