

## Low Loss RA SMA Male to SMA Male Weatherproof Cable LMR-240 Coax with LF Solder

### FMC00136/WP




#### Configuration

- Connector 1: SMA Male Right Angle
- Connector 2: SMA Male
- Cable Type: LMR-240
- Coax Flex Type: Flexible

#### Features

- Max Frequency 6 GHz
- Shielding Effectivity > 90 dB
- 84% Phase Velocity
- Double Shielded
- PE Jacket
- Silicone Connector Boot
- IP68 Rated



#### Applications

- General Purpose
- Laboratory Use

#### Description

The Fairview Microwave FMC00136/WP is a weatherproof low loss cable assembly that comes with SMA male connection with weatherproof boot on one end and SMA male with weatherproof boot on the other. Fairview Microwave's RF coaxial cable assembly products are designed for typical use, production, laboratory test and measurement, defense/military, aerial antenna towers, etc. The low loss cable has a 50 Ohm impedance and is specifically ready for quicker shipment than most in the industry can provide.

This weatherproof low loss RF cable assembly operates at a maximum frequency of 6 GHz. Our RF cable assembly has a PE jacket with 0.240 inches diameter. The SMA male to SMA male cable assembly FMC00136/WP is built with LMR-240 coax, which has a flexible design. This RF cable assembly with 0.5 inches diameter has copper as cable's inner conducting material and PE (F) dielectric type. The weatherproof boot low loss cable can operate at a temperature range of -40 to 85 degrees C. Additional dimensions, specifications, and CAD drawings for this FMC00136/WP low loss RF cable are available on our downloadable PDF datasheet.

Fairview Microwave stocks a wide selection of weatherproof low loss cable assemblies that ship the same business day as ordered from our warehouse. Make your online purchase right now to take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the ideal SMA male to SMA male cable assembly as per your requirements.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		84		%
RF Shielding	90			dB
Capacitance		24.2 [79.4]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]

## Low Loss RA SMA Male to SMA Male Weatherproof Cable LMR-240 Coax with LF Solder



### FMC00136/WP

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
DC Resistance Inner Conductor		3.2 [10.5]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		3.89 [12.76]		Ohms/1000ft [Ohms/Km]
Dielectric Withstanding Voltage (DC)			1,500	Vdc
Jacket Spark			5,000	Vrms

#### Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	250	500	1000	2500	6000	MHz	
FMC00136/WP	Custom Lengths Available	Insertion Loss (Typ.)	0.039	0.055	0.079	0.129	0.204	dB/ft	
			0.13	0.19	0.26	0.43	0.67	dB/m	
FMC00136/WP-12	12 Inch	Insertion Loss (Typ.)	0.34	0.36	0.38	0.43	0.51	dB	0.567
FMC00136/WP-24	24 Inch	Insertion Loss (Typ.)	0.38	0.41	0.46	0.56	0.71	dB	0.6
FMC00136/WP-36	36 Inch	Insertion Loss (Typ.)	0.42	0.47	0.54	0.69	0.92	dB	0.633
FMC00136/WP-48	48 Inch	Insertion Loss (Typ.)	0.46	0.52	0.62	0.82	1.12	dB	0.666
FMC00136/WP-60	60 Inch	Insertion Loss (Typ.)	0.5	0.58	0.7	0.95	1.32	dB	0.699

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.2 dB
Loss due to Connector 2:	0.1 dB
Base Weight:	0.567 pounds
Additional Weight per Inch:	0.00275 pounds

#### Mechanical Specifications

##### Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.567 lbs [257.19 g]

##### Cable

Cable Type	LMR-240
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE
Jacket Diameter	0.24 in [6.1 mm]
One Time Minimum Bend Radius	0.75 in [19.05 mm]
Repeated Minimum Bend Radius	2.5 in [63.5 mm]
Bending Moment	0.25 lbs-ft [0.34 N-m]
Flat Plate Crush	20 lbs/in [0.36 Kg/mm]

## Low Loss RA SMA Male to SMA Male Weatherproof Cable LMR-240 Coax with LF Solder



### FMC00136/WP

Tensile Strength 80 lbs [36.29 Kg]

#### Connectors

Description	Connector 1	Connector 2
Type	SMA Male Right Angle	SMA Male
Option	Weatherproof Boot	Weatherproof Boot
Specification	MIL-STD-348	
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Straight
Contact Material and Plating	Brass/Phosphor Bronze, Gold	Brass, Gold
Contact Plating Specification	50 µin minimum	
Dielectric Type	Teflon	PTFE
Body Material and Plating	Brass, Tri-Metal	Brass, Gold
Body Plating Specification	80 µin minimum	
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Gold
Coupling Nut Plating Specification	80 µin minimum	
Boot Material	Silicone	Silicone

#### Environmental Specifications

Operating Range Temperature -40 to +85 deg C  
Ingress Protection (IP) Rating IP68

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:  
Values at 25°C, sea level.

## Low Loss RA SMA Male to SMA Male Weatherproof Cable LMR-240 Coax with LF Solder



### FMC00136/WP

#### Typical Performance Data

#### How to Order

Part Number Configuration:

**FMC00136/WP**

**- xx**

**uu**

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: FMC00136/WP-12 = 12 inches long cable  
FMC00136/WP-100cm = 100 cm long cable

Low Loss RA SMA Male to SMA Male Weatherproof Cable LMR-240 Coax with LF Solder from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Low Loss RA SMA Male to SMA Male Weatherproof Cable LMR-240 Coax with LF Solder FMC00136/WP](#)

URL: <https://www.fairviewmicrowave.com/low-loss-ra-sma-male-to-sma-male-weatherproof-cable-lmr-240-coax-with-lf-solder-fmc00136-wp-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMC00136/WP CAD Drawing
Low Loss RA SMA Male to SMA Male Weatherproof Cable LMR-240 Coax with LF Solder

