

Low Loss SMA Male to RA N Male Cable LMR-195 Coax

FMC00158



Configuration

- Connector 1: SMA Male
- Connector 2: N Male Right Angle
- Cable Type: LMR-195
- Coax Flex Type: Flexible

Features

- Max Frequency 1 GHz
- Shielding Effectivity > 90 dB
- 80% Phase Velocity
- Double Shielded
- PE Jacket

Applications

- General Purpose
- Laboratory Use

Description

The SMA male to RA type N male cable using LMR-195 coax, part number FMC00158, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to type N cable assembly has a male to male gender configuration with 50 ohm flexible LMR-195 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC00158 SMA male to type N male cable assembly operates to 1 GHz. The right angle type N interface on the LMR-195 cable allows for easier connections in tight spaces. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.4:1	
Velocity of Propagation		80		%
RF Shielding	90			dB
Group Delay		1.27 [4.17]		ns/ft [ns/m]
Capacitance		25.4 [83.33]		pF/ft [pF/m]
Inductance		0.064 [0.21]		uH/ft [uH/m]
DC Resistance Inner Conductor		7.6 [24.93]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		4.9 [16.08]		Ohms/1000ft [Ohms/Km]
Jacket Spark			3,000	Vrms

Specifications by Frequency

Low Loss SMA Male to RA N Male Cable LMR-195 Coax



FMC00158

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	50	100	250	500	1000	MHz	
FMC00158	Custom Lengths Available	Insertion Loss (Typ.)	0.03	0.03	0.057	0.081	0.116	dB/ft	
			0.09	0.12	0.19	0.27	0.39	dB/m	
FMC00158-12	12 inch	Insertion Loss (Typ.)	0.33	0.34	0.36	0.39	0.42	dB	0.171
FMC00158-24	24 inch	Insertion Loss (Typ.)	0.35	0.37	0.42	0.47	0.54	dB	0.194
FMC00158-36	36 inch	Insertion Loss (Typ.)	0.38	0.41	0.48	0.55	0.65	dB	0.216
FMC00158-48	48 inch	Insertion Loss (Typ.)	0.4	0.44	0.53	0.63	0.77	dB	0.238
FMC00158-60	60 inch	Insertion Loss (Typ.)	0.43	0.47	0.59	0.71	0.88	dB	0.26

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1 dB
Loss due to Connector 2:	0.2 dB
Base Weight:	0.171 pounds
Additional Weight per Inch:	0.00184 pounds

Mechanical Specifications

Cable Assembly

Weight	0.171 lbs [77.56 g]
--------	---------------------

Cable

Cable Type	LMR-195
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.195 in [4.95 mm]
One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	2 in [50.8 mm]
Bending Moment	0.2 lbs-ft [0.27 N-m]
Flat Plate Crush	15 lbs/in [0.27 Kg/mm]
Tensile Strength	40 lbs [18.14 Kg]

Low Loss SMA Male to RA N Male Cable LMR-195 Coax

FMC00158



Connectors

Description	Connector 1	Connector 2
Type	SMA Male	N Male Right Angle
Specification		MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	ASTM B488	
Dielectric Type	PTFE	Teflon
Body Material and Plating	Passivated Stainless Steel	Brass, Nickel
Coupling Nut Material and Plating	Passivated Stainless Steel	Brass, Nickel
Hex Size	5/16 Inch	

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Low Loss SMA Male to RA N Male Cable LMR-195 Coax



FMC00158

Typical Performance Data

How to Order

Part Number Configuration:

FMC00158

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length
Base Number

Example: FMC00158-12 = 12 inches long cable
FMC00158-100cm = 100 cm long cable

Low Loss SMA Male to RA N Male Cable LMR-195 Coax from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Low Loss SMA Male to RA N Male Cable LMR-195 Coax FMC00158](#)

URL: <https://www.fairviewmicrowave.com/low-loss-sma-male-to-ra-n-male-cable-lmr-195-coax-fmc00158-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMC00158 CAD Drawing
Low Loss SMA Male to RA N Male Cable LMR-195 Coax

