

Push-On RA SMP Female to BNC Male Cable RG174 Coax in 12 Inch

The RA SMP female push-on to BNC male 12 inch cable using RG174 coax, part number FMC00374-12, from Fairview Microwave is in-stock and ships same day. This Fairview SMP to BNC cable assembly has a female to male gender configuration with 50 ohm flexible RG174 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC00374-12 SMP female to BNC male cable assembly operates to 1 GHz. The right angle SMP interface on the RG174 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		1,000	MHz
VSWR			1.4:1	
Velocity of Propagation		66		%
Capacitance	31.08	[101.97]		pF/ft [pF/m]

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	100	250	500	1,000		MHz
Insertion Loss (Max.)	0.38	0.39	0.4	0.62		dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax used in this assembly. Insertion Loss is estimated as 0.2 dB for the SMP Female connector and 0.1 dB for the BNC Male connector.

Mechanical Specifications

Cable Assembly

Length*	12 in [304.8 mm]
Diameter	0.571 in [14.5 mm]

Cable

Cable Type	RG174
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel
Dielectric Type	PE
Number of Shields	1
Shield Layer 1	Tinned Copper Braid
Jacket Material	PVC, Black
Jacket Diameter	0.11 in [2.79 mm]



Configuration:

- Push-OnSMP Female Right Angle
- BNC Male
- RG174

Features:

- Max Frequency 1 GHz
- 66% Phase Velocity
- PVC Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Connectors

Description	Connector 1	Connector 2
Type	SMP Female	BNC Male
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Connection Method	Push-On	
Contact Material & Plating	Beryllium Copper, Gold	Brass, Gold
Contact Plating Spec.	30µ in. minimum	50 µin minimum
Dielectric Type	PTFE	PTFE
Outer Cond Material & Plating	Beryllium Copper, Gold	
Outer Cond Plating Spec.	3µ in. minimum	
Body Material & Plating	Brass, Gold	Brass, Nickel
Body Plating Spec.	3µ in. minimum	100 µin minimum
Coupling Nut Material & Plating		Brass, Nickel
Coupling Nut Plating Spec.		100 µin minimum

Environmental Specifications

Temperature

Operating Range -40 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

How to Order

Part Number Configuration:

FMC00374 - xx uu

cm = Centimeters
 <blank> = Inches

Length

Example: FMC00374-12 = 12 inches long cable
 FMC00374-100cm = 100 cm long cable

Push-On RA SMP Female to BNC Male Cable RG174 Coax in 12 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [Push-On RA SMP Female to BNC Male Cable RG174 Coax in 12 Inch FMC00374-12](#)

URL: <https://www.fairviewmicrowave.com/ra-smp-female-bnc-male-cable-rg174-coax-fmc00374-12-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/14/2020	SELLIS

LENGTH MEASURED FROM CONTACT TO CONTACT

2X HEAT SHRINK

RG174

FAREVIEW MICROWAVE
FMC00374
(SEE NOTE 1)

FAREVIEW MICROWAVE
FMC00374
(SEE NOTE 1)

SMP FEMALE
RIGHT ANGLE
PUSH-ON

BNC MALE

NOTES:

1. CABLES 36" AND UNDER HAVE 1 LABEL CENTERED.
CABLES OVER 36" HAVE 2 LABELS, ONE AT EACH
END 6.0" FROM THE END OF THE CONNECTOR.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT
ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

<div><div><div></div><div></div><div></div><div></div></div><div><div>Fairview Microwave™</div><div>an INFINITE brand</div></div></div>	<div>UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS</div> <div>TOLERANCES: CABLE LENGTH (L) TOLERANCES:</div> <div><div><div>.X = ±.2 [.51]</div><div>.XX = ±.02 [.51]</div><div>.XXX = ±.005 [.13]</div></div><div><div>FRACTIONS ± 1/32</div><div>ANGLES ± 1°</div></div></div> <div><div>L ≤ 12 [305] = +1 [25] / -0</div><div>12 [305] < L ≤ 60 [1524] = +2 [51] / -0</div><div>60 [1524] < L ≤ 120 [3048] = +4 [102] / -0</div><div>120 [3048] < L ≤ 300 [7620] = +6 [152] / -0</div><div>300 [7620] < L = +5%L / -0</div></div>
---	---

THIRD-ANGLE PROJECTION

THE INFORMATION AND
DESIGN IN THIS DOCUMENT
IS THE PROPERTY OF
FAIRVIEW MICROWAVE CORPORATION.
ALL RIGHTS RESERVED.

T-Rev.D