

## FMC00498 DATA SHEET

# SMA Male to BNC Male Cable LMR-240-UF Coax with Heat Shrink

The SMA male to BNC male cable using LMR-240-UF coax, part number FMC00498, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to BNC cable assembly has a male to male gender configuration with 50 ohm flexible LMR-240-UF coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC00498 SMA male to BNC male cable assembly operates to 4 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

#### **Electrical Specifications**

Description	M	1in	T	ур	Max	U	nits	
Frequency Range	Γ	OC			4		GHz	
VSWR					1.4:1			
Velocity of Propagation			8	34			%	
RF Shielding	(	90					dB	
Group Delay			1.21	[3.97]		ns/ft	[ns/n	<u>1]</u>
Capacitance			24.2	[79.4]		pF/ft	[pF/n	<u>1]</u>
Inductance			0.06	[0.2]		uH/ft	[uH/r	<u>n]</u>
DC Resistance Inner Conductor			4.28 [	[14.04]		Ω/100	Oft [Ω/l	(m)
DC Resistance Outer Conductor			3.89 [	[12.76]		Ω/100	Oft [Ω/l	(m)
Operating Voltage (DC)					1,000	,	Vdc	
Dielectric Withstanding \	/oltage (DC)				1,500	,	Vdc	
Jacket Spark					5,000	V	'rms	
Input Power (Peak)					5.6	K۱	Natts	

#### **Performance by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	4	GHz
Insertion Loss (Typ.)	0.02	0.04	0.06	0.09	0.19	dB/ft
	0.07	0.13	0.2	0.3	0.62	dB/m

#### **Electrical Specification Notes:**

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated 0.1 dB for the straight connector and 0.1\*SQRT(FGHz) dB for the straight connector.

### **Mechanical Specifications**

**Cable Assembly** 

Diameter

0.58 in [14.73 mm]



## **Configuration:**

- SMA Male
- BNC Male
- LMR-240-UF

#### Features:

- Max Frequency 4 GHz
- Shielding Effectivity > 90 dB
- 84% Phase Velocity
- · Double Shielded
- TPE Jacket

## **Applications:**

- General Purpose
- · Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





**Cable** 

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields

LMR-240-UF
50 Ohms
Stranded
Copper
PE (F)

Shield Layer 1 Aluminum Tape
Shield Layer 2 Tinned Copper Braid
Jacket Material TPE, Black

Jacket Diameter 0.24 in [6.1 mm]

One Time Minimum Band Badius 0.75 in [10.05 n

One Time Minimum Bend Radius

Repeated Minimum Bend Radius

Bending Moment
Flat Plate Crush
Tensile Strength

0.75 in [19.05 mm]
2.5 in [63.5 mm]
0.13 lbs-ft [0.18 N-m]
13 lbs/in [0.23 Kg/mm]
80 lbs [36.29 Kg]

#### **Connectors**

Description	Connector 1	Connector 2			
Туре	SMA Male	BNC Male			
Specification	MIL-STD-348				
Impedance	50 Ohms	50 Ohms			
Contact Material & Plating	Beryllium Copper, G	old Brass, Gold			
Contact Plating Spec.	ASTM B488				
Dielectric Type	PTFE	PTFE			
Outer Cond Material & Plati	ng Passivated Stainless Stee	el, Gold Brass, Tri-Metal			
Body Material & Plating	Passivated Stainless Steel, Gold Brass, Tri-Metal				
Body Plating Spec. SAE-AMS-2700					
Coupling Nut Material & Plating Passivated Stainless Steel					
Coupling Nut Plating Spec.	. SAE-AMS-2700				

## **Environmental Specifications**

**Temperature**Operating Range
Storage Range

-40 to +85 deg C
+70 to +85 deg C

**Compliance Certifications** (see product page for current document)

## **Plotted and Other Data**

Notes:

#### **How to Order**

Part Number Configuration:

FMC00498 - xx uu

cm = Centimeters
<black> = Inches

Length

Example: FMC00498-12 = 12 inches long cable

FMC00498-100cm = 100 cm long cable





SMA Male to BNC Male Cable LMR-240-UF Coax with Heat Shrink from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: SMA Male to BNC Male Cable LMR-240-UF Coax with Heat Shrink FMC00498

URL: https://www.fairviewmicrowave.com/sma-male-bnc-male-cable-lmr240uf-coax-fmc00498-p.aspx







