

Low Loss SMB Plug to BNC Male Cable LMR-100A-UF Coax in 50 cm

The SMB plug to BNC male 50 cm cable using LMR-100A-UF coax, part number FMC00913-50CM, from Fairview Microwave is in-stock and ships same day. This Fairview SMB to BNC cable assembly has a plug to male gender configuration with 50 ohm flexible LMR-100A-UF coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC00913-50CM SMB plug to BNC male cable assembly operates to 3 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		3	GHz
VSWR			1.5:1	
Velocity of Propagation		66		%
RF Shielding	90			dB
Group Delay		1.54 [5.05]		ns/ft [ns/m]
Capacitance		30.8 [101.05]		pF/ft [pF/m]
Inductance		0.077 [0.25]		uH/ft [uH/m]
DC Resistance Inner Conductor		81 [265.75]		Ω /1000ft [Ω /Km]
DC Resistance Outer Conductor		9.5 [31.17]		Ω /1000ft [Ω /Km]
Jacket Spark			2,000	Vrms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.32	0.39	0.48	0.6	0.92	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Length*	19.68 in [499.87 mm]
Weight	0.043 lbs [19.5 g]

Cable

Cable Type	LMR-100A-UF
Impedance	50 Ohms



Configuration:

- SMB Plug
- BNC Male
- LMR-100A-UF

Features:

- Max Frequency 3 GHz
- Shielding Effectivity > 90 dB
- 66% Phase Velocity
- Double Shielded
- TPE Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper
Jacket Material	TPE, Black
Jacket Diameter	0.11 in [2.79 mm]

One Time Minimum Bend Radius	0.25 in [6.35 mm]
Repeated Minimum Bend Radius	1 in [25.4 mm]
Bending Moment	0.1 lbs-ft [0.14 N-m]
Flat Plate Crush	10 lbs/in [0.18 Kg/mm]
Tensile Strength	15 lbs [6.8 Kg]

Connectors

Description	Connector 1	Connector 2
Type	SMB Plug	BNC Male
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Beryllium Copper, Gold	Brass, Gold
Contact Plating Spec.	30 µin minimum	50 µin minimum
Dielectric Type	PTFE	PTFE
Body Material & Plating	Brass, Gold	Brass, Nickel
Body Plating Spec.	3 µin minimum	100 µin minimum
Coupling Nut Material & Plating		Brass, Nickel
Coupling Nut Plating Spec.		100 µin minimum

Environmental Specifications

Temperature

Operating Range -40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMC00913 - xx uu

_____ cm = Centimeters
 _____ <blank> = Inches
 _____ Length

Example: FMC00913-12 = 12 inches long cable
 FMC00913-100cm = 100 cm long cable

Low Loss SMB Plug to BNC Male Cable LMR-100A-UF Coax in 50 cm from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: [Low Loss SMB Plug to BNC Male Cable LMR-100A-UF Coax in 50 cm FMC00913-50CM](https://www.fairviewmicrowave.com/low-loss-smb-plug-to-bnc-male-cable-lmr-100a-uf-coax-fmc00913-50cm-p.aspx)

URL: <https://www.fairviewmicrowave.com/low-loss-smb-plug-to-bnc-male-cable-lmr-100a-uf-coax-fmc00913-50cm-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/10/2022	AGANWANI



 Fairview Microwave an INFINIT® brand		UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS <table border="1"> <thead> <tr> <th>TOLERANCES:</th> <th>CABLE LENGTH (L) TOLERANCES:</th> </tr> </thead> <tbody> <tr> <td> $X = \pm .2$ [.508] FRACTIONS $.XX = \pm .02$ [.51] $\pm 1/32$ $.XXX = \pm .005$ [.13] ANGLES $\pm 1^\circ$ </td> <td> $L \leq 12$ [305] = ± 1 [25] / -0 12 [305] $< L \leq 60$ [1524] = ± 2 [51] / -0 60 [1524] $< L \leq 120$ [3048] = ± 4 [102] / -0 120 [3048] $< L \leq 300$ [7620] = ± 6 [152] / -0 300 [7620] $< L = +5\%$ L / -0 </td> </tr> </tbody> </table>		TOLERANCES:	CABLE LENGTH (L) TOLERANCES:	$X = \pm .2$ [.508] FRACTIONS $.XX = \pm .02$ [.51] $\pm 1/32$ $.XXX = \pm .005$ [.13] ANGLES $\pm 1^\circ$	$L \leq 12$ [305] = ± 1 [25] / -0 12 [305] $< L \leq 60$ [1524] = ± 2 [51] / -0 60 [1524] $< L \leq 120$ [3048] = ± 4 [102] / -0 120 [3048] $< L \leq 300$ [7620] = ± 6 [152] / -0 300 [7620] $< L = +5\%$ L / -0	THIRD-ANGLE PROJECTION  THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION ALL RIGHTS RESERVED.	
TOLERANCES:	CABLE LENGTH (L) TOLERANCES:								
$X = \pm .2$ [.508] FRACTIONS $.XX = \pm .02$ [.51] $\pm 1/32$ $.XXX = \pm .005$ [.13] ANGLES $\pm 1^\circ$	$L \leq 12$ [305] = ± 1 [25] / -0 12 [305] $< L \leq 60$ [1524] = ± 2 [51] / -0 60 [1524] $< L \leq 120$ [3048] = ± 4 [102] / -0 120 [3048] $< L \leq 300$ [7620] = ± 6 [152] / -0 300 [7620] $< L = +5\%$ L / -0								
TITLE Low Loss SMB Plug to BNC Male Cable LMR-100A-UF Coax in 50 cm		ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.		SHEET 1 OF 1 SCALE N/A					
SIZE A	CAGE CODE 3FKR5	DRAWN BY BPUCHASKI	ITEM NO. FMC00913	REV A					