

## N Male to N Male Cable RG-142 Coax in 6 Inch with LF Solder

The type N male to type N male 6 inch cable using RG-142 coax, part number FMC0101143LF-06, from Fairview Microwave is in-stock and ships same day. This Fairview type N to type N cable assembly has a male to male gender configuration with 50 ohm flexible RG-142 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0101143LF-06 type N male to type N male cable assembly operates to 8 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

| Description             | Min   | Typ     | Max    | Units        |
|-------------------------|-------|---------|--------|--------------|
| Frequency Range         | DC    |         | 8      | GHz          |
| VSWR                    |       |         | 1.35:1 |              |
| Velocity of Propagation |       | 70      |        | %            |
| Capacitance             | 29.39 | [96.42] |        | pF/ft [pF/m] |

### Mechanical Specifications

#### Cable Assembly

|         |                     |
|---------|---------------------|
| Length* | 6 in [152.4 mm]     |
| Weight  | 0.177 lbs [80.29 g] |

#### Cable

|                                      |                            |
|--------------------------------------|----------------------------|
| Cable Type                           | RG-142                     |
| Impedance                            | 50 Ohms                    |
| Inner Conductor Type                 | Solid                      |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver  |
| Dielectric Type                      | PTFE                       |
| Number of Shields                    | 2                          |
| Shield Layer 1                       | Silver Plated Copper Braid |
| Shield Layer 2                       | Silver Plated Copper Braid |
| Jacket Material                      | FEP, Tan                   |
| Jacket Diameter                      | 0.195 in [4.95 mm]         |



### Configuration:

- N Male
- N Male
- RG-142

### Features:

- Max Frequency 8 GHz
- 70% Phase Velocity
- Double Shielded
- FEP Jacket

### Applications:

- General Purpose
- Laboratory Use

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

## Connectors

| Description                | Connector 1   | Connector 2   |
|----------------------------|---------------|---------------|
| Type                       | N Male        | N Male        |
| Configuration              | Straight      | Straight      |
| Impedance                  | 50 Ohms       | 50 Ohms       |
| Contact Material & Plating | Brass, Gold   | Brass, Gold   |
| Contact Plating Spec.      | MIL-G-45204   | MIL-G-45204   |
| Dielectric Type            | PTFE          | PTFE          |
| Body Material & Plating    | Brass, Nickel | Brass, Nickel |
| Body Plating Spec.         | QQ-N-290      | QQ-N-290      |

## Environmental Specifications

### Temperature

Operating Range -55 to +200 deg C

## Compliance Certifications (see [product page](#) for current document)

## Plotted and Other Data

Notes:

## How to Order

Part Number Configuration: **FMC0101143LF - xx uu**

cm = Centimeters  
 <blank> = Inches

Length

Example: FMC0101143LF-12 = 12 inches long cable  
 FMC0101143LF-100cm = 100 cm long cable

N Male to N Male Cable RG-142 Coax in 6 Inch with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [N Male to N Male Cable RG-142 Coax in 6 Inch with LF Solder FMC0101143LF-06](#)

URL: <https://www.fairviewmicrowave.com/standard-n-male-n-male-cable-rg142-coax-fmc0101143lf-06-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

| REVISIONS |                 |            |          |
|-----------|-----------------|------------|----------|
| REV.      | DESCRIPTION     | DATE       | APPROVED |
| B         | INITIAL RELEASE | 02/28/2022 | SRAUTUS  |

LENGTH MEASURED FROM  
CONNECTOR END TO CONNECTOR END

2X SHRINK TUBE,  
GREEN

RG142 COAX

N MALE

N MALE

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

Fairview Microwave

an INFINITE brand

TITLE

N Male to N Male Cable RG-142 Coax in 6 Inch with LF Solder

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

| TOLERANCES:  |        | CABLE LENGTH (L) TOLERANCES: |  |
|--------------|--------|------------------------------|--|
| .X = ±.2     | [.508] | FRACTIONS                    |  |
| .XX = ±.02   | [.51]  | ± 1/32                       |  |
| .XXX = ±.005 | [.13]  | ANGLES ± 1°                  |  |

CABLE LENGTH (L) TOLERANCES:

|                      |                        |
|----------------------|------------------------|
| L ≤ 12               | [305] = +1 [25] / -0   |
| 12 [305] < L ≤ 60    | [1524] = +2 [51] / -0  |
| 60 [1524] < L ≤ 120  | [3048] = +4 [102] / -0 |
| 120 [3048] < L ≤ 300 | [7620] = +6 [152] / -0 |
| 300 [7620] < L       | = +5%L / -0            |

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.

| SIZE | CAGE CODE | DRAWN BY   | ITEM NO.     | REV |
|------|-----------|------------|--------------|-----|
| A    | 3FKR5     | DFRISIELLO | FMC0101143LF | B   |

THIRD-ANGLE PROJECTION

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.

| SHEET | OF |
|-------|----|
| 1     | 1  |

SCALE

N/A