

N Male to SMA Male Cable RG-58 Coax in 6 Inch with LF Solder

The type N male to SMA male 6 inch cable using RG-58 coax, part number FMC0102058LF-06, from Fairview Microwave is in-stock and ships same day. This Fairview type N to SMA cable assembly has a male to male gender configuration with 50 ohm flexible RG-58 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0102058LF-06 type N male to SMA male cable assembly operates to 1 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Min | Typ | Max | Units |
|-------------------------|------|----------|--------|--------------|
| Frequency Range | DC | | 1,000 | MHz |
| VSWR | | | 1.35:1 | |
| Velocity of Propagation | | 66 | | % |
| Capacitance | 30.8 | [101.05] | | pF/ft [pF/m] |

Mechanical Specifications

Cable Assembly

| | |
|---------|---------------------|
| Length* | 6 in [152.4 mm] |
| Weight | 0.085 lbs [38.56 g] |

Cable

| | |
|--------------------------------------|---------------------|
| Cable Type | RG-58 |
| Impedance | 50 Ohms |
| Inner Conductor Type | Solid |
| Inner Conductor Material and Plating | Copper, Tin |
| Dielectric Type | PE |
| Number of Shields | 2 |
| Shield Layer 1 | Tinned Copper Braid |
| Jacket Material | PVC, Black |
| Jacket Diameter | 0.195 in [4.95 mm] |



Configuration:

- N Male
- SMA Male
- RG-58

Features:

- Max Frequency 1 GHz
- 66% Phase Velocity
- Double Shielded
- PVC Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Connectors

| Description | Connector 1 | Connector 2 |
|----------------------------|---------------|------------------|
| Type | N Male | SMA Male |
| Configuration | Straight | Straight |
| Impedance | 50 Ohms | 50 Ohms |
| Contact Material & Plating | Brass, Gold | Brass, Gold |
| Contact Plating Spec. | MIL-G-45204 | 50μ in. minimum |
| Dielectric Type | PTFE | PTFE |
| Body Material & Plating | Brass, Nickel | Brass, Gold |
| Body Plating Spec. | QQ-N-290 | 3μ in. minimum |
| Hex Size | | 5/16 inch |
| Torque | | 4 in-lbs 0.45 Nm |

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration: **FMC0102058LF - xx uu**

cm = Centimeters
 <blank> = Inches

Length

Example: FMC0102058LF-12 = 12 inches long cable
 FMC0102058LF-100cm = 100 cm long cable

N Male to SMA Male Cable RG-58 Coax in 6 Inch with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [N Male to SMA Male Cable RG-58 Coax in 6 Inch with LF Solder FMC0102058LF-06](#)

URL: <https://www.fairviewmicrowave.com/standard-n-male-sma-male-cable-rg58-coax-fmc0102058lf-06-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.