

FMC0202100 DATA SHEET

SMA Male to SMA Male Cable LMR-100 Coax

General purpose flexible LMR-100 cable assemblies are built using high quality connectors and Times Microwaves cable. These cable assemblies are built using double shielded flexible cable providing excellent shielding greater than 90 dB. These general purpose cables are intended for, lab use, equipment interconnect and anywhere that lower insertion loss and greater shielding effectiveness than standard RG type cable is required.

Electrical Specifications

Description	Min	Т	ур	Max	U	Inits		
Frequency Range	DC			2		GHz		
VSWR				1.35:1				
Velocity of Propagation		(56			%		
RF Shielding	90					dB		
Capacitance		30.8 [101.0	5]	pF/ft	: [pF/n	n]	
Inductance		0.077 [0.25]			uH/ft [uH/m]			
DC Resistance Inner Conductor		81 [265.75]			Ω/1000ft [Ω/Km]			
DC Resistance Outer Cor	Conductor		9.5 [31.17]			$\Omega/1000$ ft [$\Omega/$ Km]		

Mechanical Specifications

Cable Assembly

Diameter

Weight

0.315 in [8 mm]

0.02822 lbs [12.8 g]

Cable

Cable Type Impedance

Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type
Number of Shields
Shield Layer 1
Shield Layer 2
Jacket Material

Jacket Diameter

LMR-100A-PVC 50 Ohms Solid Copper PE (F)

Tinned Copper Aluminum Tape

PE, Black

0.195 in [4.95 mm]



Configuration:

- SMA Male
- SMA Male
- LMR-100A-PVC

Features:

- SMA Male to SMA Male
- Times© LMR-100 Flexible Low Loss Coax
- · Heat Shrink Booting
- VoP of 84%
- · Custom lengths available
- .

Applications:

- General Purpose
- Wireless Communications
- Lab Use
- Equipment Interconnect

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Connectors

Description	Connector 1	Connector 2				
ype SMA Male SMA Ma						
Impedance	50 Ohms	50 Ohms				
Configuration	Straight					
Contact Material & Plating	Brass, Gold	Brass, Gold				
Contact Plating Spec.	50μ in. minimum	50μ in. minimum				
Dielectric Type	PTFE	PTFE				
Hex Size	5/16 inch	5/16 inch				
Body Material & Plating	Brass, Gold	Brass, Gold				
Body Plating Spec.	3μ in. minimum	3μ in. minimum				

Environmental Specifications

Temperature

Operating Range


-40 to +85 deg C

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

Plotted and Other Data

Notes:

Typical Performance Data



How to Order

Part Number Configuration:

Example: FMC0202100-12 = 12 inches long cable

FMC0202100-100cm = 100 cm long cable





SMA Male to SMA Male Cable LMR-100 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order


Click the following link to obtain additional part information: SMA Male to SMA Male Cable LMR-100 Coax FMC0202100

URL: http://www.fairviewmicrowave.com/standard-sma-male-sma-male-cable-invalid-alias-coax-fmc0202100-p.aspx

stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.												iired. Unle:		
arising out of the use of any part or documentation.	suitability	of the part	t describ	ed hereir	for any	y particula	r purpose,	and Fair	view M	icrowave	does r	ot assume	any	liability
	arising ou	t of the use	e of any	part or do	ocument	ation.								







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
SMA Male to SMA Male Cable LMR-100 Coax	DWG NO FMC0202100				CAGE CODE 3FKR5		
	CAD FILE 010716	SHEET	SCALE	E N/A	SIZE A	5568	