

Precision 1.85mm Male to 1.85mm Female Cable VNA High Flex Coax in 48 Inch

The 1.85mm male to 1.85mm female 48 inch cable using VNA high flex coax, part number FMC900-48, from Fairview Microwave is in-stock and ships same day. This Fairview 1.85mm to 1.85mm cable assembly has a male to female gender configuration with 50 ohm flexible FM-VNA-HF coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC900-48 1.85mm male to 1.85mm female cable assembly operates to 67 GHz. The triple shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 100 dB. Fairview Microwave's precision VNA test cables with high-flex coax are designed to provide accurate performance up to 67 GHz. The stainless steel, braided armoring provides a rugged and flexible test cable solution that exceeds 100,000 flexure cycles with proper care. Very low insertion loss and VSWR as low as 1.4:1 with phase stability of $\pm 8^\circ$ with flexure give these test cables excellent electrical properties for even the most demanding applications. The rugged connectors also allow up to 5,000 mating cycles when attached with proper care.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		67	GHz
VSWR			1.4:1	
Velocity of Propagation		78		%
RF Shielding	100			dB
Group Delay		1.34 [4.4]		ns/ft [ns/m]
Capacitance		26.5 [86.94]		pF/ft [pF/m]
Input Power (Average)			18	Watts
Phase Stability with Flexure		± 8		Degrees

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	5	10	20	40	67	GHz
Insertion Loss (Max.)	2.32	3.12	4.4	6.2	8.2	dB
Power Handling (Max.)					18	W

Electrical Specification Notes:
Values at 25°C, sea level.

Mechanical Specifications

Cable Assembly

Length*	48 in [121.92 cm]
Weight	0.3315 lbs [150.37 g]



Configuration:

- 1.85mm Male
- 1.85mm Female
- FM-VNA-HF

Features:

- Max Frequency 67 GHz
- Shielding Effectivity > 100 dB
- 78% Phase Velocity
- Triple Shielded
- Phase and Amplitude stable designed for VNA testing
- 1.4:1 VSWR to 67 GHz
- Excellent Amplitude and Phase stability with flexure
- Armored Cable construction is highly flexible
- Non Conductive Nomex outer sleeve
- Serialized test data for each cable assembly
- In stock and ready to ship

Applications:

- General Purpose
- Laboratory Use
- VNA Test Cables
- Probe testing to 67 GHz
- Precision Development testing
- For use in Automated Test Systems

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Cable

Cable Type	FM-VNA-HF
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Number of Shields	3
Shield Layer 1	Silver Plated Copper Tape
Shield Layer 2	Silver Plated Copper Braid
Shield Layer 3	Silver Plated Copper Braid
Jacket Diameter	0.27 in [6.86 mm]

One Time Minimum Bend Radius	1 in [25.4 mm]
Flat Plate Crush	317 lbs/in [5.66 Kg/mm]

Connectors

Description	Connector 1	Connector 2
Type	1.85mm Male	1.85mm Female
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Dielectric Type	ULTEM	ULTEM
Outer Cond Material & Plating		Passivated Stainless Steel
Body Material & Plating	Passivated Stainless Steel	Passivated Stainless Steel
Coupling Nut Material & Plating	Passivated Stainless Steel	
Torque	8 in-lbs 0.9 Nm	

Environmental Specifications
Temperature

Operating Range	-55 to +125 deg C
-----------------	-------------------

Compliance Certifications (see [product page](#) for current document)


Plotted and Other Data

Notes:

- Values at 25°C, sea level.

How to Order

Part Number Configuration:

FMC900 - xx uu



Example: FMC900-12 = 12 inches long cable
 FMC900-100cm = 100 cm long cable

Precision 1.85mm Male to 1.85mm Female Cable VNA High Flex Coax in 48 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: [Precision 1.85mm Male to 1.85mm Female Cable VNA High Flex Coax in 48 Inch FMC900-48](#)

URL: <https://www.fairviewmicrowave.com/precision-1.85mm-male-1.85mm-female-cable-vna-cable-coax-fmc900-48-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	6/2/2020	S.ELLIS



NOTES:

1. WHITE LETTER ON BLACK LABEL.
2. BLACK LETTER ON RED LABEL.
3. CABLE LENGTH (L) TOLERANCES: $\pm 2\%L$.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

TITLE

Precision 1.85mm Male to 1.85mm Female Cable VNA
High Flex Coax in 48 Inch

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

X = $\pm .2$ [.508] FRACTIONS
.XX = $\pm .02$ [.51] $\pm 1/32$
.XXX = $\pm .005$ [.13] ANGLES $\pm 1^\circ$

CABLE LENGTH (L) TOLERANCES:

L ≤ 12 [305] = ± 1 [25] / -0
12 [305] < L ≤ 60 [1524] = ± 2 [51] / -0
60 [1524] < L ≤ 120 [3048] = ± 4 [102] / -0
120 [3048] < L ≤ 300 [7620] = ± 6 [152] / -0
300 [7620] < L = $\pm 5\%L$ / -0

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.

THIRD-ANGLE PROJECTION



THE INFORMATION AND
DESIGN IN THIS DOCUMENT
IS THE PROPERTY OF
FAIRVIEW MICROWAVE CORPORATION.
ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	3FKR5	K.DANG	FMC900	A

T-Rev.D