

## 2.92mm Male to 2.92mm Male Cable FM160FLEX Coax in 36 Inch

The 2.92mm male to 2.92mm male 36 inch cable using FM160FLEX coax, part number FMC2929914-36, from Fairview Microwave is in-stock and ships same day. This Fairview 2.92mm to 2.92mm cable assembly has a male to male gender configuration with 50 ohm flexible FM-160FLEX coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC2929914-36 2.92mm male to 2.92mm male cable assembly operates to 40 GHz. The triple shielding of this Fairview cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		40	GHz
VSWR			1.5:1	
Velocity of Propagation		76		%

### Mechanical Specifications

#### Cable Assembly

Length*	36 in [914.4 mm]
Weight	0.139 lbs [63.05 g]

#### Cable

Cable Type	FM-160FLEX
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PPO
Number of Shields	3
Shield Layer 1	Silver Plated Copper
Shield Layer 2	Aluminum Tape
Shield Layer 3	Silver Plated Copper
Jacket Material	ETFE, Gray
Jacket Diameter	0.16 in [4.06 mm]

One Time Minimum Bend Radius	0.8 in [20.32 mm]
Repeated Minimum Bend Radius	1 in [25.4 mm]
Typical Flex Cycles	10,000



### Configuration:

- 2.92mm Male
- 2.92mm Male
- FM-160FLEX

### Features:

- Max Frequency 40 GHz
- 76% Phase Velocity
- Triple Shielded
- ETFE Jacket

### Applications:

- General Purpose
- Laboratory Use

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

## Connectors

Description	Connector 1	Connector 2
Type	2.92mm Male	2.92mm Male
Configuration	Straight	Straight
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Copper Clad Steel, Gold	Copper Clad Steel, Gold
Dielectric Type	PTFE	PTFE
Body Material & Plating	Passivated Stainless Steel	
Body Plating Spec.	SAE-AMS-2700	
Hex Size	5/16 Inch	5/16 Inch
Torque	8 in-lbs 0.9 Nm	8 in-lbs 0.9 Nm

Mechanical Specification Notes:  
 IEEE-STD-P287. Figure G.4. Except Conductor Tolerances and Contact Retension.

## Environmental Specifications

### Temperature

Operating Range -40 to +85 deg C

## Compliance Certifications (see [product page](#) for current document)

## Plotted and Other Data

Notes:

## How to Order

Part Number Configuration: **FMC2929914 - xx uu**

cm = Centimeters  
 <blank> = Inches  
 Length


Example: FMC2929914-12 = 12 inches long cable  
 FMC2929914-100cm = 100 cm long cable

2.92mm Male to 2.92mm Male Cable FM160FLEX Coax in 36 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [2.92mm Male to 2.92mm Male Cable FM160FLEX Coax in 36 Inch FMC2929914-36](#)

URL: <https://www.fairviewmicrowave.com/2.92mm-male-2.92mm-male-cable-fm160flex-coax-fmc2929914-36-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



<b>FAIRVIEW MICROWAVE INC.</b> ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE 2.92mm Male to 2.92mm Male Cable FM160FLEX Coax in 36 Inch		DWG NO <b>FMC2929914</b>		CAGE CODE <b>3FKR5</b>	
CAD FILE	103114	SHEET	SCALE	N/A	SIZE A 5568