

Plenum Low Loss BNC Male to TNC Male Cable LMR-240-LLPX Coax with Times Microwave Components

FMCA100040




Configuration

- Connector 1: BNC Male
- Connector 2: TNC Male
- Cable Type: LMR-240-LLPX

Features

- Max Frequency 4 GHz
- Shielding Effectivity > 90 dB
- 76% Phase Velocity
- Fluoropolymer Jacket
- 500 Mating Cycles



Applications

- General Purpose
- Laboratory Use

Description

The BNC male to TNC male cable using LMR-240-LLPX coax, part number FMCA100040, from Fairview Microwave is in-stock and ships same day. This Fairview BNC to TNC cable assembly has a male to male gender configuration with 50 ohm LMR-240-LLPX coax. The FMCA100040 BNC male to TNC male cable assembly operates to 4 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz
VSWR			1.4:1	
Velocity of Propagation		76		%
RF Shielding	90			dB
Capacitance		26.7 [87.6]		pF/ft [pF/m]
Inductance		0.067 [0.22]		uH/ft [uH/m]
DC Resistance Inner Conductor		4 [13.12]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		3.9 [12.8]		Ohms/1000ft [Ohms/Km]
Jacket Spark			5,000	Vrms

Specifications by Frequency

Plenum Low Loss BNC Male to TNC Male Cable LMR-240-LLPX Coax with Times Microwave Components



FMCA100040

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	100	250	500	1000	4000	MHz	
FMCA100040	Custom Lengths Available	Insertion Loss (Typ.)	0.023	0.038	0.056	0.079	0.163	dB/ft	
			0.08	0.13	0.19	0.26	0.54	dB/m	
FMCA100040-12	12 Inch	Insertion Loss (Typ.)	0.16	0.19	0.23	0.28	0.47	dB	0.185
FMCA100040-24	24 Inch	Insertion Loss (Typ.)	0.18	0.23	0.29	0.36	0.63	dB	0.221
FMCA100040-36	36 Inch	Insertion Loss (Typ.)	0.21	0.27	0.34	0.44	0.79	dB	0.256
FMCA100040-48	48 Inch	Insertion Loss (Typ.)	0.23	0.31	0.4	0.52	0.96	dB	0.291
FMCA100040-60	60 Inch	Insertion Loss (Typ.)	0.25	0.34	0.46	0.6	1.12	dB	0.326

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1*SQRT(FGHz) dB
 Loss due to Connector 2: 0.1 dB
 Base Weight: 0.185 pounds
 Additional Weight per Inch: 0.4983 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter 0.5 in [12.7 mm]
 Weight 0.185 lbs [83.91 g]

Cable

Cable Type LMR-240-LLPX
 Impedance 50 Ohms
 Inner Conductor Material and Plating Copper
 Dielectric Type PTFE
 Outer Conductor 1 Material and Plating Aluminum Tape
 Jacket Material Fluoropolymer
 Jacket Diameter 0.214 in [5.44 mm]
 One Time Minimum Bend Radius 0.75 in [19.05 mm]
 Repeated Minimum Bend Radius 2.5 in [63.5 mm]
 Flat Plate Crush 85 lbs/in [1.52 Kg/mm]
 Tensile Strength 60 lbs [27.22 Kg]

Plenum Low Loss BNC Male to TNC Male Cable LMR-240-LLPX Coax with Times Microwave Components



FMCA100040

Connectors

Description	Connector 1	Connector 2
Type	BNC Male	TNC Male
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Mating Cycles	500	500
Contact Material and Plating	Beryllium Copper, Gold	Phosphor Bronze, Gold
Contact Plating Specification	50 µin minimum	50 µin minimum
Dielectric Type	PTFE	Teflon
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification	80 µin minimum	80 µin minimum
Coupling Nut Material and Plating		Brass, Tri-Metal
Coupling Nut Plating Specification		80 µin minimum
Torque		20 in-lbs 2.26 Nm

Environmental Specifications

Operating Range Temperature -40 to +125 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Plenum Low Loss BNC Male to TNC Male Cable LMR-240-LLPX Coax with Times Microwave Components



FMCA100040

Typical Performance Data

How to Order

Part Number Configuration: **FMCA100040** **- xx** **uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: FMCA100040-12 = 12 inches long cable
FMCA100040-100cm = 100 cm long cable

Plenum Low Loss BNC Male to TNC Male Cable LMR-240-LLPX Coax with Times Microwave Components from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Plenum Low Loss BNC Male to TNC Male Cable LMR-240-LLPX Coax with Times Microwave Components FMCA100040](#)

URL: <https://www.fairviewmicrowave.com/plenum-low-loss-bnc-male-to-tnc-male-cable-lmr-240-llpx-coax-with-times-microwave-components-fmca100040-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

