

Low PIM 7/16 DIN Male to N Male Weatherproof Cable TCOM-400 Coax with Times Microwave Components




FMCA100112/WP

Configuration

- Connector 1: 7/16 DIN Male
- Connector 2: N Male
- Cable Type: TCOM-400
- Coax Flex Type: Flexible

Features

- Max Frequency 6 GHz
- Low PIM: -155 dBc Max
- Shielding Effectivity > 100 dB
- 85% Phase Velocity
- Double Shielded
- PE Jacket
- 500 Mating Cycles
- Silicone Connector Boot
- IP68 Rated



Applications

- General Purpose
- Laboratory Use
- Low PIM Applications

Description

The Fairview Microwave FMCA100112/WP is a weatherproof low loss cable assembly that comes with 7/16 DIN male connection with weatherproof boot on one end and type N male with weatherproof boot on the other. Fairview Microwave's RF coaxial cable assembly products are designed for typical use, production, laboratory test and measurement, defense/military, aerial antenna towers, etc. The low loss cable has a 50 Ohm impedance and is specifically ready for quicker shipment than most in the industry can provide.

This weatherproof low loss RF cable assembly operates at a maximum frequency of 6 GHz. Our RF cable assembly has a PE jacket with 0.405 inches diameter. The 7/16 DIN male to type N male cable assembly FMCA100112/WP is built with TCOM-400 coax, which has a flexible design. This RF cable assembly with 0.5 inches diameter has copper clad aluminum as cable's inner conducting material and PE (F) dielectric type. The weatherproof boot low loss cable is reusable and can withstand elements including extreme temperature. Additional dimensions, specifications, and CAD drawings for this FMCA100112/WP low loss RF cable are available on our downloadable PDF datasheet.

Fairview Microwave stocks a wide selection of weatherproof low loss cable assemblies that ship the same business day as ordered from our warehouse. Make your online purchase right now to take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the ideal TNC male to type N female cable assembly as per your requirements.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		85		%
RF Shielding	100			dB
Group Delay		1.2 [3.94]		ns/ft [ns/m]

Low PIM 7/16 DIN Male to N Male Weatherproof Cable
TCOM-400 Coax with Times Microwave Components



FMCA100112/WP

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Passive Intermodulation IM3 (2x43dBm Tones) at 850 MHz or 1900 MHz			-155	dBc
Capacitance		23.9 [78.41]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		1.39 [4.56]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		1.47 [4.82]		Ohms/1000ft [Ohms/Km]
Dielectric Withstanding Voltage (DC)			2,500	Vdc
Jacket Spark			8,000	Vrms
Input Power (Peak)			16	KWatts

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
			Frequency					MHz	
FMCA100112/WP	Custom Lengths Available	Insertion Loss (Typ.)	0.021	0.03	0.044	0.072	0.117	dB/ft	
			0.07	0.1	0.15	0.24	0.39	dB/m	
FMCA100112/WP-12	12 Inch	Insertion Loss (Typ.)	0.23	0.23	0.25	0.28	0.32	dB	0.82
FMCA100112/WP-24	24 Inch	Insertion Loss (Typ.)	0.25	0.26	0.29	0.35	0.44	dB	0.9
FMCA100112/WP-36	36 Inch	Insertion Loss (Typ.)	0.27	0.29	0.34	0.42	0.56	dB	0.98
FMCA100112/WP-48	48 Inch	Insertion Loss (Typ.)	0.29	0.32	0.38	0.49	0.67	dB	1.06
FMCA100112/WP-60	60 Inch	Insertion Loss (Typ.)	0.31	0.35	0.42	0.56	0.79	dB	1.14

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB
 Loss due to Connector 2: 0.1 dB
 Base Weight: 0.82 pounds
 Additional Weight per Inch: 0.00666 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter 0.5 in [12.7 mm]
 Weight 0.82 lbs [371.95 g]

Cable

Cable Type TCOM-400
 Impedance 50 Ohms
 Inner Conductor Type Stranded
 Inner Conductor Material and Plating Copper Clad Aluminum
 Dielectric Type PE (F)
 Number of Shields 2
 Shield Layer 1 Silver Plated Copper Braid
 Shield Layer 2 Tinned Copper Braid

Low PIM 7/16 DIN Male to N Male Weatherproof Cable
TCOM-400 Coax with Times Microwave Components



FMCA100112/WP

Jacket Material	PE
Jacket Diameter	0.405 in [10.29 mm]
One Time Minimum Bend Radius	1 in [25.4 mm]
Repeated Minimum Bend Radius	4 in [101.6 mm]
Bending Moment	0.5 lbs-ft [0.68 N-m]
Flat Plate Crush	40 lbs/in [0.71 Kg/mm]
Tensile Strength	160 lbs [72.57 Kg]

Connectors

Description	Connector 1	Connector 2
Type	7/16 DIN Male	N Male
Option	Weatherproof Boot	Weatherproof Boot
Specification	IEC-61169-4	IEC-61169-16
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Mating Cycles	500	500
Contact Material and Plating	Brass, Silver	Brass, Silver
Contact Plating Specification	200 µin minimum	200 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification	80 µin minimum	80 µin minimum
Torque	44.25 in-lbs 5 Nm	44.25 in-lbs 5 Nm
Boot Material	Silicone	Silicone

Environmental Specifications

Operating Range Temperature	-40 to +85 deg C
Ingress Protection (IP) Rating	IP68

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:
Values at 25°C, sea level.


Low PIM 7/16 DIN Male to N Male Weatherproof Cable
TCOM-400 Coax with Times Microwave Components



FMCA100112/WP

Typical Performance Data

How to Order



Example: FMCA100112/WP-12 = 12 inches long cable
FMCA100112/WP-100cm = 100 cm long cable

Low PIM 7/16 DIN Male to N Male Weatherproof Cable TCOM-400 Coax with Times Microwave Components from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Low PIM 7/16 DIN Male to N Male Weatherproof Cable TCOM-400 Coax with Times Microwave Components FMCA100112/WP](#)

URL: <https://www.fairviewmicrowave.com/low-pim-7-16-din-male-to-n-male-weatherproof-cable-tcom-400-coax-with-times-microwave-components-fmca100112-wp-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA100112/WP CAD Drawing

Low PIM 7/16 DIN Male to N Male Weatherproof Cable TCOM-400 Coax with Times Microwave Components

