

Fire Rated Low Loss BNC Male to RA BNC Male Cable TCOM-240-FR Coax With Times Microwave Components




FMCA100164

Configuration

- Connector 1: BNC Male
- Connector 2: BNC Male Right Angle
- Cable Type: TCOM-240-FR
- Coax Flex Type: Flexible

Features

- Max Frequency 4 GHz
- Shielding Effectivity > 100 dB
- 84% Phase Velocity
- Double Shielded
- PE Jacket



Applications

- General Purpose
- Laboratory Use

Description

The BNC male to RA BNC male cable using TCOM-240-FR coax, part number FMCA100164, from Fairview Microwave is in-stock and ships same day. This Fairview BNC to BNC cable assembly has a male to male gender configuration with 50 ohm flexible TCOM-240-FR coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA100164 BNC male to BNC male cable assembly operates to 4 GHz. The right angle BNC interface on the TCOM-240-FR cable allows for easier connections in tight spaces. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 100 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz
VSWR			1.4:1	
Velocity of Propagation		84		%
RF Shielding	100			dB
Group Delay		1.21 [3.97]		ns/ft [ns/m]
Capacitance		24.2 [79.4]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		3.2 [10.5]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		2.06 [6.76]		Ohms/1000ft [Ohms/Km]

Fire Rated Low Loss BNC Male to RA BNC Male Cable TCOM-240-FR Coax With Times Microwave Components



FMCA100164

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Jacket Spark			5,000	Vrms

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	100	250	500	1000	4000	MHz	
FMCA100164	Custom Lengths Available	Insertion Loss (Typ.)	0.019	0.037	0.052	0.076	0.155	dB/ft	
			0.07	0.13	0.18	0.25	0.51	dB/m	
FMCA100164-12	12 inch	Insertion Loss (Typ.)	0.32	0.34	0.36	0.38	0.46	dB	0.177
FMCA100164-24	24 inch	Insertion Loss (Typ.)	0.34	0.38	0.41	0.46	0.61	dB	0.222
FMCA100164-36	36 inch	Insertion Loss (Typ.)	0.36	0.42	0.46	0.53	0.77	dB	0.267
FMCA100164-48	48 inch	Insertion Loss (Typ.)	0.38	0.45	0.51	0.61	0.92	dB	0.312
FMCA100164-60	60 inch	Insertion Loss (Typ.)	0.4	0.49	0.56	0.68	1.08	dB	0.357

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1 dB
Loss due to Connector 2:	0.2 dB
Base Weight:	0.177 pounds
Additional Weight per Inch:	0.00375 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.177 lbs [80.29 g]

Cable

Cable Type	TCOM-240-FR
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.24 in [6.1 mm]
One Time Minimum Bend Radius	0.75 in [19.05 mm]
Repeated Minimum Bend Radius	2.5 in [63.5 mm]
Bending Moment	0.25 lbs-ft [0.34 N-m]
Flat Plate Crush	20 lbs/in [0.36 Kg/mm]
Tensile Strength	80 lbs [36.29 Kg]

Fire Rated Low Loss BNC Male to RA BNC Male Cable TCOM-240-FR Coax With Times Microwave Components



FMCA100164

Connectors

Description	Connector 1	Connector 2
Type	BNC Male	BNC Male Right Angle
Specification	MIL-STD-348	
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Mating Cycles		500
Contact Material and Plating	Brass, Gold	Brass, Gold over nickel
Contact Plating Specification		50 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Tri-Metal
Body Plating Specification		80 µin minimum
Coupling Nut Material and Plating	Brass, Nickel	

Environmental Specifications

Operating Range Temperature -40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Fire Rated Low Loss BNC Male to RA BNC Male Cable TCOM-240-FR Coax With Times Microwave Components



FMCA100164

Typical Performance Data

How to Order

Part Number Configuration: **FMCA100164** **- xx** **uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length
Base Number

Example: FMCA100164-12 = 12 inches long cable
FMCA100164-100cm = 100 cm long cable

Fire Rated Low Loss BNC Male to RA BNC Male Cable TCOM-240-FR Coax With Times Microwave Components from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Fire Rated Low Loss BNC Male to RA BNC Male Cable TCOM-240-FR Coax With Times Microwave Components FMCA100164](#)

URL: <https://www.fairviewmicrowave.com/fire-rated-low-loss-bnc-male-to-ra-bnc-male-cable-tcom-240-fr-coax-with-times-microwave-components-fmca100164-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

