

Low Loss TNC Male to TNC Female Bulkhead Cable LMR-195-UF Coax

FMCA100231



Configuration

- Connector 1: TNC Male
- Connector 2: TNC Female Bulkhead
- Cable Type: LMR-195-UF
- Coax Flex Type: Flexible

Features

- Max Frequency 4 MHz
- Shielding Effectivity > 90 dB
- 74% Phase Velocity
- Double Shielded
- TPE Jacket

Applications

- General Purpose
- Laboratory Use

Description

The TNC male to TNC female bulkhead cable using LMR-195-UF coax, part number FMCA100231, from Fairview Microwave is in-stock and ships same day. This Fairview TNC to TNC cable assembly has a male to female gender configuration with 50 ohm flexible LMR-195-UF coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA100231 TNC male to TNC female cable assembly operates to 4 MHz. Our RF cable assembly with TNC bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz
VSWR			1.5:1	
Velocity of Propagation		74		%
RF Shielding	90			dB
Group Delay		1.27 [4.17]		ns/ft [ns/m]
Capacitance		25.4 [83.33]		pF/ft [pF/m]
Inductance		0.064 [0.21]		uH/ft [uH/m]
DC Resistance Inner Conductor		9.5 [31.17]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		4.9 [16.08]		Ohms/1000ft [Ohms/Km]
Operating Voltage (AC)			500	Vrms

Low Loss TNC Male to TNC Female Bulkhead Cable LMR-195-UF Coax

FMCA100231



Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Jacket Spark			3,000	Vrms

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	100	250	500	1000	4000	MHz	
FMCA100231	Custom Lengths Available	Insertion Loss (Typ.)	0.042	0.068	0.097	0.132	0.285	dB/ft	
			0.14	0.23	0.32	0.44	0.94	dB/m	
FMCA100231-12	12 Inch	Insertion Loss (Typ.)	0.25	0.27	0.3	0.34	0.49	dB	0.086
FMCA100231-24	24 Inch	Insertion Loss (Typ.)	0.29	0.34	0.4	0.47	0.77	dB	0.107
FMCA100231-36	36 Inch	Insertion Loss (Typ.)	0.33	0.41	0.5	0.6	1.06	dB	0.128
FMCA100231-60	60 Inch	Insertion Loss (Typ.)	0.41	0.54	0.69	0.86	1.63	dB	0.17
FMCA100231-300	300 Inch	Insertion Loss (Typ.)	1.25	1.9	2.63	3.5	7.33	dB	0.59

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB

Loss due to Connector 2: 0.1 dB

Base Weight: 0.086 pounds

Additional Weight per Inch: 0.00175 pounds

Electrical Specification Notes:

Values at 25°C, sea level.

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.086 lbs [39.01 g]

Cable

Cable Type	LMR-195-UF
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper
Dielectric Type	Foam PE
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper
Jacket Material	TPE, Black
Jacket Diameter	0.195 in [4.95 mm]
One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	2 in [50.8 mm]
Bending Moment	0.1 lbs-ft [0.14 N-m]
Flat Plate Crush	10 lbs/in [0.18 Kg/mm]
Tensile Strength	40 lbs [18.14 Kg]

Low Loss TNC Male to TNC Female Bulkhead Cable LMR-195-UF Coax

FMCA100231



Connectors

Description	Connector 1	Connector 2
Type	TNC Male	TNC Female Bulkhead
Specification		MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 µin minimum	30 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 µin minimum	100 µin minimum
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	100 µin minimum	

Environmental Specifications

Operating Range Temperature -40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:
Values at 25°C, sea level.

Low Loss TNC Male to TNC Female Bulkhead Cable LMR-195-UF Coax



FMCA100231

Typical Performance Data

How to Order

Part Number Configuration:

FMCA100231

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: FMCA100231-12 = 12 inches long cable
FMCA100231-100cm = 100 cm long cable

Low Loss TNC Male to TNC Female Bulkhead Cable LMR-195-UF Coax from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Low Loss TNC Male to TNC Female Bulkhead Cable LMR-195-UF Coax FMCA100231](#)

URL: <https://www.fairviewmicrowave.com/low-loss-tnc-male-to-tnc-female-bulkhead-cable-lmr-195-uf-coax-fm-ca100231-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

