

## 1.85mm Male to 2.92mm Female Bulkhead Cable FM-SR086TB Coax

**FMCA100332**



### Configuration

- Connector 1: 1.85mm Male
- Connector 2: 2.92mm Female Bulkhead
- Cable Type: FM-SR086TB
- Coax Flex Type: Formable

### Features

- 69.5% Phase Velocity

### Applications

- General Purpose
- Laboratory Use

### Description

The 1.85mm male to 2.92mm female bulkhead cable using FM-SR086TB coax, part number FMCA100332, from Fairview Microwave is in-stock and ships same day. This Fairview 1.85mm to 2.92mm cable assembly has a male to female gender configuration with 50 ohm formable FM-SR086TB coax. Fairview Microwave's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. Our RF cable assembly with 2.92mm bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		69.5		%
Capacitance		29 [95.14]		pF/ft [pF/m]
DC Resistance Inner Conductor		65.7 [215.55]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		10.2 [33.46]		Ohms/1000ft [Ohms/Km]

### Mechanical Specifications

#### Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.04 lbs [18.14 g]

#### Cable

Cable Type	FM-SR086TB
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1

## 1.85mm Male to 2.92mm Female Bulkhead Cable FM-SR086TB Coax

**FMCA100332**



Outer Conductor 1 Material and Plating  
Repeated Minimum Bend Radius

Copper, Tin  
0.78 in [19.81 mm]

### Connectors

Description	Connector 1	Connector 2
Type	1.85mm Male	2.92mm Female Bulkhead
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Mating Cycles	500	
Contact Material and Plating	Beryllium Copper, Gold over Nickel	Beryllium Copper, Gold over Nickel
Contact Plating Specification	50 µin minimum	50 µin minimum
Dielectric Type	PEI	
Body Material and Plating	Beryllium Copper, Gold over Nickel	Passivated Stainless Steel
Body Plating Specification	50 µin minimum	SAE-AMS-2700
Coupling Nut Material and Plating	Passivated Stainless Steel	
Coupling Nut Plating Specification	ASTM-A582	
Hex Size	5/16 inch	
Torque	8 in-lbs 0.9 Nm	

### Environmental Specifications

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

## 1.85mm Male to 2.92mm Female Bulkhead Cable FM-SR086TB Coax

### FMCA100332



#### Typical Performance Data

#### How to Order

Part Number Configuration: **FMCA100332**    **- xx**    **uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches

Length

Base Number

Example: FMCA100332-12 = 12 inches long cable  
FMCA100332-100cm = 100 cm long cable

1.85mm Male to 2.92mm Female Bulkhead Cable FM-SR086TB Coax from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [1.85mm Male to 2.92mm Female Bulkhead Cable FM-SR086TB Coax FMCA100332](#)

URL: <https://www.fairviewmicrowave.com/1.85mm-male-to-2.92mm-female-bulkhead-cable-fm-sr086tb-coax-fm-ca100332-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

## 1.85mm Male to 2.92mm Female Bulkhead Cable FM-SR086TB Coax

