1.85mm Male to RA SSMC Plug Cable FM-SR086TB Coax



FMCA100340

Configuration

- Connector 1: 1.85mm Male
- Connector 2: SSMC Plug Right Angle
- Cable Type: FM-SR086TB
- Coax Flex Type: Formable

Features

- Max Frequency 10 GHz
- 69.5% Phase Velocity
- 500 Mating Cycles

Applications

- General Purpose
- Laboratory Use

Description

The 1.85mm male to RA SSMC plug cable using FM-SR086TB coax, part number FMCA100340, from Fairview Microwave is in-stock and ships same day. This Fairview 1.85mm to SSMC cable assembly has a male to plug gender configuration with 50 ohm formable FM-SR086TB coax. Fairview Microwave's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. The FMCA100340 1.85mm male to SSMC plug cable assembly operates to 10 GHz. The right angle SSMC interface on the FM-SR086TB cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		10	GHz
VSWR			1.4:1	
Velocity of Propagation		69.5		%
Capacitance		29 [95.14]		pF/ft [pF/m]
DC Resistance Inner Conductor		65.7 [215.55]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		10.2 [33.46]		Ohms/1000ft [Ohms/Km]

Specifications by Frequency

© 2025 Infinite Electronics, Inc. Fairview Microwave is a registered trademark of Infinite Electronics, Inc.
+1 (866) 839-4711 | sales@fairviewmicrowave.com | fairviewmicrowave.com

1.85mm Male to RA SSMC Plug Cable FM-SR086TB Coax



FMCA100340

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	500	1000	2500	5000	10000	MHz	
FMCA100340	Custom Lengths Available	Insertion Loss (Typ.)	0.15	0.225	0.346	0.549	0.812	dB/ft	
			0.5	0.74	1.14	1.81	2.67	dB/m	
FMCA100340-6	6 In	Insertion Loss (Typ.)	0.31	0.36	0.44	0.57	0.74	dB	0.025
FMCA100340-9	9 In	Insertion Loss (Typ.)	0.35	0.41	0.53	0.71	0.94	dB	0.028
FMCA100340-12	12 In	Insertion Loss (Typ.)	0.38	0.47	0.61	0.84	1.14	dB	0.03
FMCA100340-18	18 In	Insertion Loss (Typ.)	0.46	0.58	0.79	1.12	1.55	dB	0.036
FMCA100340-24	24 In	Insertion Loss (Typ.)	0.53	0.69	0.96	1.39	1.96	dB	0.041

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.04*SQRT(FGHz)	dB
Loss due to Connector 2:	0.2	dB
Base Weight:	0.03	pounds
Additional Weight per Inch:	0.00084	pounds

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.03 lbs [13.61 g]

Cable

Cable Type	FM-SR086TB
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor 1 Material and Plating	Copper, Tin
Repeated Minimum Bend Radius	0.78 in [19.81 mm]

© 2025 Infinite Electronics, Inc. Fairview Microwave is a registered trademark of Infinite Electronics, Inc.

1.85mm Male to RA SSMC Plug Cable FM-SR086TB Coax



FMCA100340

Connectors

Description	Connector 1	Connector 2
Type	1.85mm Male	SSMC Plug Right Angle
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Mating Cycles	500	500
Contact Material and Plating	Beryllium Copper, Gold over Nickel	Beryllium Copper, Gold
Contact Plating Specification	50 µin minimum	MIL-G-45204
Dielectric Type	PEI	Teflon
Body Material and Plating	Beryllium Copper, Gold over Nickel	Brass, Gold
Body Plating Specification	50 µin minimum	MIL-G-45204
Coupling Nut Material and Plating	Passivated Stainless Steel	Beryllium Copper, Gold
Coupling Nut Plating Specification	ASTM-A582	MIL-G-45204
Hex Size	5/16 inch	
Torque	8 in-lbs 0.9 Nm	1.75 in-lbs 0.2 Nm

Environmental Specifications

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

© 2025 Infinite Electronics, Inc. Fairview Microwave is a registered trademark of Infinite Electronics, Inc.
+1 (866) 839-4711 | sales@fairviewmicrowave.com | fairviewmicrowave.com

1.85mm Male to RA SSMC Plug Cable FM-SR086TB Coax



FMCA100340

Typical Performance Data

How to Order

Part Number Configuration: **FMCA100340 - xx uu**

- uu — Unit of Measure:
  - cm = Centimeters
  - <blank> = Inches
- xx — Length
- FMCA100340 — Base Number

Example: FMCA100340-12 = 12 inches long cable
FMCA100340-100cm = 100 cm long cable

1.85mm Male to RA SSMC Plug Cable FM-SR086TB Coax from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 1.85mm Male to RA SSMC Plug Cable FM-SR086TB Coax FMCA100340


URL: https://www.fairviewmicrowave.com/1.85mm-male-to-ra-ssmc-plug-cable-fm-sr086tb-coax-fmca100340-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

© 2025 Infinite Electronics, Inc. Fairview Microwave is a registered trademark of Infinite Electronics, Inc.

FMCA100340 CAD Drawing

1.85mm Male to RA SSMC Plug Cable FM-SR086TB Coax



© 2025 Infinite Electronics, Inc. Fairview Microwave is a registered trademark of Infinite Electronics, Inc.