

1.85mm Male to 2.4mm Female Bulkhead Cable FM-SR086TBJ Coax

FMCA100346



Configuration

- Connector 1: 1.85mm Male
- Connector 2: 2.4mm Female Bulkhead
- Cable Type: FM-SR086TBJ
- Coax Flex Type: Formable

Features

- Max Frequency 20 GHz
- Shielding Effectivity > 100 dB
- 69.5% Phase Velocity
- FEP Jacket

Applications

- General Purpose
- Laboratory Use

Description

The 1.85mm male to 2.4mm female bulkhead cable using FM-SR086TBJ coax, part number FMCA100346, from Fairview Microwave is in-stock and ships same day. This Fairview 1.85mm to 2.4mm cable assembly has a male to female gender configuration with 50 ohm formable FM-SR086TBJ coax. Fairview Microwave's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. The FMCA100346 1.85mm male to 2.4mm female cable assembly operates to 20 GHz. Our RF cable assembly with 2.4mm bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		20	GHz
VSWR			1.4:1	
Velocity of Propagation		69.5		%
RF Shielding	100			dB
Group Delay		1.43 [4.69]		ns/ft [ns/m]
Capacitance		29 [95.14]		pF/ft [pF/m]
DC Resistance Inner Conductor		65.7 [215.55]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		10.2 [33.46]		Ohms/1000ft [Ohms/Km]

Specifications by Frequency

1.85mm Male to 2.4mm Female Bulkhead Cable FM-SR086TBJ Coax

FMCA100346



Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	1000	2000	4500	9000	20000	MHz	
FMCA100346	Custom Lengths Available	Insertion Loss (Typ.)	0.225	0.306	0.508	0.759	1.2	dB/ft	
			0.74	1.01	1.67	2.5	3.94	dB/m	
FMCA100346-6	6 In	Insertion Loss (Typ.)	0.26	0.31	0.44	0.6	0.88	dB	0.04
FMCA100346-9	9 In	Insertion Loss (Typ.)	0.31	0.39	0.57	0.79	1.18	dB	0.045
FMCA100346-12	12 In	Insertion Loss (Typ.)	0.37	0.47	0.7	0.98	1.48	dB	0.05
FMCA100346-18	18 In	Insertion Loss (Typ.)	0.48	0.62	0.95	1.36	2.08	dB	0.061
FMCA100346-24	24 In	Insertion Loss (Typ.)	0.59	0.77	1.21	1.74	2.68	dB	0.071

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.04*SQRT(FGHz) dB
 Loss due to Connector 2: 0.1 dB
 Base Weight: 0.05 pounds
 Additional Weight per Inch: 0.00167 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter 0.5 in [12.7 mm]
 Weight 0.05 lbs [22.68 g]

Cable

Cable Type FM-SR086TBJ
 Impedance 50 Ohms
 Inner Conductor Type Solid
 Inner Conductor Material and Plating Copper Clad Steel, Silver
 Dielectric Type PTFE
 Number of Shields 1
 Outer Conductor 1 Material and Plating Tinned Copper Composite Braid
 Jacket Material FEP, Black
 Jacket Diameter 0.105 in [2.67 mm]
 One Time Minimum Bend Radius 0.5 in [12.7 mm]
 Repeated Minimum Bend Radius 0.787 in [19.99 mm]

1.85mm Male to 2.4mm Female Bulkhead Cable FM-SR086TBJ Coax

FMCA100346



Connectors

Description	Connector 1	Connector 2
Type	1.85mm Male	2.4mm Female Bulkhead
Specification	IEEE-STD-P287	
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Mating Cycles	500	
Contact Material and Plating	Beryllium Copper, Gold over Nickel	Beryllium Copper, Gold over Nickel
Contact Plating Specification	50 µin minimum	50 µin minimum
Dielectric Type	PEI	PEI
Body Material and Plating	Beryllium Copper, Gold over Nickel	Passivated Stainless Steel
Body Plating Specification	50 µin minimum	SAE-AMS-2700
Coupling Nut Material and Plating	Passivated Stainless Steel	
Coupling Nut Plating Specification	ASTM-A582	
Hex Size	5/16 inch	
Torque	8 in-lbs 0.9 Nm	

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

1.85mm Male to 2.4mm Female Bulkhead Cable FM-SR086TBJ Coax



FMCA100346

Typical Performance Data

How to Order

Part Number Configuration: **FMCA100346** **- xx** **uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: FMCA100346-12 = 12 inches long cable
FMCA100346-100cm = 100 cm long cable

1.85mm Male to 2.4mm Female Bulkhead Cable FM-SR086TBJ Coax from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [1.85mm Male to 2.4mm Female Bulkhead Cable FM-SR086TBJ Coax FMCA100346](#)

URL: <https://www.fairviewmicrowave.com/1.85mm-male-to-2.4mm-female-bulkhead-cable-fm-sr086tbj-coax-fm-ca100346-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA100346 CAD Drawing
1.85mm Male to 2.4mm Female Bulkhead Cable FM-SR086TBJ Coax

