

## Low Loss SMA Male to SMA Female Cable LMR-100 Coax

### FMCA10037



#### Configuration

- Connector 1: SMA Male
- Connector 2: SMA Female
- Cable Type: LMR-100A
- Coax Flex Type: Flexible

#### Features

- Max Frequency 6 GHz
- Shielding Effectivity > 90 dB
- 66% Phase Velocity
- Double Shielded
- PVC Jacket

#### Applications

- General Purpose
- Laboratory Use

#### Description

The SMA male to SMA female cable using LMR-100 coax, part number FMCA10037, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SMA cable assembly has a male to female gender configuration with 50 ohm flexible LMR-100A coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA10037 SMA male to SMA female cable assembly operates to 6 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		66		%
RF Shielding	90			dB
Group Delay		1.54 [5.05]		ns/ft [ns/m]
Capacitance		30.8 [101.05]		pF/ft [pF/m]
Inductance		0.077 [0.25]		uH/ft [uH/m]
DC Resistance Inner Conductor		81 [265.75]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		9.5 [31.17]		Ohms/1000ft [Ohms/Km]
Jacket Spark			2,000	Vrms

#### Specifications by Frequency

## Low Loss SMA Male to SMA Female Cable LMR-100 Coax



### FMCA10037

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	250	500	1000	2500	6000	MHz	
FMCA10037	Custom Lengths Available	Insertion Loss (Typ.)	0.12	0.17	0.24	0.4	0.64	dB/ft	
			0.38	0.55	0.79	1.31	2.11	dB/m	
FMCA10037-24	24 Inch	Insertion Loss (Typ.)	0.58	0.68	0.83	1.15	1.64	dB	0.046
FMCA10037-36	36 Inch	Insertion Loss (Typ.)	0.7	0.85	1.07	1.55	2.28	dB	0.055
FMCA10037-48	48 Inch	Insertion Loss (Typ.)	0.81	1.01	1.31	1.95	2.92	dB	0.064
FMCA10037-100CM	100 CM	Insertion Loss (Typ.)	0.73	0.9	1.14	1.66	2.46	dB	0.058
FMCA10037-200CM	200 CM	Insertion Loss (Typ.)	1.11	1.44	1.93	2.97	4.56	dB	0.087

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.25 dB
Loss due to Connector 2:	0.1 dB
Base Weight:	0.037 pounds
Additional Weight per Inch:	0.07833 pounds

## Mechanical Specifications

### Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.037 lbs [16.78 g]

### Cable

Cable Type	LMR-100A
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel
Dielectric Type	PE
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PVC, Black
Jacket Diameter	0.11 in [2.79 mm]
One Time Minimum Bend Radius	0.25 in [6.35 mm]
Repeated Minimum Bend Radius	1 in [25.4 mm]
Bending Moment	0.1 lbs-ft [0.14 N-m]
Flat Plate Crush	10 lbs/in [0.18 Kg/mm]
Tensile Strength	15 lbs [6.8 Kg]

## Low Loss SMA Male to SMA Female Cable LMR-100 Coax

**FMCA10037**



### Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SMA Female
Specification		MIL-STD-348
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Mating Cycles		100
Contact Material and Plating	Brass, Gold	Beryllium Copper, Gold
Contact Plating Specification	15 µin minimum	
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating		Brass, Nickel
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	200 µin minimum	
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	200 µin minimum	

### Environmental Specifications

Operating Range Temperature -40 to +85 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

## Low Loss SMA Male to SMA Female Cable LMR-100 Coax



### FMCA10037

#### Typical Performance Data

#### How to Order

Part Number Configuration:

**FMCA10037**

**- xx**

**uu**

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: FMCA10037-12 = 12 inches long cable  
FMCA10037-100cm = 100 cm long cable

Low Loss SMA Male to SMA Female Cable LMR-100 Coax from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Low Loss SMA Male to SMA Female Cable LMR-100 Coax FMCA10037](https://www.fairviewmicrowave.com/low-loss-sma-male-to-sma-female-cable-lmr-100-coax-fmca10037-p.aspx)

URL: <https://www.fairviewmicrowave.com/low-loss-sma-male-to-sma-female-cable-lmr-100-coax-fmca10037-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

