

VITA 67.3 SMPS Female to SMA Female Cable FM-P047HF Coax

FMCA100371




Configuration

- Connector 1: SMPS Female
- Connector 2: SMA Female
- Cable Type: FM-P047HF
- Coax Flex Type: High Flex

Features

- Max Frequency 18 GHz
- Shielding Effectivity > 90 dB
- 70% Phase Velocity
- Double Shielded
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

The SMPS female to SMA female cable using FM-P047HF coax, part number FMCA100371, from Fairview Microwave is in-stock and ships same day. This Fairview SMPS to SMA cable assembly has a female to female gender configuration with 50 ohm high flex FM-P047HF coax. The FMCA100371 SMPS female to SMA female cable assembly operates to 18 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.4:1	
Velocity of Propagation		70		%
RF Shielding	90			dB
Capacitance		29 [95.14]		pF/ft [pF/m]

Specifications by Frequency

VITA 67.3 SMPS Female to SMA Female Cable FM-P047HF Coax



FMCA100371

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	1000	2000	4500	9000	18000	MHz	
FMCA100371	Custom Lengths Available	Insertion Loss (Typ.)	0.35	0.488	0.763	1.107	1.681	dB/ft	
			1.15	1.61	2.51	3.64	5.52	dB/m	
FMCA100371-6	6 In	Insertion Loss (Typ.)	0.38	0.45	0.59	0.76	1.05	dB	0.01
FMCA100371-9	9 In	Insertion Loss (Typ.)	0.47	0.57	0.78	1.04	1.47	dB	0.011
FMCA100371-12	12 In	Insertion Loss (Typ.)	0.55	0.69	0.97	1.31	1.89	dB	0.012
FMCA100371-18	18 In	Insertion Loss (Typ.)	0.73	0.94	1.35	1.87	2.73	dB	0.014
FMCA100371-24	24 In	Insertion Loss (Typ.)	0.9	1.18	1.73	2.42	3.57	dB	0.016

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB
 Loss due to Connector 2: 0.1 dB
 Base Weight: 0.0114 pounds
 Additional Weight per Inch: 0.00034 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter 0.5 in [12.7 mm]
 Weight 0.012 lbs [5.44 g]

Cable

Cable Type FM-P047HF
 Impedance 50 Ohms
 Inner Conductor Type Solid
 Inner Conductor Material and Plating Copper, Silver
 Dielectric Type PTFE
 Number of Shields 2
 Shield Layer 1 Silver Plated Copper Tape
 Shield Layer 2 Silver Plated Copper Braid
 Jacket Material FEP, Blue
 Jacket Diameter 0.06 in [1.52 mm]
 Repeated Minimum Bend Radius 0.1 in [2.54 mm]

VITA 67.3 SMPS Female to SMA Female
Cable FM-P047HF Coax



FMCA100371

Connectors

Description	Connector 1	Connector 2
Type	SMPS Female	SMA Female
Specification		MIL-STD-348
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Specification		MIL-G-45204
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Beryllium Copper, Gold	
Body Material and Plating	Passivated Stainless Steel	Brass, Gold
Body Plating Specification		MIL-G-45204

Environmental Specifications

Operating Range Temperature -65 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

VITA 67.3 SMPS Female to SMA Female Cable FM-P047HF Coax



FMCA100371

Typical Performance Data

How to Order

Part Number Configuration: **FMCA100371** **- xx** **uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: FMCA100371-12 = 12 inches long cable
FMCA100371-100cm = 100 cm long cable

VITA 67.3 SMPS Female to SMA Female Cable FM-P047HF Coax from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [VITA 67.3 SMPS Female to SMA Female Cable FM-P047HF Coax FMCA100371](#)

URL: <https://www.fairviewmicrowave.com/vita-67.3-smps-female-to-sma-female-cable-fm-p047hf-coax-fmca100371-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA100371 CAD Drawing

VITA 67.3 SMPS Female to SMA Female Cable FM-P047HF Coax

