Fairview Microwave
an INFINITE brand

FMCA1053-12
DATA SHEET

UMCX 2.5 Plug to UMCX 2.5 Plug Cable 1.37mm Coax in 12 Inch

The UMCX 2.5 plug to UMCX 2.5 plug 12 inch cable using 1.37mm coax, part number FMCA1053-12, from Fairview Microwave is in-stock and ships same day. This Fairview UMCX 2.5 to UMCX 2.5 cable assembly has a plug to plug gender configuration with 50 ohm flexible 1.37mm coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA1053-12 UMCX 2.5 plug to UMCX 2.5 plug cable assembly operates to 6 GHz. Fairview Microwave's UMCX 2.5 (also known as 2.5mm UMCX) ultra-miniature cable assemblies have a mate connection height of 2.5mm. They are constructed using flexible micro-coax cable and are comparable in design to Hirose U.FL®, IPEX MHF® as well other UMCX connector and cable manufactures. Fairview's other UMCX 2.1, WMCX and HMCX32 1.2 connectors are also available for use on our 0.81mm in-series micro-coax jumpers. These UMCX 2.5 are available in the following coax types; 0.81mm, 1.13mm, 1.37mm, RG178 and RG178-DS.

With operational frequencies up to 6 GHz, these UMCX cables are perfectly suited for wireless communications such as Wi-Fi, Bluetooth, GPS, ZigBee and LTE. These cables offer a small form factor, flexible coax and provide a low profile RF connection perfect for board-to-board connectivity. Fairview's UMCX 2.5 cable assemblies are available from stock in standard lengths and will ship same-day they are ordered. Custom lengths are also available upon request with slightly longer lead times.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Configuration:

- UMCX 2.5 Plug
- UMCX 2.5 Plug
- 1.37mm

Features:

- Max Frequency 6 GHz
- FEP Jacket
- 2.5mm mated assembly height
- Operate from DC to 6 GHz
- 100% RF and Continuity tested
- Compatible with Hirose U.FL and IPEX MHF products
- Small foot print with easy snap on/off mating

Applications:

- General Purpose
- Laboratory Use
- Wireless LAN, Mini PCI
- Mobile Antenna/GPS/Radio Systems
- PDA/PCS/Cellular Handset applications
- Wireless Communications systems (LAN, GSM, PCS, WCDMA, UMTS)

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		6	GHz
VSWR			1.55:1	
Operating Voltage (DC)			300	Vdc

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	6	GHz
Insertion Loss (Typ.) VSWR (Max.)	0.15 1.4:1	0.35 1.4:1	0.53 1.4:1	0.8 1.4:1	1.37 1.55:1	dB
Return Loss (Max.)	15.56	15.56	15.56	15.56	13.32	dB

Mechanical Specifications

Cable Assembly

Length*	12 in [304.8 mm]
Weight	0.01 lbs [4.54 g]

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Copyright © 2020

Cable

Cable Type	1.37mm
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	FEP
Number of Shields	1
Shield Layer 1	Tinned Copper
Outer Conductor Material and Plating	Tinned Copper
Jacket Material	FEP
Jacket Diameter	0.053 in [1.35 mm]

Connectors

Description	Connector 1	Connector 2
Type	UMCX 2.5 Plug	UMCX 2.5 Plug
Impedance	50 Ohms	50 Ohms

Environmental Specifications

Temperature

Operating Range	-55 to +125 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration: **FMCA1053 - xx uu**

- uu: cm = Centimeters; <blank> = Inches
- xx: Length

Example: FMCA1053-12 = 12 inches long cable
FMCA1053-100cm = 100 cm long cable

Copyright © 2020

UMCX 2.5 Plug to UMCX 2.5 Plug Cable 1.37mm Coax in 12 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: UMCX 2.5 Plug to UMCX 2.5 Plug Cable 1.37mm Coax in 12 Inch FMCA1053-12

URL: https://www.fairviewmicrowave.com/umcx-2.5-plug-umcx-2.5-plug-cable-1.37mm-coax-fmca1053-12-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



UMCX connectors are similar to U.FL*
*U.FL is a Registered Trademark of
Hirose Electronic Group

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].				
TITLE UMCX 2.5 Plug to UMCX 2.5 Plug Cable 1.37mm Coax in 12 Inch	DWG NO FMCA1053		CAGE CODE 3FKR5		
	CAD FILE 120814	SHEET	SCALE N/A	SIZE A	150

Copyright © 2020