
N Male to TNC Male Cable TCOM-240 Coax



FMCA10692

Configuration

- Connector 1: N Male
- Connector 2: TNC Male
- Cable Type: TCOM-240
- Coax Flex Type: Flexible



Features

- Max Frequency 6 GHz
- Shielding Effectivity > 100 dB
- 84% Phase Velocity
- Double Shielded
- PE Jacket

Applications

- General Purpose
- Laboratory Use

Description

The type N male to TNC male cable using TCOM-240 coax, part number FMCA10692, from Fairview Microwave is in-stock and ships same day. This Fairview type N to TNC cable assembly has a male to male gender configuration with 50 ohm flexible TCOM-240 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA10692 type N male to TNC male cable assembly operates to 6 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 100 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		84		%
RF Shielding	100			dB
Group Delay		1.21 [3.97]		ns/ft [ns/m]
Capacitance		24.2 [79.4]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		3.2 [10.5]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		2.06 [6.76]		Ohms/1000ft [Ohms/Km]

© 2026 Infinite Electronics, Inc. Fairview Microwave is a registered trademark of Infinite Electronics, Inc.

N Male to TNC Male Cable TCOM-240 Coax



FMCA10692

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Jacket Spark			5,000	Vrms

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	250	500	1000	2500	6000	MHz	
FMCA10692	Custom Lengths Available	Insertion Loss (Typ.)	0.036	0.052	0.075	0.123	0.198	dB/ft	
			0.12	0.18	0.25	0.41	0.65	dB/m	
FMCA10692-6	6 inch	Insertion Loss (Typ.)	0.37	0.4	0.44	0.52	0.65	dB	0.153
FMCA10692-9	9 inch	Insertion Loss (Typ.)	0.38	0.41	0.46	0.56	0.7	dB	0.1605
FMCA10692-12	12 inch	Insertion Loss (Typ.)	0.39	0.43	0.48	0.59	0.75	dB	0.168
FMCA10692-18	18 inch	Insertion Loss (Typ.)	0.41	0.45	0.52	0.65	0.85	dB	0.183
FMCA10692-24	24 inch	Insertion Loss (Typ.)	0.43	0.48	0.55	0.71	0.95	dB	0.198

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1*sqrt(fGHz)	dB
Loss due to Connector 2:	0.3	dB
Base Weight:	0.168	pounds
Additional Weight per Inch:	0.0025	pounds

Mechanical Specifications

Cable Assembly

Width/Diameter	0.81 in [20.57 mm]
Weight	0.168 lbs [76.2 g]

Cable

Cable Type	TCOM-240
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.24 in [6.1 mm]
One Time Minimum Bend Radius	0.75 in [19.05 mm]
Repeated Minimum Bend Radius	2.5 in [63.5 mm]
Bending Moment	0.25 lbs-ft [0.34 N-m]
Flat Plate Crush	20 lbs/in [0.36 Kg/mm]
Tensile Strength	80 lbs [36.29 Kg]

© 2026 Infinite Electronics, Inc. Fairview Microwave is a registered trademark of Infinite Electronics, Inc.
+1 (866) 839-4711 | sales@fairviewmicrowave.com | fairviewmicrowave.com

N Male to TNC Male Cable TCOM-240 Coax



FMCA10692

Connectors

Description	Connector 1	Connector 2
Type	N Male	TNC Male
Specification	MIL-STD-348	
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Mating Cycles		500
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification		50 µin minimum
Dielectric Type	PTFE	Teflon
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification		80 µin minimum
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Plating Specification		80 µin minimum
Torque		8 in-lbs 0.9 Nm

Environmental Specifications

Operating Range Temperature	-40 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

© 2026 Infinite Electronics, Inc. Fairview Microwave is a registered trademark of Infinite Electronics, Inc.
+1 (866) 839-4711 | sales@fairviewmicrowave.com | fairviewmicrowave.com

N Male to TNC Male Cable TCOM-240 Coax



FMCA10692

Typical Performance Data

How to Order

Part Number Configuration: **FMCA10692 - xx uu**

- uu — Unit of Measure:
  - cm = Centimeters
  - <blank> = Inches
- xx — Length
- FMCA10692 — Base Number

Example: FMCA10692-12 = 12 inches long cable
FMCA10692-100cm = 100 cm long cable

N Male to TNC Male Cable TCOM-240 Coax from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: N Male to TNC Male Cable TCOM-240 Coax FMCA10692


URL: https://www.fairviewmicrowave.com/n-male-to-tnc-male-cable-tcom-240-coax-fmca10692-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

© 2026 Infinite Electronics, Inc. Fairview Microwave is a registered trademark of Infinite Electronics, Inc.

FMCA10692 CAD Drawing

N Male to TNC Male Cable TCOM-240 Coax



© 2025 Infinite Electronics, Inc. Fairview Microwave is a registered trademark of Infinite Electronics, Inc.