

Test Probe Pigtail SMA Female to Stripped Lead Cable .047 Copper Tin Plated in 9 Inch

FMCA1186-9



Configuration

- Connector 1: SMA Female
- Connector 2: Stripped Lead
- Cable Type: FM-SR047CUTN
- Coax Flex Type: Semi-Rigid

Features

- Max Frequency 6 GHz
- 100% RF Tested Prior to Final Trim
- 1.35:1 Max VSWR to 6 GHz
- 100% High Pot Tested to 500V
- .047 Diameter Semi-Rigid Coax
- Individually Packed in Protective Tube

Applications

- General Purpose
- Test & Measurement
- Laboratory Use
- RF test lead for measurements up to 6GHz
- Testing of individual function or subsection of an RF circuit board
- Inject signals for test and verification

Description

The 50 ohm pigtail SMA female to stripped lead 9 inch cable using .047 coax, part number FMCA1186-9, from Fairview Microwave is in-stock and ships same day. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA1186-9 SMA female to stripped lead cable assembly operates to 6 GHz. Fairview's semi-rigid test probes are convenient ready-to-use probes designed for use in testing microwave circuits. These probes are constructed of high quality semi-rigid coax and SMA Female connectors. The assemblies come in multiple cable diameters to help when attaching two very fine traces or into tight spaces. There are two versions including straight-cut probe ends for those that would like to customize the dimensions of the center conductor and dielectric dimensions as well as pre-stripped probe ends that are ready for immediate use. Each assembly has been RF tested to ensure VSWR specifications of the assembly are met prior to trimming. Each assembly comes in special packaging to protect the small diameter coax and pre-trimmed probe ends.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.35:1	

Test Probe Pigtail SMA Female to Stripped Lead Cable .047 Copper Tin Plated in 9 Inch

FMCA1186-9



Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Operating Voltage (AC)			500	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	6				GHz
Insertion Loss (Typ.)	0.35	0.6				dB
VSWR (Max.)	1.35:1	1.35:1				

Mechanical Specifications

Cable Assembly

Length	9 in [228.6 mm]
Width/Diameter	0.4 in [10.16 mm]
Weight	0.024 lbs [10.89 g]

Cable

Cable Type	FM-SR047CUTN
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor 1 Material and Plating	Copper, Tin
Outer Conductor Diameter	0.047 in [1.19 mm]
Jacket Material	Tan

Connectors

Description	Connector 1	Connector 2
Type	SMA Female	Stripped Lead
Impedance	50 Ohms	0 Ohms
Configuration	Straight	
Outer Conductor Material and Plating	Brass, Gold	
Body Material and Plating	Brass, Gold	

Environmental Specifications

Operating Range Temperature	+125 deg C
-----------------------------	------------

Test Probe Pigtail SMA Female to Stripped Lead Cable .047 Copper Tin Plated in 9 Inch

FMCA1186-9



Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data

How to Order

Part Number Configuration:

FMCA1186 **- xx** **uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: FMCA1186-12 = 12 inches long cable
FMCA1186-100cm = 100 cm long cable

Test Probe Pigtail SMA Female to Stripped Lead Cable .047 Copper Tin Plated in 9 Inch from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Test Probe Pigtail SMA Female to Stripped Lead Cable .047 Copper Tin Plated in 9 Inch FMCA1186-9](#)

URL: <https://www.fairviewmicrowave.com/test-probe-pigtail-sma-female-stripped-lead-lead-cable-.047-coax-fmca1186-9-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

