

Low Loss SMA Male to N Male Weatherproof Cable LMR-195 Coax with Times Microwave Components



FMCA1079/WP

Configuration

- Connector 1: SMA Male
- Connector 2: N Male
- Cable Type: LMR-195
- Coax Flex Type: Flexible

Features

- Max Frequency 6 GHz
- Shielding Effectivity > 90 dB
- 80% Phase Velocity
- Double Shielded
- PE Jacket
- Silicone Connector Boot
- IP68 Rated

Applications

- General Purpose
- Laboratory Use

Description

The Fairview Microwave FMCA1079/WP is a weatherproof low loss cable assembly that comes with SMA male connection with weatherproof boot on one end and type N male with weatherproof boot on the other. Fairview Microwave's RF coaxial cable assembly products are designed for typical use, production, laboratory test and measurement, defense/military, aerial antenna towers, etc. The low loss cable has a 50 Ohm impedance and is specifically ready for quicker shipment than most in the industry can provide.

This weatherproof low loss RF cable assembly operates at a maximum frequency of 6 GHz. Our RF cable assembly has a PE jacket with 0.195 inches diameter. The SMA male to type N male cable assembly FMCA1079/WP is built with LMR-195 coax, which has a flexible design. This RF cable assembly with 0.5 inches diameter has copper as cable's inner conducting material and PE (F) dielectric type. The weatherproof boot low loss cable is reusable and can withstand elements including extreme temperature. Additional dimensions, specifications, and CAD drawings for this FMCA1079/WP low loss RF cable are available on our downloadable PDF datasheet.

Fairview Microwave stocks a wide selection of weatherproof low loss cable assemblies that ship the same business day as ordered from our warehouse. Make your online purchase right now to take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the ideal SMA male to type N male cable assembly as per your requirements.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		80		%
RF Shielding	90			dB
Capacitance		25.4 [83.33]		pF/ft [pF/m]
Inductance		0.064 [0.21]		uH/ft [uH/m]

Low Loss SMA Male to N Male Weatherproof Cable LMR-195 Coax with Times Microwave Components



FMCA1079/WP

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
DC Resistance Inner Conductor		7.6 [24.93]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		4.9 [16.08]		Ohms/1000ft [Ohms/Km]
Dielectric Withstanding Voltage (DC)			1,000	Vdc
Jacket Spark			3,000	Vrms

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	250	500	1000	2500	6000	MHz	
FMCA1079/WP	Custom Lengths Available	Insertion Loss (Typ.)	0.057	0.081	0.116	0.19	0.299	dB/ft	
			0.19	0.27	0.39	0.63	0.99	dB/m	
FMCA1079/WP-12	12 Inch	Insertion Loss (Typ.)	0.26	0.29	0.32	0.39	0.5	dB	0.625
FMCA1079/WP-24	24 Inch	Insertion Loss (Typ.)	0.32	0.37	0.44	0.58	0.8	dB	0.647
FMCA1079/WP-36	36 Inch	Insertion Loss (Typ.)	0.38	0.45	0.55	0.77	1.1	dB	0.669
FMCA1079/WP-48	48 Inch	Insertion Loss (Typ.)	0.43	0.53	0.67	0.96	1.4	dB	0.691
FMCA1079/WP-60	60 Inch	Insertion Loss (Typ.)	0.49	0.61	0.78	1.15	1.7	dB	0.713

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1 dB
Loss due to Connector 2:	0.1 dB
Base Weight:	0.625 pounds
Additional Weight per Inch:	0.00183 pounds

Electrical Specification Notes:
Values at 25°C, sea level.

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.625 lbs [283.5 g]

Cable

Cable Type	LMR-195
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE
Jacket Diameter	0.195 in [4.95 mm]
One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	2 in [50.8 mm]

Low Loss SMA Male to N Male Weatherproof Cable
LMR-195 Coax with Times Microwave Components



FMCA1079/WP

Bending Moment	0.2 lbs-ft [0.27 N-m]
Flat Plate Crush	15 lbs/in [0.27 Kg/mm]
Tensile Strength	40 lbs [18.14 Kg]

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	N Male
Option	Weatherproof Boot	Weatherproof Boot
Specification		MIL-STD-348
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	ASTM B488	50 µin minimum
Dielectric Type	Teflon	Teflon
Body Material and Plating	Passivated Stainless Steel	Brass, Tri-Metal
Coupling Nut Material and Plating	Passivated Stainless Steel	Brass, Tri-Metal
Boot Material	Silicone	Silicone

Environmental Specifications

Ingress Protection (IP) Rating	IP68
--------------------------------	------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:
Values at 25°C, sea level.

Low Loss SMA Male to N Male Weatherproof Cable LMR-195 Coax with Times Microwave Components



FMCA1079/WP

Typical Performance Data

How to Order

Part Number Configuration:

FMCA1079/WP

- xx

uu

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: FMCA1079/WP-12 = 12 inches long cable
FMCA1079/WP-100cm = 100 cm long cable

Low Loss SMA Male to N Male Weatherproof Cable LMR-195 Coax with Times Microwave Components from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Low Loss SMA Male to N Male Weatherproof Cable LMR-195 Coax with Times Microwave Components FMCA1079/WP](https://www.fairviewmicrowave.com/low-loss-sma-male-to-n-male-weatherproof-cable-lmr-195-coax-with-times-microwave-components-fmca1079-wp)

URL: <https://www.fairviewmicrowave.com/low-loss-sma-male-to-n-male-weatherproof-cable-lmr-195-coax-with-times-microwave-components-fmca1079-wp-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA1079/WP CAD Drawing

Low Loss SMA Male to N Male Weatherproof Cable LMR-195 Coax with Times Microwave Components

