

Low PIM N Male to 4.1/9.5 Mini DIN Male Plenum  
Cable SPP-250-LLPL Coax in 24 Inch

**FMCA1315-24**



**Configuration**

- Connector 1: N Male
- Connector 2: 4.1/9.5 Mini DIN Male
- Cable Type: SPP-250-LLPL
- Coax Flex Type: Corrugated

**Features**

- Max Frequency 6 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > 100 dB
- 76% Phase Velocity
- FEP Jacket
- Low PIM < -160 dBc
- IP67 (Mated)
- Low Loss with Excellent VSWR
- PIM Test Results Marked on Each Cable
- UL910 Plenum Rated Cable
- Extremely Flexible and Lightweight



**Applications**

- General Purpose
- Laboratory Use
- Low PIM Applications
- DAS
- Mobile Networks
- In-Building Wireless
- Small Cells
- PIM Testing

**Description**

Low PIM N male to 4.1/9.5 mini DIN male part number FMCA1315 from Fairview Microwave is in-stock and ships same day. This low PIM N male to 4.1/9.5 mini DIN male plenum coax cable assembly offers low PIM performance to support Distributed Antenna Systems (DAS), in-building wireless and other emerging mobile communication networks. The SPP-250-LLPL coax cable carries a UL910 rating for plenum installations. Each low PIM N male to 4.1/9.5 mini DIN male cable assembly is marked with its actual Passive Intermodulation (PIM) test result.

Fairview's FMCA1315 datasheet specifications and outline drawing are shown below in this PDF. Our extensive offering of low PIM cable assemblies, low-PIM adapters and other RF products support multi-carrier system prototype, cable installations and PIM testing applications.

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.35:1	
Velocity of Propagation		76		%
RF Shielding	100			dB
Passive Intermodulation IM3 (2x43dBm Tones) at 850 MHz or 1900 MHz		-165	-160	dBc
Capacitance		26.7 [87.6]		pF/ft [pF/m]

Low PIM N Male to 4.1/9.5 Mini DIN Male Plenum  
Cable SPP-250-LLPL Coax in 24 Inch



**FMCA1315-24**

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Operating Voltage (AC)			750	Vrms

**Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2	4	6	GHz
Insertion Loss (Max.)	0.48	0.51	0.56	0.64	0.7	dB
VSWR (Max.)	1.25:1	1.25:1	1.25:1	1.35:1	1.35:1	
Power Handling (Max.)	850	507	460	370	250	Watts

Electrical Specification Notes:

Values at 25°C, sea level

PIM test results vary between cables

The Insertion Loss data above is based on the performance specifications of the coax used in this assembly. The Insertion Loss includes an estimated loss of 0.4dB of connector loss.

**Mechanical Specifications**

**Cable Assembly**

Length 24 in [609.6 mm]

Width/Diameter .28 in [7.11 mm]

**Cable**

Cable Type SPP-250-LLPL

Inner Conductor Type Solid

Inner Conductor Material and Plating Copper, Bare

Dielectric Type PTFE

Number of Shields 1

Shield Layer 1 Annular Corrugated Copper Tube

Outer Conductor Diameter 0.25 in [6.35 mm]

Jacket Material FEP

Jacket Diameter 0.28 in [7.11 mm]

One Time Minimum Bend Radius 1.5 in [38.1 mm]

Low PIM N Male to 4.1/9.5 Mini DIN Male Plenum  
Cable SPP-250-LLPL Coax in 24 Inch



**FMCA1315-24**

**Connectors**

Description	Connector 1	Connector 2
Type	N Male	4.1/9.5 Mini DIN Male
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Silver	Brass, Silver
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Seal Gasket Material	Silicone Rubber	Silicone Rubber

**Environmental Specifications**

Operating Range Temperature	-55 to +125 deg C
Plenum Rating	UL910

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:  
Values at 25°C, sea level.

Low PIM N Male to 4.1/9.5 Mini DIN Male Plenum  
Cable SPP-250-LLPL Coax in 24 Inch

**FMCA1315-24**



Typical Performance Data




Low PIM N Male to 4.1/9.5 Mini DIN Male Plenum  
Cable SPP-250-LLPL Coax in 24 Inch



**FMCA1315-24**

**How to Order**

Part Number Configuration:



Example: FMCA1315-12 = 12 inches long cable  
FMCA1315-100cm = 100 cm long cable

Low PIM N Male to 4.1/9.5 Mini DIN Male Plenum Cable SPP-250-LLPL Coax in 24 Inch from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Low PIM N Male to 4.1/9.5 Mini DIN Male Plenum Cable SPP-250-LLPL Coax in 24 Inch FMCA1315-24](#)

URL: <https://www.fairviewmicrowave.com/n-male-4.1-9.5-male-cable-spp250llpl-fmca1315-24-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

# FMCA1315-24 CAD Drawing

Low PIM N Male to 4.1/9.5 Mini DIN Male Plenum Cable SPP-250-LLPL Coax in 24 Inch

