

## Slide-On BMA Jack 2 Hole Flange to SMP Female Cable RG405 Type .086 Coax in 12 Inch

The BMA jack slide-on 2 hole flange to SMP female 12 inch cable using RG405 type .086 coax, part number FMCA1607-12, from Fairview Microwave is in-stock and ships same day. This Fairview BMA to SMP cable assembly has a jack to female gender configuration with 50 ohm semi-rigid FM-SR086CU coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA1607-12 BMA jack to SMP female cable assembly operates to 18 GHz. Our RF cable assembly with BMA 2 hole flange interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

| Description     | Min | Typ | Max   | Units |
|-----------------|-----|-----|-------|-------|
| Frequency Range | DC  |     | 18    | GHz   |
| VSWR            |     |     | 1.5:1 |       |
| Return Loss     |     |     | 15.56 | dB    |

### Performance by Frequency

| Description           | F1   | F2   | F3   | F4   | F5   | Units |
|-----------------------|------|------|------|------|------|-------|
| Frequency             | 1    | 2    | 4.5  | 9    | 18   | GHz   |
| Insertion Loss (Typ.) | 0.42 | 0.48 | 0.66 | 0.94 | 1.33 | dB    |

### Mechanical Specifications

#### Cable Assembly

|          |                    |
|----------|--------------------|
| Length*  | 12 in [304.8 mm]   |
| Diameter | 0.75 in [19.05 mm] |

#### Cable

|                                      |                           |
|--------------------------------------|---------------------------|
| Cable Type                           | FM-SR086CU                |
| Impedance                            | 50 Ohms                   |
| Inner Conductor Type                 | Solid                     |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |
| Dielectric Type                      | PTFE                      |
| Number of Shields                    | 1                         |
| Outer Conductor Material and Plating | Copper                    |
| Repeated Minimum Bend Radius         | 0.05 in [1.27 mm]         |



### Configuration:

- Slide-On BMA Jack 2 Hole Flange
- SMP Female
- FM-SR086CU

### Features:

- Max Frequency 18 GHz

### Applications:

- General Purpose
- Laboratory Use
- Rack and Panel
- BMA Cable RF Backplanes
- Phased Array Interconnects
- High Speed Switching Networks
- Blind Mate BMA Test

Fairview Microwave  
301 Leora Ln., Suite 100  
Lewisville, TX 75056  
Tel: 1-800-715-4396 / (972) 649-6678  
Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

## Connectors

| Description                   | Connector 1            | Connector 2            |
|-------------------------------|------------------------|------------------------|
| Type                          | BMA Jack               | SMP Female             |
| Mount Method                  | 2 Hole Flange          |                        |
| Specification                 |                        | MIL-STD-348            |
| Impedance                     | 50 Ohms                | 50 Ohms                |
| Connection Method             | Slide-On               |                        |
| Contact Material & Plating    | Beryllium Copper, Gold | Beryllium Copper, Gold |
| Contact Plating Spec.         | 51.18μ in. minimum     | MIL-G-45204            |
| Dielectric Type               | PTFE                   | PTFE                   |
| Outer Cond Material & Plating | Beryllium Copper, Gold |                        |
| Body Material & Plating       | Stainless Steel, Gold  | Beryllium Copper, Gold |
| Body Plating Spec.            | 19.68μ in. minimum     | MIL-G-45204            |

Mechanical Specification Notes:

\*All cable assemblies have a length tolerance of 1.5% or  $\pm 3/8"$ , whichever is greater.

## Environmental Specifications

### Temperature


Operating Range -55 to +125 deg C

## Compliance Certifications (see [product page](#) for current document)

## Plotted and Other Data

Notes:

## Typical Performance Data



## How to Order

Part Number Configuration:

**FMCA1607 - xx uu**

cm = Centimeters  
<blank> = Inches  
Length

Example: FMCA1607-12 = 12 inches long cable  
FMCA1607-100cm = 100 cm long cable


Slide-On BMA Jack 2 Hole Flange to SMP Female Cable RG405 Type .086 Coax in 12 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [Slide-On BMA Jack 2 Hole Flange to SMP Female Cable RG405 Type .086 Coax in 12 Inch FMCA1607-12](#)

URL: <https://www.fairviewmicrowave.com/bma-jack-smp-female-cable-rg405-type-.086-coax-fmca1607-12-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





**STANDARD TOLERANCES**

.X ±0.2  
.XX ±0.01  
.XXX ±0.005

\*STANDARD TOLERANCES APPLY  
ONLY TO DIMENSIONS IN INCHES

**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:  
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
3. DIMENSIONS ARE IN INCHES [mm].

**TITLE**

Slide-On BMA Jack 2 Hole Flange to SMP Female Cable  
RG405 Type .086 Coax in 12 Inch

**DWG NO**

FMCA1607

**CAGE CODE**

3FKR5

CAD FILE 12/20/17

SHEET

SCALE N/A

SIZE A

CN2245