

N Male to N Female Bulkhead Low PIM Cable 36 Inch Length Using TFT-402 Coax Using Times Microwave Components

The type N male to type N female bulkhead 36 inch cable using TFT-402 coax, part number FMCA2320-36, from Fairview Microwave is in-stock and ships same day. This Fairview type N to type N cable assembly has a male to female gender configuration with 50 ohm flexible TFT-402 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The FMCA2320-36 type N male to type N female cable assembly operates to 5.8 GHz. Our RF cable assembly with type N bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than -80 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Min | Typ | Max | Units |
|-------------------------------|-----|-------------|-------|----------------------------------|
| Frequency Range | DC | | 5.8 | GHz |
| VSWR | | | 1.4:1 | |
| Velocity of Propagation | | 76 | | % |
| RF Shielding | -80 | | | dB |
| Passive Intermodulation | | | -160 | dBc |
| Capacitance | | 26.7 [87.6] | | pF/ft [pF/m] |
| DC Resistance Inner Conductor | | 8.5 [27.89] | | Ω /1000ft [Ω /Km] |
| DC Resistance Outer Conductor | | 5.6 [18.37] | | Ω /1000ft [Ω /Km] |

Performance by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|------|------|-----|------|------|-------|
| Frequency | 0.25 | 0.5 | 1 | 2.5 | 5.8 | GHz |
| Insertion Loss (Typ.) | 0.3 | 0.39 | 0.5 | 0.77 | 1.13 | dB |

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of $0.1 \cdot \sqrt{FGHz}$ dB for the male connector and 0.1 dB for the female connector.

Mechanical Specifications

Cable Assembly

Cable

Cable Type

TFT-402



Configuration:

- N Male
- N Female Bulkhead
- TFT-402

Features:

- Max Frequency 5.8 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > -80 dB
- 76% Phase Velocity
- Double Shielded
- FEP Jacket

Applications:

- General Purpose
- Laboratory Use
- Low PIM Applications
- Indoor and Outdoor Use
- Plenum Rated Applications

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

| | |
|--------------------------------------|----------------------------|
| Impedance | 50 Ohms |
| Inner Conductor Type | Solid |
| Inner Conductor Material and Plating | Copper, Silver |
| Dielectric Type | PTFE |
| Number of Shields | 2 |
| Shield Layer 1 | Silver Plated Copper Braid |
| Shield Layer 2 | Tinned Copper Braid |
| Jacket Material | FEP, Blue |
| Jacket Diameter | 0.16 in [4.06 mm] |
| One Time Minimum Bend Radius | 0.75 in [19.05 mm] |

Connectors

| Description | Connector 1 | Connector 2 |
|---------------------------------|------------------|-----------------------------|
| Type | N Male | N Female |
| Mount Method | | Bulkhead |
| Impedance | 50 Ohms | 50 Ohms |
| Mating Cycles | 500 | |
| Contact Material & Plating | Brass, Silver | Brass, Copper Clad Aluminum |
| Contact Plating Spec. | 200 µin | 3 µm |
| Dielectric Type | PTFE | PTFE |
| Outer Cond Material & Plating | | Brass, Copper Clad Aluminum |
| Outer Cond Plating Spec. | | 3 µm |
| Body Material & Plating | Brass, Tri-Metal | Brass, Copper Clad Aluminum |
| Body Plating Spec. | 80 µin | 3 µm |
| Coupling Nut Material & Plating | Brass, Tri-Metal | |
| Coupling Nut Plating Spec. | 80 µin | |
| Torque | 15 in-lbs 1.7 Nm | 10 in-lbs 1.13 Nm |

Environmental Specifications

Temperature

Operating Range -40 to +125 deg C

Compliance Certifications (see [product page](#) for current document)


Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMCA2320 - xx uu



Example: FMCA2320-12 = 12 inches long cable
FMCA2320-100cm = 100 cm long cable

N Male to N Female Bulkhead Low PIM Cable 36 Inch Length Using TFT-402 Coax Using Times Microwave Components from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: [N Male to N Female Bulkhead Low PIM Cable 36 Inch Length Using TFT-402 Coax Using Times Microwave Components FMCA2320-36](#)

URL: <https://www.fairviewmicrowave.com/low-pim-n-male-n-female-cable-tft-402-coax-fmca2320-36-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



| REVISIONS | | | |
|-----------|---|---------|----------|
| REV. | DESCRIPTION | DATE | APPROVED |
| B | PCR PE3C7959 20220517 AND PE3C7948 20210610 | 5/17/22 | SRAUTUS |



NOTES:

1. CABLES 84" AND UNDER HAVE 1 LABEL CENTERED. CABLES OVER 84" HAVE 2 LABELS, ONE AT EACH END 12" FROM THE FRONT OF THE CONNECTOR.
2. PIM LABEL 6" FROM CABLE END 1 PLACE.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

| | | |
|---|--|--|
| <p>Fairview Microwave an INFINIT[®] brand</p> | <p>UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS</p> <p>TOLERANCES: CABLE LENGTH (L) TOLERANCES:</p> <p>L ≤ 12 [305] = +1 [25] / -0 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0 120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 300 [7620] < L = +5%L / -0</p> <p>.X = ±.2 [5.08] FRACTIONS ± 1/32 .XX = ±.02 [.51] ANGLES ± 1° .XXX = ±.005 [.13]</p> | <p>THIRD-ANGLE PROJECTION</p> <p>THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.</p> |
| | <p>TITLE</p> <p>N Male to N Female Bulkhead Low PIM Cable 36 Inch Length Using TFT-402 Coax Using Times Microwave Components</p> | <p>SHEET 1 OF 1</p> <p>SCALE N/A</p> |
| <p>ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.</p> | | <p>SIZE A CAGE CODE 3FKR5 DRAWN BY DFRISIELLO ITEM NO. FMCA2320 REV B</p> |

T-Rev.D