

## SMA Male to SMA Male Right Angle Low PIM Cable 100 CM Length Using TFT-402 Coax Using Times Microwave Components



### FMCA2327-100CM

#### Configuration

- Connector 1: SMA Male
- Connector 2: SMA Male Right Angle
- Cable Type: TFT-402
- Coax Flex Type: Flexible

#### Features

- Max Frequency 5.8 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > -80 dB
- 76% Phase Velocity
- Double Shielded
- FEP Jacket

#### Applications

- General Purpose
- Laboratory Use
- Low PIM Applications
- Indoor and Outdoor Use
- Plenum Rated Applications

#### Description


The SMA male to RA SMA male 100 cm cable using TFT-402 coax, part number FMCA2327-100CM, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SMA cable assembly has a male to male gender configuration with 50 ohm flexible TFT-402 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The FMCA2327-100CM SMA male to SMA male cable assembly operates to 5.8 GHz. The right angle SMA interface on the TFT-402 cable allows for easier connections in tight spaces. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than -80 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.4:1	
Velocity of Propagation		76		%
RF Shielding	-80			
Passive Intermodulation IM3 (2x43dBm Tones) at 850 MHz or 1900 MHz			-160	dBc
Capacitance		26.7 [87.6]		pF/ft [pF/m]
DC Resistance Inner Conductor		8.5 [27.89]		Ohms/1000ft [Ohms/Km]

SMA Male to SMA Male Right Angle  
Low PIM Cable 100 CM Length Using TFT-402 Coax  
Using Times Microwave Components



FMCA2327-100CM

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
DC Resistance Outer Conductor		5.6 [18.37]		Ohms/1000ft [Ohms/Km]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	5.8	GHz
Insertion Loss (Typ.)	0.47	0.53	0.63	0.86	1.16	dB

Electrical Specification Notes:  
The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.15 dB per connector.

Mechanical Specifications


Cable Assembly

Width/Diameter0.374 in [9.5 mm]

Cable

Cable TypeTFT-402  
Impedance50 Ohms  
Inner Conductor TypeSolid  
Inner Conductor Material and PlatingCopper, Silver  
Dielectric TypePTFE  
Number of Shields2  
Shield Layer 1Silver Plated Copper Braid  
Shield Layer 2Tinned Copper Braid  
Jacket MaterialFEP, Blue  
Jacket Diameter0.16 in [4.06 mm]  
One Time Minimum Bend Radius0.75 in [19.05 mm]

SMA Male to SMA Male Right Angle  
Low PIM Cable 100 CM Length Using TFT-402 Coax  
Using Times Microwave Components



FMCA2327-100CM

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SMA Male Right Angle
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Contact Material and Plating	Brass, Silver	Brass, Silver
Contact Plating Specification	5 µm	5 µm
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Silver	Brass, Copper Clad Aluminum
Body Plating Specification	5 µm	3 µm
Coupling Nut Material and Plating	Brass, Copper Clad Aluminum	Brass, Copper Clad Aluminum
Coupling Nut Plating Specification	3 µm	3 µm
Torque	9 in-lbs 1.02 Nm	

Environmental Specifications

Operating Range Temperature -55 to +150 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

SMA Male to SMA Male Right Angle  
Low PIM Cable 100 CM Length Using TFT-402 Coax  
Using Times Microwave Components



## FMCA2327-100CM

### Typical Performance Data

### How to Order

Part Number Configuration:

**FMCA2327**

**- xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches

Length

Base Number

Example: FMCA2327-12 = 12 inches long cable  
FMCA2327-100cm = 100 cm long cable

SMA Male to SMA Male Right Angle Low PIM Cable 100 CM Length Using TFT-402 Coax Using Times Microwave Components from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [SMA Male to SMA Male Right Angle Low PIM Cable 100 CM Length Using TFT-402 Coax Using Times Microwave Components FMCA2327-100CM](https://www.fairviewmicrowave.com/low-pim-sma-male-ra-sma-male-cable-tft-402-coax-fmca2327-100cm-p.aspx)

URL: <https://www.fairviewmicrowave.com/low-pim-sma-male-ra-sma-male-cable-tft-402-coax-fmca2327-100cm-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA2327-100CM CAD Drawing

SMA Male to SMA Male Right Angle Low PIM Cable 100 CM Length Using

TFT-402 Coax Using Times Microwave Components

