

## 4.3-10 Male to 4.3-10 Male Low PIM Cable 200 CM Length Using TFT-5G-402 Coax Using Times Microwave Components

### FMCA2334-200CM



#### Configuration

- Connector 1: 4.3-10 Male
- Connector 2: 4.3-10 Male
- Cable Type: TFT-5G-402
- Coax Flex Type: Flexible

#### Features

- Max Frequency 5.8 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > 80 dB
- 76% Phase Velocity
- Double Shielded
- FEP Jacket
- 500 Mating Cycles

#### Applications

- General Purpose
- Laboratory Use
- Low PIM Applications
- Indoor and Outdoor Use
- Plenum Rated Applications

#### Description

The 4.3-10 male to 4.3-10 male 200 cm cable using TFT-5G-402 coax, part number FMCA2334-200CM, from Fairview Microwave is in-stock and ships same day. This Fairview 4.3-10 to 4.3-10 cable assembly has a male to male gender configuration with 50 ohm flexible TFT-5G-402 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The FMCA2334-200CM 4.3-10 male to 4.3-10 male cable assembly operates to 5.8 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 80 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

| Description                                | Minimum | Typical | Maximum | Units |
|--------------------------------------------|---------|---------|---------|-------|
| Frequency Range                            | DC      |         | 5.8     | GHz   |
| VSWR                                       |         |         | 1.4:1   |       |
| Velocity of Propagation                    |         | 76      |         | %     |
| RF Shielding                               | 80      |         |         | dB    |
| Passive Intermodulation                    |         |         | -160    | dBc   |
| IM3 (2x43dBm Tones) at 850 MHz or 1900 MHz |         |         |         |       |

4.3-10 Male to 4.3-10 Male Low PIM Cable  
200 CM Length Using TFT-5G-402 Coax Using  
Times Microwave Components



## FMCA2334-200CM

### Electrical Specifications

| Description | Minimum | Typical     | Maximum | Units        |
|-------------|---------|-------------|---------|--------------|
| Capacitance |         | 26.7 [87.6] |         | pF/ft [pF/m] |

### Specifications by Frequency

| Description           | F1   | F2   | F3   | F4   | F5   | Units |
|-----------------------|------|------|------|------|------|-------|
| Frequency             | 0.25 | 0.5  | 1    | 2.5  | 5.8  | GHz   |
| Insertion Loss (Typ.) | 0.56 | 0.67 | 0.93 | 1.63 | 2.46 | dB    |

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1\*SQRT(FGHz) dB per connector.

### Mechanical Specifications

#### Cable Assembly

|                |                      |
|----------------|----------------------|
| Width/Diameter | 0.866 in [22 mm]     |
| Weight         | 0.533 lbs [241.76 g] |

#### Cable

|                                      |                    |
|--------------------------------------|--------------------|
| Cable Type                           | TFT-5G-402         |
| Impedance                            | 50 Ohms            |
| Inner Conductor Type                 | Solid              |
| Inner Conductor Material and Plating | Copper             |
| Dielectric Type                      | PTFE               |
| Number of Shields                    | 2                  |
| Jacket Material                      | FEP, Blue          |
| Jacket Diameter                      | 0.16 in [4.06 mm]  |
| One Time Minimum Bend Radius         | 0.75 in [19.05 mm] |

4.3-10 Male to 4.3-10 Male Low PIM Cable  
200 CM Length Using TFT-5G-402 Coax Using  
Times Microwave Components



## FMCA2334-200CM

### Connectors

| Description                        | Connector 1       | Connector 2       |
|------------------------------------|-------------------|-------------------|
| Type                               | 4.3-10 Male       | 4.3-10 Male       |
| Impedance                          | 50 Ohms           | 50 Ohms           |
| Configuration                      | Straight          | Straight          |
| Mating Cycles                      | 500               | 500               |
| Contact Material and Plating       | Brass, Silver     | Brass, Silver     |
| Contact Plating Specification      | 200 µin           | 200 µin           |
| Dielectric Type                    | PTFE              | PTFE              |
| Body Material and Plating          | Brass, Tri-Metal  | Brass, Tri-Metal  |
| Body Plating Specification         | 80 µin            | 80 µin            |
| Coupling Nut Material and Plating  | Brass, Tri-Metal  | Brass, Tri-Metal  |
| Coupling Nut Plating Specification | 80 µin            | 80 µin            |
| Torque                             | 44 in-lbs 4.97 Nm | 44 in-lbs 4.97 Nm |

### Environmental Specifications

Operating Range Temperature -55 to +85 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

## 4.3-10 Male to 4.3-10 Male Low PIM Cable 200 CM Length Using TFT-5G-402 Coax Using Times Microwave Components

### FMCA2334-200CM



#### Typical Performance Data

#### How to Order

Part Number Configuration:

**FMCA2334**

**- xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: FMCA2334-12 = 12 inches long cable  
FMCA2334-100cm = 100 cm long cable

4.3-10 Male to 4.3-10 Male Low PIM Cable 200 CM Length Using TFT-5G-402 Coax Using Times Microwave Components from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [4.3-10 Male to 4.3-10 Male Low PIM Cable 200 CM Length Using TFT-5G-402 Coax Using Times Microwave Components FMCA2334-200CM](https://www.fairviewmicrowave.com/low-pim-4.3-10-male-4.3-10-male-cable-tft-5g-402-coax-fmca2334-200cm-p.aspx)

URL: <https://www.fairviewmicrowave.com/low-pim-4.3-10-male-4.3-10-male-cable-tft-5g-402-coax-fmca2334-200cm-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

### 4.3-10 Male to 4.3-10 Male Low PIM Cable 200 CM Length Using TFT-5G-402 Coax Using Times Microwave Components

