

Low Loss N Male to N Female Weatherproof Cable SPO-250 Coax in 24 Inch with Times Microwave Components

FMCA2562/WP-24




Configuration

- Connector 1: N Male
- Connector 2: N Female
- Cable Type: SPO-250
- Coax Flex Type: Flexible

Features

- Max Frequency 6 GHz
- Low PIM: -160 dBc Max
- 83% Phase Velocity
- PE Jacket
- Silicone Connector Boot
- IP68 Rated



Applications

- General Purpose
- Laboratory Use

Description

The type N male to type N female 24 inch cable using SPO-250 coax, part number FMCA2562/WP-24, from Fairview Microwave is in-stock and ships same day. This Fairview type N to type N cable assembly has a male to female gender configuration with 50 ohm flexible SPO-250 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA2562/WP-24 type N male to type N female cable assembly operates to 6 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		83		%
Passive Intermodulation			-160	dBc
IM3 (2x43dBm Tones) at 850 MHz or 1900 MHz				
Capacitance		24 [78.74]		pF/ft [pF/m]
Inductance		0.054 [0.18]		uH/ft [uH/m]

Specifications by Frequency

Low Loss N Male to N Female Weatherproof Cable SPO-250 Coax in 24 Inch with Times Microwave Components



FMCA2562/WP-24

Part Number	Length	Description	F1	F2	F3	F4	Units	Weight (lbs)
		Frequency	500	1000	2500	6000	MHz	
FMCA2562/WP	Custom Lengths Available	Insertion Loss (Typ.)	0.028	0.041	0.068	0.108	dB/ft	
			0.1	0.14	0.23	0.36	dB/m	
FMCA2562/WP-24	24 In	Insertion Loss (Typ.)	0.2	0.29	0.46	0.71	dB	0.751
FMCA2562/WP-36	36 In	Insertion Loss (Typ.)	0.23	0.33	0.53	0.82	dB	0.798
FMCA2562/WP-60	60 In	Insertion Loss (Typ.)	0.29	0.2	0.66	1.03	dB	0.892
FMCA2562/WP-50CM	50 CM	Insertion Loss (Typ.)	0.19	0.27	0.43	0.67	dB	0.735

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1*SQRT(FGHz) dB
 Loss due to Connector 2: 0.1*SQRT(FGHz) dB
 Base Weight: 0.704 pounds
 Additional Weight per Inch: 0.00391 pounds

Mechanical Specifications

Cable Assembly

Length 24 in [609.6 mm]
 Width/Diameter 0.5 in [12.7 mm]
 Weight 0.751 lbs [340.65 g]

Cable

Cable Type SPO-250
 Impedance 50 Ohms
 Inner Conductor Type Stranded
 Inner Conductor Material and Plating Copper Clad Aluminum
 Dielectric Type Foam PE
 Outer Conductor 1 Material and Plating Copper, Corrugated
 Jacket Material PE
 Jacket Diameter 0.303 in [7.7 mm]
 One Time Minimum Bend Radius 1 in [25.4 mm]
 Bending Moment 0.5 lbs-ft [0.68 N-m]

Low Loss N Male to N Female Weatherproof Cable SPO-250 Coax in 24 Inch with Times Microwave Components



FMCA2562/WP-24

Connectors

Description	Connector 1	Connector 2
Type	N Male	N Female
Option	Weatherproof Boot	
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Phosphor Bronze, Silver	Brass, Silver
Contact Plating Specification	196 µin minimum	200 µin minimum
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating		Brass, Tri-Metal
Outer Conductor Plating Specification		100 µin minimum
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification	118 µin minimum	100 µin minimum
Coupling Nut Material and Plating	Brass, Tri-Metal	
Coupling Nut Plating Specification	118 µin minimum	
Boot Material	Silicone	Silicone

Environmental Specifications

Operating Range Temperature	-40 to +85 deg C
Ingress Protection (IP) Rating	IP68

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:
Values at 25°C, sea level.

Low Loss N Male to N Female Weatherproof Cable SPO-250 Coax in 24 Inch with Times Microwave Components



FMCA2562/WP-24

Typical Performance Data

How to Order

Part Number Configuration:

FMCA2562/WP - xx uu

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length
Base Number

Example: FMCA2562/WP-12 = 12 inches long cable
FMCA2562/WP-100cm = 100 cm long cable

Low Loss N Male to N Female Weatherproof Cable SPO-250 Coax in 24 Inch with Times Microwave Components from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Low Loss N Male to N Female Weatherproof Cable SPO-250 Coax in 24 Inch with Times Microwave Components FMCA2562/WP-24](#)

URL: <https://www.fairviewmicrowave.com/low-loss-n-male-to-n-female-weatherproof-cable-spo-250-coax-in-24-inch-with-times-microwave-components-fmca2562-wp-24-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA2562/WP-24 CAD Drawing

Low Loss N Male to N Female Weatherproof Cable SPO-250 Coax in 24 Inch with Times Microwave Components

