

12G SDI 75 Ohm HD-BNC Male to 75 Ohm HD-BNC Male Cable 75 Ohm 4855R-BK Coax in 120 Inch

The 75 ohm HD-BNC male to 75 ohm HD-BNC male 120 inch cable using 75 ohm 4855R-BK coax, part number FMCA2607/BK-120, from Fairview Microwave is in-stock and ships same day. This Fairview HD-BNC to HD-BNC cable assembly has a male to male gender configuration with 75 ohm flexible Belden 4855R-BK coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA2607/BK-120 HD-BNC male to HD-BNC male cable assembly operates to 12 GHz and enables 12Gb/s data transfer rates for high resolution uncompressed video signal transmission. These products offer 4K and Ultra-HD quality signals that meet SMPTE Standard 2082-1.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		12	GHz
VSWR			1.5:1	
Velocity of Propagation		82		%
Group Delay		1.2 [3.94]		ns/ft [ns/m]
Capacitance		16.3 [53.48]		pF/ft [pF/m]
Inductance		0.107 [0.35]		uH/ft [uH/m]
DC Resistance Inner Conductor		19.7 [64.63]		Ω /1000ft [Ω /Km]
DC Resistance Outer Conductor		3.9 [12.8]		Ω /1000ft [Ω /Km]
Operating Voltage (AC)			300	Vrms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2.5	5	12	GHz
Insertion Loss (Typ.)	0.95	1.28	1.92	2.69	4.32	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Length*	120 in [304.8 cm]
Weight	0.3 lbs [136.08 g]

Cable

Cable Type	Belden 4855R-BK
Impedance	75 Ohms



Configuration:

- HD-BNC Male
- HD-BNC Male
- Belden 4855R-BK

Features:

- Max Frequency 12 GHz
- 82% Phase Velocity
- PVC Jacket
- Meets SMPTE ST 2082-1
- Backwards Compatible with 2081-1
- 12Gb/s Transmission
- Cost Effective

Applications:

- General Purpose
- Laboratory Use
- 12G-SDI, Video, and Broadband UHDTV
- Broadband Internet Delivery
- Broadcast A/V
- 4K/8K Video Equipment
- Medical Equipment Requiring High Speed Video
- HD Cameras

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	HDPE
Number of Shields	1
Shield Layer 1	Aluminum Polyester
Shield Layer 2	Tinned Copper
Jacket Material	PVC, Black
Jacket Diameter	0.159 in [4.04 mm]

Connectors

Description	Connector 1	Connector 2
Type	HD-BNC Male	HD-BNC Male
Impedance	75 Ohms	75 Ohms
Contact Material & Plating	Brass, Gold	Brass, Gold
Contact Plating Spec.	10 µin minimum	10 µin minimum
Dielectric Type	PTFE	PTFE
Outer Cond Material & Plating	Brass, Nickel	Brass, Nickel
Outer Cond Plating Spec.	100 µin minimum	100 µin minimum
Body Material & Plating	Brass, Nickel	Brass, Nickel
Body Plating Spec.	100 µin minimum	100 µin minimum

Environmental Specifications

Temperature

Operating Range -30 to +75 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

How to Order

Part Number Configuration:

FMCA2607/BK - xx uu

cm = Centimeters
 <blank> = Inches
 Length

Example: FMCA2607/BK-12 = 12 inches long cable
 FMCA2607/BK-100cm = 100 cm long cable

12G SDI 75 Ohm HD-BNC Male to 75 Ohm HD-BNC Male Cable 75 Ohm 4855R-BK Coax in 120 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: [12G SDI 75 Ohm HD-BNC Male to 75 Ohm HD-BNC Male Cable 75 Ohm 4855R-BK Coax in 120 Inch FMCA2607/BK-120](https://www.fairviewmicrowave.com/12g-sdi-75-ohm-hd-bnc-male-to-75-ohm-hd-bnc-male-cable-75-ohm-4855r-bk-coax-in-120-inch-fmca2607-bk-120)

URL: <https://www.fairviewmicrowave.com/12g-sdi-75-ohm-hd-bnc-male-to-75-ohm-hd-bnc-male-cable-75-ohm-4855r-bk-coax-in-120-inch-fmca2607-bk-120-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/29/22	AGANWANI



FMCA2607/ZZ (ZZ = CABLE COLOR DESIGNATION)	COAX CABLE COLOR
FMCA2607/BK	BLACK
FMCA2607/BL	BLUE
FMCA2607/GR	GREEN
FMCA2607/OR	ORANGE
FMCA2607/RD	RED
FMCA2607/VL	VIOLET
FMCA2607/WH	WHITE
FMCA2607/YW	YELLOW

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

TITLE

12G SDI 75 Ohm HD-BNC Male to 75 Ohm HD-BNC Male Cable 75 Ohm 4855R-BK Coax in 120 Inch

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

CABLE LENGTH (L) TOLERANCES:

.X = ± 2 [5.08]	FRACTIONS
.XX = $\pm .02$ [.51]	$\pm 1/32$
.XXX = $\pm .005$ [.13]	ANGLES $\pm 1^\circ$

$$\begin{aligned} L \leq 12 \text{ [305]} &= +1 \text{ [25]} / -0 \\ 12 \text{ [305]} < L \leq 60 \text{ [1524]} &= +2 \text{ [51]} / -0 \\ 60 \text{ [1524]} < L \leq 120 \text{ [3048]} &= +4 \text{ [102]} / -0 \\ 120 \text{ [3048]} < L \leq 300 \text{ [7620]} &= +6 \text{ [152]} / -0 \\ 300 \text{ [7620]} < L &= +5\% / -0 \end{aligned}$$

THIRD-ANGLE PROJECTION



THE INFORMATION AND
DESIGN IN THIS DOCUMENT
IS THE PROPERTY OF
FAIRVIEW MICROWAVE CORPORATION.
ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE	N/A
-------	-----

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY

SIZE	A
------	---

CAGE CODE	3FK
-----------	-----

DRAWN BY
HBA

ITEM NO.	
----------	--

REV	A
-----	---