

6G SDI 75 Ohm BNC Male to 75 Ohm BNC Male Cable 75 Ohm 1855A-OR Coax in 120 Inch

The 75 ohm BNC male to 75 ohm BNC male 120 inch cable using 75 ohm 1855A-OR coax, part number FMCA2735/OR-120, from Fairview Microwave is in-stock and ships same day. This Fairview BNC to BNC cable assembly has a male to male gender configuration with 75 ohm flexible Belden 1855A-OR coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA2735/OR-120 BNC male to BNC male cable assembly operates to 6 GHz and enables 6Gb/s data transfer rates for high resolution uncompressed video signal transmission. These products offer 4K and Ultra-HD quality signals that meet SMPTE Standard 2081-1.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		6	GHz
VSWR			1.5:1	
Velocity of Propagation		82		%
Group Delay		1.22 [4]		ns/ft [ns/m]
Capacitance		16.3 [53.48]		pF/ft [pF/m]
Inductance		0.107 [0.35]		uH/ft [uH/m]
DC Resistance Inner Conductor		20.1 [65.94]		Ω /1000ft [Ω /Km]
DC Resistance Outer Conductor		3.7 [12.14]		Ω /1000ft [Ω /Km]
Operating Voltage (AC)			300	Vrms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	6	GHz
Insertion Loss (Typ.)	0.72	0.95	1.28	1.96	3.09	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Length*	120 in [304.8 cm]
Weight	0.3 lbs [136.08 g]

Cable

Cable Type	Belden 1855A-OR
Impedance	75 Ohms
Inner Conductor Type	Solid



Configuration:

- BNC Male
- BNC Male
- Belden 1855A-OR

Features:

- Max Frequency 6 GHz
- 82% Phase Velocity
- PVC Jacket
- Meets SMPTE ST 2081-1
- 6Gb/s Transmission
- Cost Effective

Applications:

- General Purpose
- Laboratory Use
- 6G-SDI, Video, and Broadband UHDTV
- Broadband Internet Delivery
- Broadcast A/V
- 4K/8K Video Equipment
- Medical Equipment Requiring High Speed Video
- HD Cameras

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Inner Conductor Material and Plating	Copper, Bare
Dielectric Type	PE
Number of Shields	1
Shield Layer 1	Aluminum Polyester
Shield Layer 2	Tinned Copper
Jacket Material	PVC, Orange
Jacket Diameter	0.159 in [4.04 mm]

Connectors

Description	Connector 1	Connector 2
Type	BNC Male	BNC Male
Impedance	75 Ohms	75 Ohms
Contact Material & Plating	Brass, Gold	Brass, Gold
Contact Plating Spec.	10 µin minimum	10 µin minimum
Dielectric Type	PTFE	PTFE
Outer Cond Material & Plating	Brass, Nickel	Brass, Nickel
Outer Cond Plating Spec.	50 µin minimum	50 µin minimum
Body Material & Plating	Brass, Nickel	Brass, Nickel
Body Plating Spec.	100 µin minimum	100 µin minimum

Environmental Specifications

Temperature

Operating Range -30 to +75 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

- Notes:
- Values at 25°C, sea level.

How to Order

Part Number Configuration:

FMCA2735/OR - xx uu

cm = Centimeters
<blank> = Inches
Length


Example: FMCA2735/OR-12 = 12 inches long cable
FMCA2735/OR-100cm = 100 cm long cable

6G SDI 75 Ohm BNC Male to 75 Ohm BNC Male Cable 75 Ohm 1855A-OR Coax in 120 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [6G SDI 75 Ohm BNC Male to 75 Ohm BNC Male Cable 75 Ohm 1855A-OR Coax in 120 Inch FMCA2735/OR-120](https://www.fairviewmicrowave.com/6g-sdi-75-ohm-bnc-male-to-75-ohm-bnc-male-cable-75-ohm-1855a-or-coax-in-120-inch-fmca2735-or-120-p.aspx)

URL: <https://www.fairviewmicrowave.com/6g-sdi-75-ohm-bnc-male-to-75-ohm-bnc-male-cable-75-ohm-1855a-or-coax-in-120-inch-fmca2735-or-120-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/29/22	AGANWANI

LENGTH MEASURED FROM CONTACT TO CONTACT

2X HEAT SHRINK BOOT

1855A COAX CABLE

1.0/2.3 MALE

1.0/2.3 MALE

FMCA2735/ZZ (ZZ = CABLE COLOR DESIGNATION)	COAX CABLE COLOR
FMCA2735/BK	BLACK
FMCA2735/BL	BLUE
FMCA2735/BR	BROWN
FMCA2735/GR	GREEN
FMCA2735/GY	GRAY
FMCA2735/OR	ORANGE
FMCA2735/RD	RED
FMCA2735/VL	VIOLET
FMCA2735/WH	WHITE
FMCA2735/YW	YELLOW

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

Fairview Microwave

an INFINITE brand

TITLE

6G SDI 75 Ohm BNC Male to 75 Ohm BNC Male Cable
75 Ohm 1855A-OR Coax in 120 Inch

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

CABLE LENGTH (L) TOLERANCES:

.X = ±.2 [.51] FRACTIONS
.XX = ±.02 [.51] ± 1/32
XXX = ±.005 [.13] ANGLES ± 1°

L ≤ 12 [305] = +1 [25] / -0
12 [305] < L ≤ 60 [1524] = +2 [51] / -0
60 [1524] < L ≤ 120 [3048] = +4 [102] / -0
120 [3048] < L ≤ 300 [7620] = +6 [152] / -0
300 [7620] < L = +5%L / -0

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.

SIZE A

CAGE CODE 3FKR5

DRAWN BY HBAKKE

ITEM NO. FMCA2735/ZZ

REV A

THIRD-ANGLE PROJECTION

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

T-Rev.D