

SMA Male to SMA Male Cable RG402 Type .141 Coax in 50 CM

The SMA male to SMA male 50 cm cable using RG402 type .141 coax, part number FMCA2816-50CM, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SMA cable assembly has a male to male gender configuration with 50 ohm semi-rigid FM-SR141CU-STR coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA2816-50CM SMA male to SMA male cable assembly operates to 18 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Min | Typ | Max | Units |
|--------------------------------------|-----|-------------|-------|--------------|
| Frequency Range | DC | | 18 | GHz |
| VSWR | | | 1.5:1 | |
| Capacitance | | 29.9 [98.1] | | pF/ft [pF/m] |
| Dielectric Withstanding Voltage (AC) | | | 1,000 | Vrms |

Performance by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|-----|------|------|------|------|-------|
| Frequency | 1 | 2 | 4.5 | 9 | 18 | GHz |
| Insertion Loss (Typ.) | 0.4 | 0.46 | 0.61 | 0.88 | 1.27 | dB |

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Length* 19.68 in [499.87 mm]
Weight 0.069 lbs [31.3 g]

Cable

Cable Type FM-SR141CU-STR
Impedance 50 Ohms
Inner Conductor Type Solid
Inner Conductor Material and Plating Copper Clad Steel, Silver
Dielectric Type PTFE
Number of Shields 1
Shield Layer 1 Copper



Configuration:

- SMA Male
- SMA Male
- FM-SR141CU-STR

Features:

- Max Frequency 18 GHz

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Connectors

| Description | Connector 1 | Connector 2 |
|---------------------------------|-----------------------|-----------------------|
| Type | SMA Male | SMA Male |
| Specification | MIL-STD-348A | MIL-STD-348A |
| Impedance | 50 Ohms | 50 Ohms |
| Contact Material & Plating | Brass, Gold | Brass, Gold |
| Contact Plating Spec. | 50µ in. minimum | 50µ in. minimum |
| Dielectric Type | Teflon | Teflon |
| Body Material & Plating | Stainless Steel, Gold | Stainless Steel, Gold |
| Body Plating Spec. | 10µ in. minimum | 10µ in. minimum |
| Coupling Nut Material & Plating | Brass, Nickel | Brass, Nickel |
| Coupling Nut Plating Spec. | 100µ in. minimum | 100µ in. minimum |
| Hex Size | 5/16 in | 5/16 in |
| Torque | 5 in-lbs 0.57 Nm | 5 in-lbs 0.57 Nm |

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

- Notes:
- Values at 25°C, sea level.

How to Order

Part Number Configuration:

FMCA2816 - xx uu

cm = Centimeters
<blank> = Inches
Length

Example: FMCA2816-12 = 12 inches long cable
FMCA2816-100cm = 100 cm long cable

SMA Male to SMA Male Cable RG402 Type .141 Coax in 50 CM from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [SMA Male to SMA Male Cable RG402 Type .141 Coax in 50 CM FMCA2816-50CM](#)

URL: <https://www.fairviewmicrowave.com/sma-male-to-sma-male-cable-rg402-type-.141-coax-fmca2816-50cm-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

