

RA N Male to RA N Male Cable Tinned Copper RG402 Type .141 Coax in 150 CM

FMCA2901-150CM



Configuration

- Connector 1: N Male Right Angle
- Connector 2: N Male Right Angle
- Cable Type: FM-SR141CUTN-STR
- Coax Flex Type: Semi-Rigid

Features

- Max Frequency 4 GHz

Applications

- General Purpose
- Laboratory Use

Description

The RA type N male to RA type N male 150 cm cable using Tinned Copper RG402 type .141 coax, part number FMCA2901-150CM, from Fairview Microwave is in-stock and ships same day. This Fairview type N to type N cable assembly has a male to male gender configuration with 50 ohm semi-rigid FM-SR141CUTN-STR coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA2901-150CM type N male to type N male cable assembly operates to 4 GHz. The right angle type N interfaces on the FM-SR141CUTN-STR cable allow for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz
VSWR			1.5:1	

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2.5	4			GHz
Insertion Loss (Typ.)	1	1.27	1.54			dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.2 dB per connector.

Mechanical Specifications

Cable Assembly

Length 59.06 in [150.01 cm]
Width/Diameter 0.5 in [12.7 mm]

RA N Male to RA N Male Cable Tinned Copper RG402 Type .141 Coax in 150 CM



FMCA2901-150CM

Weight	0.299 lbs [135.62 g]
Cable	
Cable Type	FM-SR141CUTN-STR
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Tinned Copper
One Time Minimum Bend Radius	1 in [25.4 mm]

Connectors

Description	Connector 1	Connector 2
Type	N Male Right Angle	N Male Right Angle
Specification	MIL-STD-348	MIL-STD-348
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Right Angle
Contact Material and Plating	Brass, Gold over Nickel	Brass, Gold over Nickel
Contact Plating Specification	MIL-G-45204	MIL-G-45204
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Gold over Nickel	Brass, Gold over Nickel
Body Plating Specification	MIL-G-45204	MIL-G-45204
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	QQ-N-290	QQ-N-290

Environmental Specifications

Operating Range Temperature	-55 to +125 deg C
-----------------------------	-------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

RA N Male to RA N Male Cable Tinned Copper RG402 Type .141 Coax in 150 CM

FMCA2901-150CM



Typical Performance Data

How to Order

Part Number Configuration:

FMCA2901

- xx

uu

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: FMCA2901-12 = 12 inches long cable
FMCA2901-100cm = 100 cm long cable

RA N Male to RA N Male Cable Tinned Copper RG402 Type .141 Coax in 150 CM from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [RA N Male to RA N Male Cable Tinned Copper RG402 Type .141 Coax in 150 CM FMCA2901-150CM](#)

URL: <https://www.fairviewmicrowave.com/ra-n-male-to-ra-n-male-cable-tinned-copper-rg402-type-.141-coax-in-150-cm-fmca2901-150cm-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA2901-150CM CAD Drawing

RA N Male to RA N Male Cable Tinned Copper RG402 Type .141 Coax in 150 CM

