

RA N Male to RA N Male Cable Tinned Aluminum RG402 Type .141 Coax in 60 Inch

The RA type N male to RA type N male 60 inch cable using Tinned Aluminum RG402 type .141 coax, part number FMCA2857-60, from Fairview Microwave is in-stock and ships same day. This Fairview type N to type N cable assembly has a male to male gender configuration with 50 ohm semi-rigid FM-SR141ALTN-STR coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA2857-60 type N male to type N male cable assembly operates to 11 GHz. The right angle type N interfaces on the FM-SR141ALTN-STR cable allow for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Min | Typ | Max | Units |
|-----------------|-----|-----|-------|-------|
| Frequency Range | DC | | 11 | GHz |
| VSWR | | | 1.5:1 | |

Performance by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|------|------|------|------|----|-------|
| Frequency | 1 | 2.5 | 5 | 11 | | GHz |
| Insertion Loss (Typ.) | 1.05 | 1.33 | 1.78 | 2.83 | | dB |

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.2 dB per connector.

Mechanical Specifications

Cable Assembly

| | |
|---------|----------------------|
| Length* | 60 in [152.4 cm] |
| Weight | 0.241 lbs [109.32 g] |

Cable

| | |
|--------------------------------------|---------------------------|
| Cable Type | FM-SR141ALTN-STR |
| Impedance | 50 Ohms |
| Inner Conductor Type | Solid |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |
| Dielectric Type | PTFE |
| Number of Shields | 1 |
| Shield Layer 1 | Tinned Aluminum |
| Jacket Diameter | 0.141 in [3.58 mm] |

| | |
|------------------------------|------------------|
| One Time Minimum Bend Radius | 0.1 in [2.54 mm] |
|------------------------------|------------------|



Configuration:

- N Male Right Angle
- N Male Right Angle
- FM-SR141ALTN-STR

Features:

- Max Frequency 11 GHz

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Connectors

| Description | Connector 1 | Connector 2 |
|---------------------------------|---------------|---------------|
| Type | N Male | N Male |
| Impedance | 50 Ohms | 50 Ohms |
| Contact Material & Plating | Gold | Gold |
| Dielectric Type | PTFE | PTFE |
| Body Material & Plating | Brass, Gold | Brass, Gold |
| Coupling Nut Material & Plating | Brass, Nickel | Brass, Nickel |

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

How to Order

Part Number Configuration:

FMCA2857 - xx uu

cm = Centimeters
 <blank> = Inches

Length

Example: FMCA2857-12 = 12 inches long cable
 FMCA2857-100cm = 100 cm long cable


RA N Male to RA N Male Cable Tinned Aluminum RG402 Type .141 Coax in 60 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [RA N Male to RA N Male Cable Tinned Aluminum RG402 Type .141 Coax in 60 Inch FMCA2857-60](#)

URL: <https://www.fairviewmicrowave.com/ra-n-male-to-ra-n-male-cable-tinned-aluminum-rg402-type-.141-coax-in-60-inch-fmca2857-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.


| REVISIONS | | | |
|-----------|-----------------|------------|----------|
| REV. | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 07/11/2022 | AGANWANI |



1. CABLES 36" AND UNDER HAVE 1 LABEL CENTERED.
CABLES OVER 36" HAVE 2 LABELS, ONE AT EACH END
6.0" FROM THE FRONT OF THE CONNECTOR.


Fairview Microwave
an INFINITE brand

RA N Male to RA N Male Cable Tinned Aluminum
RG402 Type .141 Coax in 60 Inch

$$\begin{aligned} L \leq 12 \text{ [305]} &= +1 \text{ [25]} / -0 \\ 12 \text{ [305]} < L \leq 60 \text{ [1524]} &= +2 \text{ [51]} / -0 \\ 60 \text{ [1524]} < L \leq 120 \text{ [3048]} &= +4 \text{ [102]} / -0 \\ 120 \text{ [3048]} < L \leq 300 \text{ [7620]} &= +6 \text{ [152]} / -0 \\ 300 \text{ [7620]} < L &= +5\%L / -0 \end{aligned}$$


SHEET 1 OF 1

SCALE

N/A