

RA TNC Male to TNC Female Bulkhead Cable RG405 Type .086 Coax in 48 Inch

The RA TNC male to TNC female bulkhead 48 inch cable using RG405 type .086 coax, part number FMCA2925-48, from Fairview Microwave is in-stock and ships same day. This Fairview TNC to TNC cable assembly has a male to female gender configuration with 50 ohm semi-rigid FM-SR086CU-STR coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA2925-48 TNC male to TNC female cable assembly operates to 6 GHz. The right angle TNC interface on the FM-SR086CU-STR cable allows for easier connections in tight spaces. Our RF cable assembly with TNC bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Min | Typ | Max | Units |
|-------------------------|------|--------------|-------|--------------|
| Frequency Range | DC | | 6 | GHz |
| VSWR | | | 1.5:1 | |
| Velocity of Propagation | | 69.5 | | % |
| RF Shielding | -110 | | | dB |
| Capacitance | | 29.4 [96.46] | | pF/ft [pF/m] |

Performance by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|------|------|------|----|----|-------|
| Frequency | 1 | 2.5 | 6 | | | GHz |
| Insertion Loss (Typ.) | 1.18 | 1.54 | 2.46 | | | dB |

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB for the straight connector and 0.2 dB for the right angle connector.

Mechanical Specifications

Cable Assembly

| | |
|---------|---------------------|
| Length* | 48 in [121.92 cm] |
| Weight | 0.141 lbs [63.96 g] |

Cable

| | |
|--------------------------------------|---------------------------|
| Cable Type | FM-SR086CU-STR |
| Impedance | 50 Ohms |
| Inner Conductor Type | Solid |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |



Configuration:

- TNC Male Right Angle
- TNC Female Bulkhead
- FM-SR086CU-STR

Features:

- Max Frequency 6 GHz
- Shielding Effectivity > -110 dB
- 69.5% Phase Velocity

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Dielectric Type PTFE
 Number of Shields 1
 Outer Conductor Material and Plating Copper
 Repeated Minimum Bend Radius 0.05 in [1.27 mm]

Connectors

| Description | Connector 1 | Connector 2 |
|---------------------------------|-------------------------|------------------------------------|
| Type | TNC Male | TNC Female |
| Mount Method | | Bulkhead |
| Impedance | 50 Ohms | 50 Ohms |
| Contact Material & Plating | Brass, Gold over Nickel | Beryllium Copper, Gold over Nickel |
| Dielectric Type | PTFE | PTFE |
| Body Material & Plating | Brass, Nickel | Brass, Nickel |
| Coupling Nut Material & Plating | Brass, Nickel | |

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMCA2925 - xx uu

cm = Centimeters
 <blank> = Inches
 Length

Example: FMCA2925-12 = 12 inches long cable
 FMCA2925-100cm = 100 cm long cable


RA TNC Male to TNC Female Bulkhead Cable RG405 Type .086 Coax in 48 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [RA TNC Male to TNC Female Bulkhead Cable RG405 Type .086 Coax in 48 Inch FMCA2925-48](#)

URL: <https://www.fairviewmicrowave.com/ra-tnc-male-to-tnc-female-bulkhead-cable-rg405-type-.086-coax-fmca2925-48-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

| REVISIONS | | | |
|-----------|-----------------|------------|----------|
| REV. | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 07/26/2022 | AGANWANI |



NOTES:

1. CABLES 36" AND UNDER HAVE 1 LABEL CENTERED. CABLES OVER 36" HAVE 2 LABELS, ONE AT EACH END 6.0" FROM THE FRONT OF THE CONNECTOR.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

| | | | | | | | | | | | | | | | | | | |
|---|--|---|---------------------------------------|-----------|-----------------------------|------------------|--------|---|--------------------|-------------|--|--|--|---|--|--|----------------------------|--|
| <p>Fairview Microwave an INFINIT[®] brand</p> | <p>UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS</p> <p>TOLERANCES: CABLE LENGTH (L) TOLERANCES:</p> <table border="0"> <tr> <td>.X = ±.2 [5.08]</td> <td>FRACTIONS</td> <td>L ≤ 12 [305] = +1 [25] / -0</td> </tr> <tr> <td>.XX = ±.02 [.51]</td> <td>± 1/32</td> <td>12 [305] < L ≤ 60 [1524] = +2 [51] / -0</td> </tr> <tr> <td>.XXX = ±.005 [.13]</td> <td>ANGLES ± 1°</td> <td>60 [1524] < L ≤ 120 [3048] = +4 [102] / -0</td> </tr> <tr> <td></td> <td></td> <td>120 [3048] < L ≤ 300 [7620] = +6 [152] / -0</td> </tr> <tr> <td></td> <td></td> <td>300 [7620] < L = +5%L / -0</td> </tr> </table> | | .X = ±.2 [5.08] | FRACTIONS | L ≤ 12 [305] = +1 [25] / -0 | .XX = ±.02 [.51] | ± 1/32 | 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 | .XXX = ±.005 [.13] | ANGLES ± 1° | 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0 | | | 120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 | | | 300 [7620] < L = +5%L / -0 | <p>THIRD-ANGLE PROJECTION</p> <p>THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.</p> |
| | .X = ±.2 [5.08] | FRACTIONS | L ≤ 12 [305] = +1 [25] / -0 | | | | | | | | | | | | | | | |
| .XX = ±.02 [.51] | ± 1/32 | 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 | | | | | | | | | | | | | | | | |
| .XXX = ±.005 [.13] | ANGLES ± 1° | 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0 | | | | | | | | | | | | | | | | |
| | | 120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 | | | | | | | | | | | | | | | | |
| | | 300 [7620] < L = +5%L / -0 | | | | | | | | | | | | | | | | |
| <p>TITLE</p> <p>RA TNC Male to TNC Female Bulkhead Cable RG405 Type .086 Coax in 48 Inch</p> | <p>ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.</p> | | <p>SHEET 1 OF 1</p> <p>SCALE N/A</p> | | | | | | | | | | | | | | | |
| <p>SIZE A</p> | <p>CAGE CODE 3FKR5</p> | <p>DRAWN BY PSRINIVAS</p> | <p>ITEM NO. FMCA2925</p> <p>REV A</p> | | | | | | | | | | | | | | | |

T-Rev.D